

The GYSFLASH 8.12 PL (8 A) is an advanced charger, designed to recharge 12 V lead-acid and lithium-iron phosphate (LiFePO₄) batteries. It has 2 distinct and intelligent charging programmes that optimise the performance of each battery type. The 8 A charging current is ideal for recharging batteries in cars, vans and motor homes.

UNIVERSAL LEAD / LITHIUM CHARGER

• 2 charging modes:

Pb : for charging all 12 V lead-acid batteries from 15 Ah to 160 Ah.

LiFePO₄ : for charging lithium-iron phosphate batteries from 1.2 Ah to 160 Ah.

3 charging currents:

Allows you to select the charging current best suited to the capacity of the battery.


	Pb	1 A
	LiFePO₄	4 A
	Pb	8 A
	LiFePO₄	8 A

• **Cold ❄️ / AGM option** : specific charging mode for cold conditions (below 5°C) and for more demanding Start & Stop (AGM) batteries.

• **Optimised maintenance charge**, the charger can be attached to the battery indefinitely during winter storage. The «Auto Restart» function means that the device will memorise all settings in the event of a power cut, and will automatically restart.

100% AUTOMATIC CHARGE

- Extends the life and performance of Lead (gel, AGM, liquid, calcium, etc.) and Lithium (LFP) batteries.
- The charger precisely regulates the charging parameters depending on the internal temperature.



Supplied with:



Clamps
(45 cm)



Eyelets - M6
(45 cm)



SAE connector
(145 cm)

Options



SAE / Cigar lighter
(45 cm)
ref. 077331



Extension cable
SAE / SAE (45 cm)
ref. 077348

ULTRA-SAFE

- Protects the vehicle's on-board electronics: short circuit, reverse polarity and overload protection. Spark prevention system.
- Automatic stand-by mode if the battery is disconnected.
- Integrated temperature sensor to prevent internal electronics' overheating.
- Simplified interface to avoid handling errors.

ERGONOMIC

- Compact design, light and portable.
- Resistant to dust and liquid ingress (IP65).
- Can be wall mounted.

50 / 60 Hz		I _{charge}					Ondulation/ Ripple	Charging curve		40°C/230V					IP	
220-240 V AC	130 W	1/4/8 A	12 V	Pb 2 < 160 Ah LiFePO ₄ 1.2 < 160 Ah	2 < 240 Ah 1.2 < 240 Ah	<0.4 Ah/ month	<150 mV Rms	I _U U	7 step 8 step	8 A @ 100 %	190 x 100 x 52	365 x 195 x 70	1.1	Automatic >2 V	IP 65	2 m