



Professional battery tester with ultra-precise measurement and intuitive colour display.

COMPREHENSIVE TESTING FUNCTIONALITY



6 and 12 V Battery Test:

- Voltage and state-of-charge test.



6 and 12 V Starter:

- Start-up voltage test.



6 and 12 V alternator:

- No-load and under-load voltage test, and under-load current ripple test.

VERSATILE

Compatible with 3 types of lead-acid battery, ranging from 7 to 240 Ah:

- Sealed batteries VRLA / GEL / AGM FLAT PLATE / AGM SPIRAL
- STANDARD LIQUID batteries
- START / STOP batteries (EFB/AGM)


Working specifications:

FR	DIN	SAE	JIS	IEC	CA/MCA
				international standard	marine battery
10 > 2000 A	10 > 1400 A	10 > 2000 A	26A17 > 245H2	10 > 1400 A	10 > 2000 A

HIGHLY ACCURATE

- Automatic external temperature compensation.
- Dynamic resistance measurement minimises battery discharge and gives a reliable result that is not influenced by:
 - surface charge
 - parasitic load (lights, various indicators, etc)
 - contact problems (terminal oxidation, loose terminal lugs)


INTUITIVE & SAFE



- 2.4-inch colour screen.
- Result available in less than 1 second.
- Follow up with a new test straight away.
- Stores the results of the last test performed.
- Reverse polarity protection.



Interface translated into 9 languages



			TEST			 RESULT		 TEMPERATURE COMPENSATION			
			Battery A	Battery V	CHARGING & STARTING SYSTEM VEHICLE						
	6-12 V	7 > 240 Ah	•	• min 5 V	6 V 12 V	1 s	instant	•	8 x 1,8 x 13,4 cm	70 cm	