

Constant Voltage LED Power Supply

SLT100-12VFG-UN

SLT100-24VFG-UN3



Product description:

This type of power supply is an exclusively designed stabilized power supply for LED lamp. With constant voltage (CV) technology, it is suitable for constant voltage lamps (12/24V DC) connected in parallels. As an advantage of constant voltage (CV) technology, a switch can be installed between secondary side and lamps. The built-in protection circuit will shut down the power supply in case of such faults as: open circuit, short circuit, over load. The power supply will restart automatically after fault correction.

In Over Temperature Protection, the power supply will shut down in case of interior or exterior temperature exceed, after temperature goes down, this fault can be eliminate with re-power.

Standards:

EN61347-1	UL8750
EN61347-2-13	FCC15B
EN61547	
EN55015	
EN61000-3-2	
EN61000-3-3	
EN62384	
EN62493	


Characteristics:

- Terminal block for quick connection
- Class II protection against electric shock from direct and indirect contact
- SELV output(<60V)
- Fast start-up time <0.5s
- Open circuit, short circuit, over load and over temperature protection
- Super thin design
- No load power consumption≤0.5W (for 12/24V version)
- Efficiency:≥92% (AC230V,full load)


Specifications:

Model		SLT100-12VFG-UN	SLT100-24VFG-UN3
Output	turn on time(S)	<0.5	<0.5
	output power(W)	96W@230V 80W@120V	100W@230V 80W@120V
	output votage(V)	12	24
	output voltage tolerance ^①	+/-5%	+/-5%
	ripple voltage(mV)	300(Vp-p)	400(Vp-p)
	working current range(A)	0-8@230V 0-6.67@120V	0-4.17@230V 0-3.33@120V
	dimming interface	No	
	dimming range	n/a	
Input	rated supply voltage(Vac)	120-240	120-240
	voltage range(Vac)	108-264	108-264
	line frequency(Hz)	50/60	50/60
	input current(mA)	500@230V,750@120V	500@230V,750@120V
	efficiency ^②	92.0%	93.0%
	average efficiency ^③	91.0%	92.0%
	no load power consumption(W)	<0.5	<0.5
	power factor ^②	0.95	0.95
	inrush current(lpk)	45A/180us	45A/180us
Protection	over voltage protection	YES	YES
	short circuit protection	YES	YES
	over temperature protection	YES	YES
	over load protection	YES	YES
	automatic restart	Yes, except	Yes, except
	surge capacity	L-N:1kV	L-N:1kV
Ambient and Life	Ta(°C)	-20...45	-20...45
	Tc max.(°C)	90	90
	Storage Temperature(°C)	-30...80	
	ambient humidity range	5%...85%, Not condensing	
	nominal life-time(hrs)	50000@Tc=90°C	50000@Tc=90°C
Other	weight(g)	215	215
	dimensions (LxWxH)(mm)	298×30×16.5	
	casing material	Plastic	
	housing colour	Grey+Blue	
	type of protection	IP20	
	protection class	Class II for EU; Class2 output for USA	Class II for EU; Class2 output for USA
Note	1. Tolerance:includes set up tolerance, line regulation and load regulation. 2. Tested at full load,230Vac.Refer to"Power Factor" and "EFFICIENT"curve graphs. 3. Calculate the model's average efficiency for each test voltage by testing at 100%, 75%, 50%, and 25% of rated current and then computing the simple arithmetic average of these four values. 4. All parameters NOT specially mentioned are measured at nominal voltage input, rated load and 25 of ambient temperature. 5. The power supply is considered as a component that will be operated in combination with final equipment. Since EMC performance will be affected by the complete installation, the final equipment manufacturers must re-qualify EMC Directive on the complete installation again.		



Dimensions(mm):





Wiring diagram:



Electrical curves:



Electrical curves:



MCBS information:

Miniature circuit breaker Model	B10	B13	B16	B20	C10	C13	C16	C20
SLT100-12VFG-UN	8	11	14	17	14	17	23	28
SLT100-24VFG-UN3	8	11	14	17	14	17	23	28

Order information:

Order.No.	Model	Carton quantity(pcs)	Carton dimension(mm)	G.W./CTN(kg)
1001-610250-0130	SLT100-12VFG-UN	50	335x275x225	12.3
1001-210069-0130	SLT100-24VFG-UN3	50	335x275x225	12.2

Sales & Technical Support:

SELF Electronics Co.,Ltd.(Headquarters)

Add: No. 1345 JuXian Road, Ningbo Hi Tech Park, Ningbo, China 315103
 Phone: +86-574-2880-5765, +86-574-2880-5658 (for English assistance)
 +86-574-2880-5678 (for Chinese assistance)
 Fax: +86-574-28805656
 E-mail: sales@self-electronics.com
<http://www.self-electronics.com>

SELF Electronics Co.,Ltd.,Shenzhen Office

Add: Room2007, Xinglang Xuan, Xinghemingju, Fuming Rd.,
 Futian District, Shenzhen
 Tel: +86-755-8355-8850
 Fax: +86-755-8355-8840
 E-mail: szsales@self-electronics.com

SELF Electronics Germany GmbH

August-Horch-Str. 7, 51149 Cologne
 Phone: +492203-18501-0
 Fax: 492203-18501-199
 E-mail: saleseu@self-electronics.com