

Constant Voltage LED Power Supply

SLT75-12VFG-UN

SLT75-24VFG-UN



Product description:

This type of power supply is an exclusively designed stabilized power supply for LED lamp. With constant voltage (CV) technology, it is suitable for constant voltage lamps (12/24V DC) connected in parallels. As an advantage of constant voltage (CV) technology, a switch can be installed between secondary side and lamps.

The built-in protection circuit will shut down the power supply in case of such faults as: open circuit, short circuit, over load. The power supply will restart automatically after fault correction.

Standards:

EN61347-1
EN61347-2-13
EN61547
EN55015
EN61000-3-2
EN61000-3-3
EN62384
EN62493
UL8750
FCC15B


Characteristics:

- Independent power supply for constant voltage LED lamp
- Terminal block for quick connection
- Class II protection against electric shock from direct and indirect contact
- SELV output(<60V)
- Fast start-up time $\leq 0.5s$
- Open circuit, short circuit, over load and over temperature protection
- Auto restart after fault conditions removal
- Super thin design
- No load power consumption $\leq 0.5W$
- Efficiency: $\geq 92\%$ (AC230V, full load)


Specifications :

Model	SLT75-12VFG-UN		SLT75-24VFG-UN	
Output	turn on time(S)	<0.5	<0.5	
	output power(W)	75	75	
	output votage(V)	12	24	
	output voltage tolerance ^①	+/-5%	+/-5%	
	ripple voltage(mV)	200(Vp-p)	200(Vp-p)	
	working current range(A)	0-6.25@230V 0-5@120V	0-3.125@230V 0-2.5@120V	
	dimming interface	No		
	dimming range	n/a		
Input	rated supply voltage(Vac)	120-240	120-240	
	voltage range(Vac)	108-264	108-264	
	line frequency(Hz)	50/60	50/60	
	input current(mA)	380@230V,550@120V	380@230V,550@120V	
	efficiency ^②	92.0%	92.5%	
	average efficiency ^③	91.0%	91.5%	
	no load power consumption(W)	≤0.5	≤0.5	
	power factor ^②	0.95	0.95	
	inrush current(Ipk)	45A/180us	45A/180us	
Protection	over voltage protection	YES	YES	
	short circuit protection	YES	YES	
	over temperature protection	YES	YES	
	automatic restart	YES	YES	
	over load protection	YES	YES	
	surge capacity	L-N:1kV	L-N:1kV	
Ambient and Life	Ta(℃)	-20...45	-20...45	
	Tc max.(℃)	90	90	
	Storage Temperature(℃)	-30...80		
	ambient humidity range	5%...85%, Not condensing		
	nominal life-time(hrs)	50000@Tc=85℃		
Other	weight(g)	155	155	
	dimensions (L×W×H)(mm)	298×30×16.5		
	casing material	Plastic		
	housing colour	Grey+Blue		
	type of protection	IP20		
	protection class	Class2		
Note	1. Tolerance:includes set up tolerance, line regulation and load regulation. 2. Tested at full load,230Vac.Refer to"Power Factor" and "EFFICIENT"curve graphs. 3. Calculate the model's average efficiency for each test voltage by testing at 100%, 75%, 50%, and 25% of rated current and then computing the simple arithmetic erage of these four values. 4. All parameters NOT specially mentioned are measured at nominal voltage input, rated load and 25 of ambient temperature. 5. The power supply is considered as a component that will be operated in combination with final equipment. Since EMC performance will be affected by the complete installation, the final equipment manufacturers must re-qualify EMC Directive on the complete installation again.			



Dimensions(mm):



Wiring diagram:





Electrical curves:



note

For constant current power supply,"LOAD" means the percentage of the maximum rated output voltage.
For constant voltage power supply,"LOAD" means the percentage of the maximum rated output current.

Electrical curves:



note

For constant current power supply, "LOAD" means the percentage of the maximum rated output voltage.
For constant voltage power supply, "LOAD" means the percentage of the maximum rated output current.

MCBS information:

Miniature circuit breaker Model	B10	B13	B16	B20	C10	C13	C16	C20
SLT75-12VFG-UN	8	11	14	17	14	17	23	28
SLT75-24VFG-UN	8	11	14	17	14	17	23	28

Order information:

Order.No.	Model	Carton quantity(pcs)	Carton dimension(mm)	G.W./CTN(kg)
1001-610255-0130	SLT75-12VFG-UN	50	335x275x225	8.9
1001-610254-0130	SLT75-24VFG-UN	50	335x275x225	8.9

Sales & Technical Support:

SELF Electronics Co.,Ltd.(Headquarters)

Add: No. 1345 JuXian Road, Ningbo Hi Tech Park, Ningbo, China 315103
 Phone: +86-574-2880-5765, +86-574-2880-5658 (for English assistance)
 +86-574-2880-5678 (for Chinese assistance)
 Fax: +86-574-28805656
 E-mail: sales@self-electronics.com
<http://www.self-electronics.com>

SELF Electronics Co.,Ltd.,Shenzhen Office

Add: Room2007, Xinglang Xuan, Xinghemingju, Fuming Rd.,
 Futian District, Shenzhen
 Tel: +86-755-8355-8850
 Fax: +86-755-8355-8840
 E-mail: szsales@self-electronics.com

SELF Electronics Germany GmbH

August-Horch-Str. 7, 51149 Cologne
 Phone: +492203-18501-0
 Fax: 492203-18501-199
 E-mail: saleseu@self-electronics.com