

VOLTCRAFT - RELIABLE AND PRECISE. SINCE 1982.

For decades, our product range has been dynamically adapting to the constant changes in the industry.

We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.


MSB-132 TEST LEAD

Item no. 3741996 (red / 1 m)

Item no. 3741997 (black / 1 m)

Item no. 3741998 (red / 2 m)

Item no. 3741999 (black / 2 m)



The compact and sturdy thermal imaging camera is a non-contact infrared temperature measurement device. The thermal image is shown in three adjustable pseudo colours on the colour screen. Menu and function keys simplify operation.

FEATURES

CAT I 30 VAC / 60 VDC, 32 A // 4 mm plug // Cable length: 1 m // Housing material: PA // Cable material: PVC // Double insulation cable // Gold-plated contact

PACKAGE CONTENTS

1x Test lead

TECHNICAL DATA

Connector	4 mm Banana Plug (Straight, Gold-Plated)
Cable Length	1 m
Cable colour	Red / Black
Insulation material	PVC
Housing material	PA
Contact Material	Brass (Gold-Plated) with Copper-Beryllium Spring
Conductor Cross-Section	2.5 mm ² (13 AWG)
Wire Stranding	72 / 0.08BC x 7 (Ø 4.0 mm)
Measurement Category	CAT I
Voltage Rating	30 V AC / 60 V DC
Current Rating	32 A
Contact Resistance	0.1 Ω
Operating Temperature	-10°C to +50°C (< 80% RH)
Storage Temperature	-10°C to +55°C (< 80% RH)
Weight	40 g

