

LogiLink®

USB-C to DisplayPort Cable

8K/60 Hz

Art. No.: CUA0130
CUA0131
CUA0132

Easily connect USB-C enabled devices to DisplayPort-enabled displays with LogiLink USB-C to DisplayPort cable. Ideal for watching videos and presentations on large DP enabled displays.

Features:

» Supports transmission from USB-C source to DP monitor
» Supports up to 8K@60 Hz or 4K@120 Hz
» For USB-C (Thunderbolt 3/4) devices with DP Alt Mode support
» Supports mirror and extend display modes
» Plug & Play with no drivers or installation required
» Black durable nylon braided cable





*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.

Made in China

Specifications:

Connection 1	USB-C 3.2 Gen 2, male
Connection 2	DisplayPort 1.4, male
Max. Resolution	Up to 8K@60 Hz, 4K@120 Hz
Supported Bandwidth	Up to 32.4 Gbps
HDCP	2.2
Compatible to Thunderbolt 3/4	Yes
HDR (High-Dynamic Range)	Yes, support Dolby Vision
3D Support	Yes
MST (Multi-Stream Transport)	Yes
DDC (Display Data Channel)	Yes
DSC (Display Stream Compression)	Yes
Display Modes	Primary/Extended/Mirror
Uncompressed Audio	LPCM 7.1
Compressed Audio	DTS, Dolby Digital, DTS-HD Master Audio, Dolby TrueHD
Housing Material	Aluminum alloy
Cable	Black nylon braided cable
Operating Temperature	0–45°C
Operating Humidity	25–60% RH (no condensation)

Art-No.	Cable Length	EAN Code
CUA0130	1 m	4052792084856
CUA0131	2 m	4052792084863
CUA0132	3 m	4052792084870



Package Contents:

» 1x USB-C to DisplayPort Cable
» 1x User Manual

Package Information:

Art-No.	Packing Dimension	Packing Weight	Carton Dimension	Carton Q'ty	Carton Weight
CUA0130	85 x 25 x 190 mm	0.067 kg	350 x 280 x 450 mm	100 pcs	7.24 kg
CUA0131	85 x 25 x 190 mm	0.093 kg	350 x 280 x 450 mm	100 pcs	9.78 kg
CUA0132	85 x 30 x 190 mm	0.133 kg	350 x 330 x 450 mm	100 pcs	13.85 kg

*The specifications and pictures are subject to change without prior notice.
*All trade names referenced are the registered trademarks of their respective owners.

Made in China