


TWE-357
denver.eu



denver

True Wireless Stereo Earbuds TWE-357



denver.eu
www.facebook.com/denver.eu
Instruction Manual


ENG 1

ENG

Safety information

Please read the safety instructions carefully before using the product for the first time and keep the instructions for future reference.

1. This product is not a toy. Keep it out of reach of children.
2. Warning: This product includes lithium polymer batteries.
3. Keep product out of the reach of children and pets to avoid chewing and swallowing.
4. Product operating and storage temperature is from 0 degree Celsius to 40 degree Celsius. Under and over this temperature might affect the function.
5. Never open the product. Touching the inside electrics can cause electric shock. Repairs or service should only be performed by qualified personnel.
6. Do not expose to heat, water, moisture, direct sunlight!
7. Please remove the earphones in case of any leakage or excessive heat from the product to avoid burns or rash.
8. Please protect your ears against loud volume. Loud volume can damage your ears.
9. Bluetooth wireless technology operates within a range of about 10 m (30 feet). The maximum communication distance may vary depending on the presence of obstacles (people, metal objects, walls, etc.) or the electro-magnetic environment.
10. Microwaves emitting from a Bluetooth device may affect the operation of electronic medical devices.
11. The unit is not waterproof. If water or foreign objects enter the unit, it may result in fire or electric shock. If water or a foreign object enters the unit, stop use immediately.
12. This product does not support harmonized charging.



Delivery Content:


1. Two earbuds (L / R)
3. Charging case

2. USB charging cable
4. Instruction manual

ENG 2

Usage Instructions

1. Pairing the earbuds with your smartphone



Step 1. The earbuds would turn on once they are taken out from the charging case, or long press the touch panels of both earbuds to turn on the earbuds, with voice prompt of 'Power on'.

Step 2. RED and BLUE LED would start blinking on both the earbuds. Both of the earbuds would automatically pair with each other within 5 secs.

Once they are paired with each other, one of the earbuds would show a RED and BLUE LED blinking alternatively, which means they are ready to pair with your smartphone.

Step 3. Now switch on Bluetooth in your smartphone to search for nearby devices and pair with the name 'TWE-357' with voice prompt 'Connected' after the pairing succeed. Enter '0000' if prompted for password.

The earbuds would re-connect with smartphone automatically after pairing.

Notes:

The L or R earbud can be used alone to pair with your smartphone, and thus only mono sound is available.

ENG 3

2. During Music Playback

- 2.1 Touch the L or R panel ONCE to Play / Pause the track
- 2.2 Touch the L or R panel TWICE to skip to Next track
- 2.3 Touch the L or R panel THREE TIMES to skip to Prev. track
- 2.4 Long touch the L or R panel for 3 seconds to trigger the Siri or Google Assistant.

3. During Calls

- 3.1 Touch the L or R panel ONCE to attend the incoming call / end the call.
 - 3.2 Touch the L or R panel for 2 seconds to reject the incoming call.
- With total 4 mics for perfect calls (ENC): The earbuds will reduce the wind and noise interference, so your words always come through loud and clear.

4. Charge the Earbuds & Charging Case

- 4.1 Put the earbuds in the charging case, the earbuds power off and start charging automatically. When the earbuds are charging, the icons on the LED display blinks until they are fully charged.
- 4.2 When the case is charging, the case LED digits blinks until it is fully charged.

5. Product Parameters

Model name: TWE-357

Bluetooth version: 5.3

Bluetooth name: TWE-357 (L / R / Both Earbuds)

Standby time: Approx. 15 hours

Music playback time: up to 5 hours


Earbuds battery capacity: 3.7V 30 mAh x L / R

Charging case battery capacity: 3.7V 230 mAh

Please notice - All products are subject to change without any notice.
We take reservations for errors and omissions in the manual.

ENG 4

ALL RIGHTS RESERVED, COPYRIGHT DENVER A/S



Electric and electronic equipment and included batteries contains materials, components and substances that can be hazardous to your health and the environment, if the waste material (discarded electric and electronic equipment and batteries) is not handled correctly.

Electric and electronic equipment and batteries is marked with the crossed out trash can symbol, seen above. This symbol signifies that electric and electronic equipment and batteries should not be disposed of with other household waste, but should be disposed of separately.

As the end user it is important that you submit your used batteries to the appropriate and designated facility. In this manner you make sure that the batteries are recycled in accordance with legislature and will not harm the environment.

All cities have established collection points, where electric and electronic equipment and batteries can either be submitted free of charge at recycling stations and other collection sites, or be collected from the households. Additional information is available at the technical department of your city.

Hereby, Denver A/S declares that the radio equipment type DENVER TWE-357 is in compliance with Directive 2014/53/EU. The full text of the RED declaration of conformity is available at the following internet address: denver.eu and then click the search ICON on top line of website. Write model number: TWE-357 and enter the page.

Operating Frequency Range: 2402MHz - 2480MHz
Max Output Power: 4dBm

Information on standby/off mode power consumption and power management for products compliant with Commission Regulation (EU) 2023/826 can be found at the following internet address: denver.eu and then click the search ICON on top line of website. Write model number: TWE-357 and enter the page.

Operating Frequency Range: 2402MHz - 2480MHz
Max Output Power: 4dBm

DENVER A/S
Omega 5A, Soeften
DK-8382 Hinnerup
Denmark
www.facebook.com/denver.eu

Warning: Lithium battery inside

Denver A/S reserve the rights for print errors
Denver A/S cannot be held responsible for any technical or typographical errors and reserves the right to make changes to the product and manuals without prior notice.
If you detect any inaccuracies or omissions, please inform us at the address on the back cover.

ENG 5

Contact

Main contact point: contact.hq@denver.eu

Nordics

Headquarter
Denver A/S
Omega 5A, Soeften
DK-8382 Hinnerup
Denmark

Phone: +45 86 22 61 00
(Push "1" for support)

E-Mail

For technical questions, please write to:
support.hq@denver.eu

For all other questions please write to:
contact.hq@denver.eu

Benelux

DENVER BENELUX B.V.
Barwoutswaarder 13C+D
3449 HE Woerden
The Netherlands

Phone: 0900-3437623
E-Mail: support.nl@denver.eu

Spain/Portugal

DENVER SPAIN S.A
Ronda Augustes y Louis Lumiere, n° 23 - nave
16
Parque Tecnológico
46980 PATERNA
Valencia (Spain)

Spain
Phone: +34 960 046 883
Mail: support.es@denver.eu

Portugal:
Phone: +35 1255 240 294
E-Mail: denver.service@satfiel.com

Germany

Denver Germany GmbH Service
Service Center
Max-Emanuel-Str. 4
94036 Passau

Phone: +49 851 379 369 40

E-Mail

support.de@denver.eu

Monday - Thursday 09:00 - 16:30
Friday 09:00 - 14:00

Austria

Lurf Premium Service GmbH
Deutschstrasse 1
1230 Wien

Phone: +43 1 904 3085
E-Mail: denver@lurfservice.at

Poland

LetMeRepair Poland sp. z o.o.

ul. Czeszochowska 140
62-800 Kalisz

Phone: 62 75 38 092
E-Mail: denver-service@ietmerepair.pl

Godziny pracy: 8 - 18 (poniedziałek - piątek)

If your country is not listed above,
please write an email to
contact.hq@denver.eu

