


Data Sheet


Type Number:	55602	
System:	Nickel Metal Hydride/ KOH Electrolyte	
Nominal Voltage [V]:	1.2	
Nominal Capacity C [mAh]:	15	
Typical Capacity C [mAh]:	16	
	at 3 mA / 1.00 V	
Weight, approx. [g]	1.3	
Dimensions [mm]:	min.	max.
Diameter [d]:	11.4	11.5
Height [h]:	2.9	3.1
UL Recognition:	MH 13654 (N)	
Coding:	Manufacturing 5 digit code (123 = day/4 = year/ 5 = version)	
Temperature Ranges [°C]	min.	max.
Storage: less than 30 days	-40	65
Discharge:	-20	65
Charge:	0	65
Charging Method:		
Normal Charging:	1.5 mA for 14 – 16 h	
Accelerated Charging (20° C):	3 mA for 7-8 h	
Fast Charging:	7.5 mA for 3 h *	
	Time controlled, voltage control recommended	
Trickle Charging:	0.45 mA	
Overcharge (20° C):	2 mA continuous 3 mA up to 1 year	
Charge Retention [%] at 20°C:	90	
	Capacity available after 1 month Storage at 20°C	
Internal Resistance [Ohm]:	4	
	at charged cells, 20°C, DC: 0.2 CA/2 CA, (IEC 61951-2)	
Impedance [Ohm]:	0.49	
	at charged cells, 20°C, AC: 1kHz, (IEC 61951-2)	
Typical Capacities [mAh]:		
	at 15 mA / 0.90 V	15
Max. Discharge Current (cont.) [mA]:	30	
Life Expectancy (typical):		
IEC Cycle:	1000 Cycles	
Trickle Charge:	up to 6 years (20°C)	
Trickle Charge:	up to 3 years (45°C)	

* for fully discharged cells, 20 °C

Capacities based on normal charging