

Quick Start Guide

TB353FU

TB353ZA


TB353ZU

Lenovo

Get started

- Read this guide carefully before using your device.
- All pictures and illustrations in this guide are for your reference only. The actual product may vary.
- Rated IP68: Dust-tight. Tested for immersion in up to 1.5 meters of fresh water for up to 30 minutes. Temporary audio distortion until dry.

Overview




- | | | |
|---------------------------------------|---------------------|-----------------|
| 1 Power button/
Fingerprint sensor | 2 Volume buttons | 3 Action key |
| 4 Microphones | 5 Front camera | 6 LED indicator |
| 7 NFC area | 8 Audio jack | 9 Speakers |
| 10 USB-C1 connector | 11 USB-C2 connector | 12 Flash |
| 13 Rear camera | | |

- Only the USB-C1 connector supports the wired screen projection.
- Both the USB-C1 and USB-C2 connectors support charging and data transfer, but they cannot be used for simultaneous charging or data transfer.



Install cards

- Turn off your device before inserting or removing a card.
- Make sure to insert cards before installing the battery.
- If you're using a third-party SIM, contact your carrier for more details.

1. Starting from the notch, release all the latches around the perimeter before removing the back cover.




2. Insert a SIM card or microSD card.




Install the battery

- This device does not come with the battery pre-installed.
- This device can work normally even without battery when connected to a required ac adapter. But make sure to store the removed battery properly to avoid any damage.

1. Insert the battery, aligning its gold contacts with the device's and making sure the connector snaps firmly into place. Then press it down flat.



2. Replace the back cover.



- ⚠ • Ensure that the back cover is securely latched on all sides. An open or loose cover directly exposes internal components, and any intrusion of water or dust may cause permanent failure. Therefore, prolonged operation without the back cover installed is strictly prohibited.
- To avoid injury or damage to your device, do not use incompatible, worn or damaged batteries, chargers or cables. Specifically, do not charge the battery separately using any equipment other than your device.

Charge your device

For environmental reasons this package may not include a charger in certain countries or regions. This device can be powered with most USB power adapters and a cable with USB Type-C plug. Use a USB Power Delivery compliant charger that supports power output no less than 15 W for tablet charging. Please note that a minimum output power of 36 W is required from the charger for device operation without a battery.

It is recommended to use a charger that complies with applicable national/regional regulations for mobile device adapters. Only use a charger that complies with international and regional safety standards (such as EN/IEC/UL 62368-1) for charging. Other chargers may not comply with applicable safety standards, and using such chargers to charge may result in injury or death.

Configure network connection

- Go to **Settings** > **WLAN/Wi-Fi**, and toggle the switch to turn **WLAN/Wi-Fi** on or off.
- Go to **Settings** > **Mobile network**, and toggle the switch to turn **Mobile data** on or off .
- Go to **Settings** > **Bluetooth**, and toggle the switch to turn **Bluetooth** on or off.

Help and more

To get more information and download the *User Guide*, go to <https://support.lenovo.com>.

European Union (EU) / United Kingdom (UK) compliance statement



Lenovo (Singapore) Pte. Ltd. declares that the radio equipment types: TB353FU and TB353ZU are in compliance with EU Radio Equipment Directive 2014/53/EU. Lenovo (Slovakia) Ltd. declares that the radio equipment types: TB353FU and TB353ZU are in compliance with UK Radio Equipment Regulation SI 2017 No. 1206. The full text of the system declarations of conformity are available at:

<https://www.lenovo.com/us/en/compliance/eu-doc> for EU and

<https://www.lenovo.com/us/en/compliance/uk-doc> for UK.

This radio equipment operates with the following frequency bands and maximum radio-frequency power:

Model Name	Frequency Bands	Maximum Power (dBm)
TB353FU	WLAN 2400 - 2483.5 MHz	< 20
	WLAN 5150 - 5250 MHz	< 23
	WLAN 5250 - 5350 MHz	< 23
	WLAN 5470 - 5725 MHz	< 23
	WLAN 5725 - 5850 MHz	< 14
	WLAN 6E 5945 - 6425 MHz	< 23
	Bluetooth 2400 - 2483.5 MHz	< 20
	NFC 13.56 MHz	42 dBμA/m @ 10 m

Model Name	Frequency Bands	Maximum Power (dBm)
TB353ZU	LTE B1/B3/B5/B7/B8/B20/B28/B38/B40	23
	LTE B41	26
	5G NR n1/n3/n5/n7/n8/n20/n28/n38/n40/n41	23
	5G NR n77/n78	26
	WLAN 2400 - 2483.5 MHz	< 20
	WLAN 5150 - 5250 MHz	< 23
	WLAN 5250 - 5350 MHz	< 23
	WLAN 5470 - 5725 MHz	< 23
	WLAN 5725 - 5850 MHz	< 14
	WLAN 6E 5945 - 6425 MHz	< 23
	Bluetooth 2400 - 2483.5 MHz	< 20
	NFC 13.56 MHz	42 dBμA/m @ 10 m

Restrictions of use:

Usage of this device is limited to indoor in the bands 5250 to 5350 MHz and 5945 to 6425 MHz.

	AT	BE	BG	CH	CY	CZ	DE	DK	EE	EL	ES	FI
	FR	HR	HU	IE	IS	IT	LI	LT	LU	LV	MT	NL
	NO	PL	PT	RO	SE	SI	SK	TR	UK	UK (NI)		

Specific Absorption Rate information

THE DEVICE MEETS INTERNATIONAL GUIDELINES FOR EXPOSURE TO RADIO WAVES.

The device is a radio transmitter and receiver. It is designed not to exceed the limits for exposure to radio waves (radio frequency electromagnetic fields) recommended by international guidelines. The guidelines were developed by an independent scientific organization (ICNIRP) and include a substantial safety margin designed to assure the safety of all persons, regardless of age and health. The radio wave exposure guidelines use a unit of measurement known as the Specific Absorption Rate, or SAR.

Tests for SAR are conducted using standard operating positions with the device transmitting at its highest certified power level in all tested frequency bands. The highest SAR values under the ICNIRP guidelines for your device model are listed below:

Maximum SAR for this model and conditions under which it was recorded.				
EU/UK 10g SAR Limit (2.0 W/kg)	TB353FU	Body-worn (0 mm)	WLAN, Bluetooth	1.58 W/kg
EU/UK 10g SAR Limit (4.0 W/kg)		Limb (0 mm)	WLAN, Bluetooth	1.58 W/kg
EU/UK 10g SAR Limit (2.0 W/kg)	TB353ZU	Body-worn (0 mm)	5G NR, WLAN, Bluetooth	1.58 W/kg
EU/UK 10g SAR Limit (4.0 W/kg)		Limb (0 mm)	5G NR, WLAN, Bluetooth	1.58 W/kg

 The above information is for EU countries and UK. Please refer to the actual product for supported frequency bands in other countries.

During use, the actual SAR values for your device are usually well below the values stated. This is because, for purposes of system efficiency and to minimize interference on the network, the operating power of the device is automatically decreased when full power is not needed for the data connection. The lower the power output of the device, the lower its SAR value. If you are interested in further reducing your RF exposure then you can easily do so by limiting your usage or simply using a hands-free kit to keep the device away from the body.

Charging capabilities and the compatible charging devices of this product

The power delivered by the charger must be between min 15 Watts required by the radio equipment, and max 45 Watts in order to achieve the maximum charging speed. And the device supports USB Power Delivery (USB-PD).



© Copyright Lenovo 2026.

Reduce | Reuse | Recycle



V1.0_20260326



80602329H001

DL

Printed in China

