# Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

**Supplier's name or trade mark:** V-TAC

**Supplier's address:** V-TAC Europe, bul. Rozhen 41, Sofia, BG

**Model identifier:** 78646

**Type of light source:**

| | | | |
|---|---|---|---|
| Lighting technology used: | LED | Non-directional or directional: | NDLS |
| Light source cap-type (or other electric interface) | L/N CON-NECTION | | |
| Mains or non-mains: | MLS | Connected light source (CLS): | No |
| Colour-tuneable light source: | No | Envelope: | - |
| High luminance light source: | No | | |
| Anti-glare shield: | No | Dimmable: | No |


**Product parameters**

| Parameter | Value | Parameter | Value |
|---|---|---|---|
| **General product parameters:** | | | |
| Energy consumption in on-mode (kWh/1000 h), rounded up to the nearest integer | 18 | Energy efficiency class | E |
| Useful luminous flux (ϕuse), indicating if it refers to the flux in a sphere (360º), in a wide cone (120º) or in a narrow cone (90º) | 1 980 in Sphere (360°) | Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set | 3 000 or 4 000 or 6 500 |
| On-mode power ($P_{on}$), expressed in W | 18,0 | Standby power ($P_{sb}$), expressed in W and rounded to the second decimal | 0,00 |
| Networked standby power ($P_{net}$) for CLS, expressed in W and rounded to the second decimal | - | Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set | 80 |
| Outer dimensions without separate control gear, lighting control — Height | 29 | Spectral power distribution in the range 250 nm to 800 nm, at full-load | See image in last page |
| Outer dimensions without separate control gear, lighting control — Width | 221 | | |
| Outer dimensions without separate control gear, lighting control — Depth | 221 | | |

| | | | | |
|---|---|---|---|---|
| parts and non-lighting control parts, if any (millimetre) | | | | |
| Claim of equivalent power[(a)] | | - | If yes, equivalent power (W) | - |
| | | | Chromaticity coordinates (x and y) | 0,380<br>0,380 |
| **Parameters for LED and OLED light sources:** | | | | |
| R9 colour rendering index value | | 6 | Survival factor | 1,00 |
| the lumen maintenance factor | | 0,96 | | |
| **Parameters for LED and OLED mains light sources:** | | | | |
| displacement factor (cos ϕ1) | | 0,70 | Colour consistency in McAdam ellipses | 6 |
| Claims that an LED light source replaces a fluorescent light source without integrated ballast of a particular wattage. | | -[(b)] | If yes then replacement claim (W) | - |
| Flicker metric (Pst LM) | | 1,0 | Stroboscopic effect metric (SVM) | 0,4 |

(a) '-' : not applicable;

(b) '-' : not applicable;


1.0
光谱三原色色比 R=33.1%,G=47.9%,B=19.0%,
0.5
380
460
540
620
700
780

Model placed on the Union market from 29/10/2025.

**EPREL registration number:** 2519294

https://eprel.ec.europa.eu/qr/2519294

**Supplier:** V-TAC Europe Ltd (Manufacturer)

**Website:** www.v-tac.eu

**Customer care service:**

**Name:** V-TAC Europe

**Website:** www.v-tac.eu

**Email:** office@v-tac.eu

**Phone:** +359290566

**Address:**
bul. Rozhen 41
Sofia
Bulgaria