

KERN EMB 5.2K5

KERN

Entry level laboratory balance with tremendous weighing performance



Category

Brand	KERN
Product category	Laboratory balance
Product group	School balance
Product family	EMB

Measuring System

Weighing system	Strain gauge
Weighing capacity [Max]	5200 g
Readability [d]	5 g
Reproducibility	5 g
Linearity	± 10 g
Resolution	1.040
Tare range	5200 g

Adjustment options	Adjusting with external weight
--------------------	--------------------------------

Recommended adjusting weight	5 kg (M1)
------------------------------	-----------

Possible calibration points	5 kg
-----------------------------	------

Stabilization time	2,5 s
--------------------	-------

Warm-up time	10 min
--------------	--------

Eccentric loading at 1/3 [Max]	10 g
--------------------------------	------

Construction type of the scale	Single-range balance
--------------------------------	----------------------

Units	g dwt ozt oz
-------	-----------------------

Maximum creep (15 minutes)	10 g
----------------------------	------

Maximum creep (30 minutes)	20 g
----------------------------	------

Default unit	g
--------------	---

Display

Display type	LCD
--------------	-----

Display backlight	no
Display screen size	58×18 mm
Display digit height	15 mm
Languages of the user interface	Symbol language

Construction

Dimension housing (W×D×H)	170×244×39 mm
Dimensions weighing surface (Ø)	150 mm
Dimensions weighing surface	150 mm
Material housing	plastic
Material weighing plate	plastic

Functions

Underfloor weighing	Hook (included in delivery)
IP protection - complete device	-
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min
Tare function	manual (multi)
Number of keys for operation	2

Power Supply

Supplied power supply	Battery
Power supply type	Power adapter
	EURO
Plug-in power supply / adapter for countries - optional	UK US CH
Input voltage device / power [Max]	9 V, 300 mA
Power socket for mains adapter	Hollow plug, inside minus, Ø inside 2,1 mm, Ø outside 5,5 mm, long 12 mm
Battery / accumulator type	Alkali(-Manganese)
Battery	2×1.5 V AA
Battery connection	Pad + Spring
Battery operating time	150 h
Battery voltage	3 V
Battery - Individual weight	46 g
Rechargeable battery	KS-A01
Rechargeable battery operating time - backlight off	50 h
Rechargeable battery charging time	10 h
Rechargeable battery optional	Rchrg. battery optional
Battery/Accu connected	not connected, enclosed

KERN EMB 5.2K5



Entry level laboratory balance with tremendous weighing performance

Environmental conditions

Ambient temperature [Min]	0 °C
Ambient temperature [Max]	40 °C
Humidity of environment [Max]	80 %
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Approval

CE mark	✓
---------	---

Services (optional)

Article number for adjustment at the location of installation	961-248
Article number for DAkkS calibration	963-128
Article number for certificate of conformity	969-517

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	205×264×67 mm
Shipping method	Parcel service
Net weight approx.	0,55 kg
Gross weight approx.	0,70 kg
Shipping weight	0,7 kg

Product information

GTIN/EAN number	4045761028401
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

