



START

- 1**
- ◇ J1
 - ◇ J2
 - ◇ J3
 - ◇ J4
 - ◇ J5



- 2**
- ◇ R1... R6: 330 Ohm (Orange, Orange, Brown) - (Oranje, Oranje, Bruin) - (Orange, Orange, Brun) - (Orange, Orange, Braun) - (Orange, Orange, Brun) - (Oranssi, Oranssi, Ruskea) - (Naranjado, Naranjado, Marrón) - (Laranja, Laranja, Castanho) - (Aranciato, Aranciato, Marrone)
 - ◇ R7, R8, R9: 0 ohm (Black) - (zwart) - (noir) - (Schwarz) - (Svart) - (Musta) - (Negro) - (Preto) - (Nero)
 - ◇ R10... R13: 2K2 ((Red, Red, Red) - (Rood, Rood, Rood) - (Rouge, Rouge, Rouge) - (Rot, Rot, Rot) (Röd, Röd, Röd) - (Punainen, Punainen, Punainen) - (Rojo, Rojo, Rojo) - (Encarnado, Encarnado, Encarnado) - (Rosso, Rosso, Rosso)




- 3** DIODE
- CATHODE
- ◇D1... D5: 1N4148

Watch the polarity!
Att. la polarité!




- 4** CAPACITORS
- C...
- ◇ C1: 100nF (104)
 - ◇ C2: 22p


- 5** ELECTROLYTIC CAPACITORS
- Watch the polarity!
Att. À la polarité!




- 6** LED 3mm




- 7** REGULATOR




- 8** TRIMMER




- 9** PUSH BUTTON




- 10** SOCKET + IC



- 11** POWER JACK



- 12** BATTERY HOLDER



- 13** DISPLAY

