


<b>5 x 20 mm</b>	F = No. 120.900	(DIN 41661 / EN 60127-2-2)
	M = No. 121.800	(DIN 41571/2)
	T = No. 122.800	(DIN 41662 / EN 60127-2-3)

Inhalt:	100 St./pcs.:	10 x 160 mA	10 x	1	A
contents:		10 x 250 mA	10 x	1,6	A
contenu:		10 x 500 mA	10 x	2,5	A
		10 x 630 mA	10 x	4	A
		10 x 800 mA	10 x	6,3	A




<b>5 x 20 mm</b>	F = No. 520.800	(DIN 41661 / EN 60127-2-2)
	M = No. 521.800	(DIN 41571/2)
	T = No. 522.800	(DIN 41662 / EN 60127-2-3)

Inhalt:	200 St./pcs.:	10 x 100 mA	20 x	800	mA
contents:		10 x 200 mA	30 x	1	A
contenu:		10 x 315 mA	10 x	1,25	A
		10 x 400 mA	20 x	1,6	A
		30 x 500 mA	10 x	2,5	A
		20 x 630 mA	10 x	4	A
			10 x	6,3	A



<b>5 x 20 mm</b>	F = No. E3520.800	(DIN 41661 / EN 60127-2-2)
	M = No. E3521.800	(DIN 41571/2)
	T = No. E3522.800	(DIN 41662 / EN 60127-2-3)

Inhalt:	360 St./pcs.:	20 x 100 mA	20 x	800	mA
contents:		20 x 125 mA	20 x	1	A
contenu:		20 x 160 mA	20 x	1,25	A
		20 x 200 mA	20 x	1,6	A
		20 x 250 mA	20 x	2	A
		20 x 315 mA	20 x	2,5	A
		20 x 400 mA	20 x	3,15	A
		20 x 500 mA	20 x	4	A
		20 x 630 mA	20 x	6,3	A



<b>6,3 x 32 mm</b>	F = No. 632.800
	M = No. 632.820
	T = No. 632.830

Inhalt:	120 St./pcs.:	10 x 315 mA	10 x	2	A
contents:		10 x 500 mA	10 x	2,5	A
contenu:		10 x 800 mA	10 x	4	A
		10 x 1 A	10 x	5	A
		10 x 1,25 A	10 x	6,3	A
		10 x 1,6 A	10 x	10	A