

KERN UFN 600K200IPM

KERN

Pallet scale with stainless steel load support (IP67) and stainless steel display device (IP65), verification optional



Display backlight	✓
Display digit height	52 mm
Languages of the user interface	Symbol language

Construction

Dimension display device (W×D×H)	267×173×93 mm
Dimensions weighing surface (W×D)	1190×840 mm
Dimensions weighing surface	1190×840 mm
Dimensions weighing platform (W×D×H)	1360×850×90 mm
Material weighing plate	stainless steel
Material platform	stainless steel (SUS304)
Material display housing	stainless steel
Material load cell(s)	stainless steel
Level indicator	✓
Levelling feet adjustable	✓
Stand inclinable	✓
Wall mount	✓
Cable length	5 m
Display device cable length	5 m
Allowed cable length display device [Max]	30 m
Platform Construction	Welded load plate; smooth surface
Load cells - number	4

Functions

Sum memory function	✓
Recipe/summing level	Sum A
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Function for averaging under unstable weighing conditions	✓
Counting function	✓
Reference quantity	10, 20, 50, 100, 200
IP protection - display	IP65
IP protection - load cell	IP67
Auto-off interval(s) in battery mode/rechargeable battery mode	selectable
Auto-off interval(s) in mains power mode	selectable
Tare function	manual (single & multi)
Number of keys for operation	7

Category

Brand	KERN
Product category	Industrial scale
Product group	Pallet scale
Product family	UFN

Measuring System

Weighing system	Strain gauge
Weighing capacity [Max]	600 kg
Readability [d]	0,2 kg
Reproducibility	0,2 kg
Linearity	± 0,2 kg
Minimum weight [Min]	4 kg
Resolution	3.000
Tare range	-600 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	600 kg (M1)
Stabilization time	3 s
Warm-up time	10 min
Eccentric loading at 1/3 [Max]	0,2 kg
Load cell connection	4-wire
Units (if device is conformity assessed)	kg
Construction type of the scale	Single-range balance
Units	kg
Default unit	kg
Loadcell type	ZEMIC H8C 0.5 ton

Display

Display type	LCD
Display type	LCD with backlight

KERN UFN 600K200IPM



Pallet scale with stainless steel load support (IP67) and stainless steel display device (IP65), verification optional

Interface

Interfaces	RS-232 (optional, factory) Bluetooth BTC (v2.0) (optional, factory) analogue (0 - 10 V) (optional, factory) analogue (4 - 20 mA) (optional, factory)
------------	---

Power Supply

Supplied power supply	Accu & Power supply
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Input voltage power supply / power [Max]	110 V - 230 V AC
Power supply cable removable	removable
Input voltage device / power [Max]	12 V, 500 mA
Power socket for mains adapter	Hollow plug, inside plus, Ø outside 5,5 mm, Ø inside 2,1 mm, long 9,5 mm
Battery / accumulator type	Pb
Battery connection	Plug-in terminals
Rechargeable battery operating time - backlight on	20 h
Rechargeable battery operating time - backlight off	35 h
Rechargeable battery charging time	10 h
Battery/Accu connected	fixed electrical connection, not insulated

Environmental conditions

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Humidity of environment [Min]	10 %
Humidity of environment [Max]	95 %

Approval

CE mark	✓
Conformity assessment possible ex works	✓
Accuracy classe	III
Verification scale interval [e]	0,2 kg

Services (optional)

Article number for adjustment at the location of installation	961-250
Article number for conformity assessment	965-230
Article number for DAkkS calibration	963-130
Article number for certificate of conformity	969-517

Packing & Shipping


Delivery time	2 d
Dimensions packaging (W×D×H)	1410×910×210 mm
Shipping method	Freight
Net weight approx.	55 kg
Gross weight approx.	85 kg
Shipping weight	85 kg

Product information

GTIN/EAN number	4045761239807
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION



FACTORY

