INDUSTRIAL SCALE

PCE-SSB 30



- **Weight units: kg, g, lb, oz**
- **Alarm function for upper and lower weight limits**
- **Adjustable zero tracking**
- **Peak, stable, and average hold function**
- **Manual and automatic tare subtraction function**
- **Robust, waterproof stainless steel housing**
- **Operation via power adapter**

The industrial scale is the ideal solution for precise weighing tasks in industry, production, and food processing. Thanks to its robust, waterproof stainless steel housing, it is well suited for daily use under demanding conditions and impresses with durable construction as well as simple operation. With a weighing range from 0.02 to 30 kg / 0.04 ... 66.1 lbs and a resolution of 5 g / 0.2 oz, the industrial scale delivers reliable and accurate measurement results for a wide variety of applications. The selection of weight units in kilograms, grams, pounds, and ounces allows flexible use in national and international work environments.

For efficient process control, the industrial scale features an alarm function for upper and lower weight limits, supported by a clearly visible traffic light display. This makes it easy to monitor target weights quickly, which is especially beneficial in inspection and filling processes. The range of functions is complemented by adjustable zero tracking as well as manual and automatic tare subtraction, making it particularly convenient to weigh containers and packaging. In addition, peak, stable, and average hold functions are available so that measurement results can be recorded and evaluated reliably.

Power is supplied as standard via a power adapter.

Specification

Weighing range	
Measuring range max.	30 kg
Resolution	5 g

General technical data	
Units	kg, g, lb, oz
Display Typ	LCD
Digit size [WxH]	10 x 20 mm / 0.39 x 0.79 in
Alarm	optical, Acoustic
Alarm modes	Lower alarm value Upper alarm value
Minimum load [min]	20 g
Dimensions	Weighing platform: 220 x 190 mm / 8.66 x 7.48 in
Protection class (device)	IP68
Power supply	100 ... 240 V AC | 50/60 Hz
Operating conditions	0 ... 40 °C , 10 ... 90 %RH
Storage conditions	0 ... 40 °C , 10 ... 90 %RH
Dimensions (L x W x H)	320 x 270 x 130 mm
Weight	3165 g

PCE Americas Inc. dba PCE Instruments
1201 Jupiter Park Drive, Suite 8
Jupiter, FL 33458
USA

Phone: +1-561-320-9162
info@pce-americas.com