H Series Reed Relays

- **Features: High Voltage Relay, Open Frame with M4 Screw Mount**
- **Applications: Test and Medical Equipment & Others**
- **Markets: Medical, Test and Measurement & Others**



Part Description: H00-1X00

Nominal Voltage	Contact Quantity & Contact Form	Switch Model
12, 24	1A, 1B	69, 83


Customer Options / Contact Data (@ 20°C)	Switch Model 69 (A-Dry)	Switch Model 83 (A-Dry)	Unit
Contact Material	Rhodium	Rhodium	
Rated Power (max.) Any DC combination of V&A not to exceed max. rated power	50	50	W
Switching Voltage (max.) DC or peak AC	10,000	7,500	V
Switching Current (max.) DC or peak AC	3.0	3.0	A
Carry Current (max.) DC or peak AC	5.0	5.0	A
Contact Resistance (max.) @ 0.5V & 10mA, Measured with 40% Pull-In Overdrive	150	150	mOhm
Breakdown Voltage (min.) (upon request)* According to EN60255-27	15	15	kVDC
Operating Time (max.) Including Bounce, Measured w/40% Pull-In Overdrive	3.0	3.0	ms
Release Time (max.) Measured without Coil Suppression	1.5	1.5	ms
Insulation Resistance (min./typ.) Rh<45%, 100V Test Voltage	10^{12}	10^{12}	OH
Capacitance (typ.) @ 10kHz across open Switch	1	1	pF

USA: +1 866.782.6339 | info@standexelectronics.com EMEA: +49 (0)7733 9253 200 | emea@standexmeder.com APAC: +86 21/37606000 | salesasia@standexmeder.com


H Series Reed Relays

Coil Data (at 20°C)		Coil Voltage (VDC)		Coil Resistance (OH)	Pull-In Voltage (VDC)	Drop-Out Voltage (VDC)	Coil Power (mW)	Coil Inductance (mH)
Contact Form	Switch Model	Nominal	Max.	Typical (± 10 %)	Max.	Min.	Nominal	Nominal
1A	69	12		230	8.4	1.0	620	
		24		700	18.0	2.0	822	
	83	12		230	8.4	1.0	620	
		24		700	18.0	2.0	822	
1B	69	12		180	8.4	1.0	800	
		24		360	18.0	2.0	1,6	
	83	12		180	8.4	1.0	800	
		24		360	18.0	2.0	1,6	
The Pull-In, Drop-Out Voltage and Coil Resistance will change at rate of 0.4% per °C								

Relay Data (@ 20°C)		Unit
Dielectric Strength Coil/Contact (min.) According to EN60255-27	20	kVDC
Insulation Resistance Coil/Contact (min.) Rh<45%, 200V Test Voltage	10^{12}	OH
Capacitance Coil/Contact (typ.) @10 kHZ	1.2	pF
Shock Resistance (max.) 1/2 sine wave, 6md, 3-axis	50	g
Vibration Resistance (max.) 10 – 2,000 Hz	20	g
Operating Temperature (max.) Surrounding of the relay's housing	-20 to 70	°C
Storage Temperature (max.) Surrounding of the relay's housing	-35 to 95	°C
Soldering Temperature (max.) 5 sec. max.	260	°C
Washability Aqueous rinse suitable. Proper drying necessary.	Fully Sealed	

Glossary Contact Form		
Form A	NO = Normally Open Contacts SPST = Single Pole Single Throw	
Form B	NC = Normally Closed Contacts SPST = Single Pole Single Throw	


Dimensions (in mm [inch]) Tolerances acc. to ISO 2768-m




USA: +1 866.782.6339 | info@standexelectronics.com EMEA: +49 (0)7733 9253 200 | emea@standexmeder.com APAC: +86 21/37606000 | salesasia@standexmeder.com

H Series Reed Relays

Life Test Data (*Load increase reduces life expectancy of Reed Switches)





Handling & Assembly Instructions

- Switching inductive and/or capacitive loads create voltage and/or current peaks, which may damage the relay. Protective circuits need to be used.
- External magnetic fields needs to be taken into consideration, including a too high packing density. This may influence the relays' electrical characteristics.
- Mechanical shock impacts e.g. dropping the relays may cause immediate or post-installation failure.
- Wave soldering: maximum 260°/5 seconds.

Please note: All technical specifications on this series datasheet refer to the standard product range. Modifications in the sense of technical progress are reserved. For general information only. For more specific information, please consult the product datasheet, available upon request.

This series datasheet could contain technical inaccuracies or typographical errors. Changes are periodically made to the information herein. These change will be incorporated in future revisions.

For deviating values, most current specifications and products please contact your nearest sales office.

USA: +1 866.782.6339 | info@standexelectronics.com EMEA: +49 (0)7733 9253 200 | emea@standexmeder.com APAC: +86 21/37606000 | salesasia@standexmeder.com