INFRARED THERMOMETER

PCE-IR 810L



- **IR measuring range: -50 ... 550°C**
- **Response time approx. 1 s**
- **Measurement spot ratio (D:S) 8:1**
- **Spectral range: 6 ... 14 µm**
- **Measuring functions: MAX, MIN**
- **Automatic data hold function**
- **Emissivity: 0.95**

The Infrared thermometer is suitable for the rapid, non-contact measurement of surface temperatures and can be used, for example, for maintenance and servicing work, in workshops, and for checking machines, systems and technical components. The Infrared thermometer has an IR measuring range of -50 ... 550°C, a resolution of 0.1°C and an accuracy of ±2 % of reading, depending on the measuring range.

With a response time of >1 s and a measurement spot ratio of 8:1, the Infrared thermometer enables targeted temperature measurement from a specific distance. The spectral range is 6 ... 14 µm, while the emissivity is set to 0.95. The MAX and MIN functions are available for evaluating the measured values. An automatic data hold function keeps the measured value after the measurement, allowing it to be read conveniently. Power is supplied by a 9V alkaline battery, enabling the device to operate independently of an external power supply.

Specification

Infrared temperature	
Measuring range	-50 ... 0 °C
Resolution	0,1 °C
Accuracy	±4 °C
Infrared temperature	
Measuring range	0 ... 550 °C
Resolution	0,1 °C
Accuracy	±2% of reading or ±2°C
Infrared temperature	
Measuring range	-58 ... +32 °F
Resolution	0,1 °F
Accuracy	±7°F
Infrared temperature	
Measuring range	32 ... 1022 °F
Resolution	0,1 °F
Accuracy	±2% of measured value or ±4°F

General technical data	
Measuring functions	MIN, MAX, HOLD
Display type	LCD with backlight
Display size	0,98 Inch
Response time	1 s
Automatic power-off	8 s
Measurement spot	8:1
Laser	Class 2 <1mW
Emissivity	0,95
Spectral range	6 ... 14 µm
Wavelength range	630 ... 670 Nm
Menu language	English, English (GB)
(Rechargeable) battery	1 x 9 V 9V block , Alkali-manganese
Capacity	550 mAh
Performance	4,95 Wh
Operating conditions	0 ... 50 °C , 10 ... 90 % RH
Storage conditions	-20 ... 60 °C , 0 ... 80 % RH
Dimensions (L x W x H)	133 x 34 x 78 mm
Weight	94 g

PCE Instruments UK Ltd.
Chester Rd, Old Trafford Suite 1N-B, Trafford House, M32 0RS Manchester
Great Britain

Phone: +44 (0) 161 464902 0
info@pce-instruments.co.uk