

KERN KXP 60V20M

KERN

Platform: weighing plate of stainless steel, painted steel base, silicone-coated aluminium load cell with protection against dust and water splashes IP65



Category

Brand	KERN
Product category	Component
Product group	Platform
Product family	KXP-V20-IP65

Measuring System

Weighing capacity [Max]	30 kg; 60 kg
Readability [d]	2 g
Minimum weight [Min]	200 g; 400 g
Load cell connection	6-wire
Loadcell type	aluminium IP65 silicone-coated

Construction

Dimensions weighing surface (W×D)	400×300 mm
Dimensions weighing surface	400×300 mm
Dimensions weighing platform (W×D×H)	400×300×90 mm
Material weighing plate	stainless steel
Material platform	steel, lacquered
Material load cell(s)	aluminium
Levelling feet adjustable	✓
Transport safety lock - bolt torque	0,1 Nm
Cable length	3 m
Allowed cable length display device [Max]	10 m
Load cells - number	1

Functions

IP protection - complete device	IP65 (load cell)
IP protection - load cell	IP65

Approval

Conformity assessment possible ex works	✓
Verification scale interval [e]	10 g; 20 g

Services (optional)

Article number for conformity assessment	965-229
Article number for DAkkS calibration	963-129

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	630×495×210 mm
Shipping method	Parcel service
Net weight approx.	11 kg
Gross weight approx.	13 kg
Shipping weight	13,1 kg

Product information

GTIN/EAN number	4045761151833
REACH classification	no prohibited substances

Pictograms

STANDARD



FACTORY

