

SAUTER FH 500

KERN

Universal digital force gauge for tensile and compressive force measurements with integrated load cell



Material display housing	plastic
Mounting - force application	External thread M6
Load support (tensile force)	Hook

Functions	
Function for averaging	✓
Limit-setting function	✓
Memory function	✓
Statistic function	✓
Auto-off interval(s) in battery mode/rechargeable battery mode	1 - 60 min

Interface	
Interfaces	RS-232 standard USB-Device

Power Supply	
Supplied power supply	Accu & Power supply
Power supply type	Power adapter
Plug-in power supply / adapter for countries - optional	EURO
	AUS
	UK
	US
	CH

Input voltage power supply / power [Max]	100 V - 240 V
Input voltage device / power [Max]	5 V 1000 mA
Power socket for mains adapter	USB C
Battery / accumulator type	NiMH
Battery connection	2-pole tub connector
Battery capacity	1.200 mAh
Battery voltage	3,7 V
Battery - Number of cells	3
Battery - Construction	Inseparable connection of cells (pack)
Battery capacity (Wh)	4,4 Wh
Rechargeable battery operating time - backlight on	24 h
Rechargeable battery operating time - backlight off	40 h
Rechargeable battery charging time	120 min
Battery/Accu connected	fixed electrical connection, not insulated

Environmental conditions	
Ambient temperature [Min]	10 °C
Ambient temperature [Max]	40 °C
Storage temperature [Min]	-10 °C

Category

Brand	Sauter
Product category	Force measurement
Product group	Digital force gauge (internal measuring cell)
Product family	FH-S

Measuring System

Measuring range force [Max] (N)	500 N
Readability force [d] (N)	0,1 N
Measuring head measuring frequency	2 kHz
Internal data memory: Number of value groups	1
Overload protection (% of [Max])	150%
Tolerance (% of [Max])	0,5%
Internal data memory: Number of individual values	10
Directions of force	tension compression
Default unit	N

Display

Display type	LCD
Screen reversible	✓

Construction

Dimension housing (W×D×H)	230×70×40 mm
Dimensions completely mounted (W×D×H)	280×70×40 mm
Dimension display device (W×D×H)	45×25×0 mm
Material housing	plastic

SAUTER FH 500



Universal digital force gauge for tensile and compressive force measurements with integrated load cell

Storage temperature [Max] 40 °C

Approval

CE mark ✓

Services (optional)

Article number for DAkkS calibration (tensile force) 963-161

Article number for DAkkS calibration (compressive force) 963-261

Article number for DAkkS calibration (tensile force/ compressive force) 963-361

Article number for factory calibration (tensile force) 961-161

Article number for factory calibration (compressive force) 961-261

Article number for factory calibration (tensile force/ compressive force) 961-361

Packing & Shipping

Delivery time 1 d

Dimensions packaging (W×D×H) 330×190×95 mm

Shipping method Parcel service

Net weight approx. 0,55 kg

Gross weight approx. 1,4 kg

Shipping weight 1,356 kg

Product information

GTIN/EAN number 4045761368613

REACH classification no prohibited substances

Pictograms

STANDARD



OPTION

