

KERN PLJ 6200-2A

KERN

Range of precision balances with enormous weighing capacities – ideal for heavy tare containers or large samples



Category

Brand	KERN
Product category	Laboratory balance
Product group	Precision balance
Product family	PLJ

Measuring System

Automatic adjustment - Standard temperature deviation	1,2 °C
Weighing system	Force compensation
Weighing capacity [Max]	6200 g
Readability [d]	0,01 g
Reproducibility	0,01 g
Linearity	± 0,05 g
Resolution	620.000
Tare range	6200 g
Adjustment options	Internal calibration (automatic)
Stabilization time	3 s
Warm-up time	4 h
Eccentric loading at 1/3 [Max]	0,05 g
USP Minimum weight of sample (k = 2, U = 0.1%)	20 g
Construction type of the scale	Single-range balance

Units	g
	mg
	gn
	dwt
	tl (Tw)
	tl (HK)
	ozt
	tl (Singap, Malays)
	ct
	mo

	lb
	oz
Weighing capacity [Max] (ct)	31000 ct
Maximum creep (15 minutes)	100 mg
Maximum creep (30 minutes)	200 mg
Default unit	g

Display

Display type	LCD graphic
Display backlight	✓
Display screen size	132×38 mm
Display digit height - smallest digit	4 mm
Display digit height	15 mm
Languages of the user interface	English

Construction

Dimension housing (W×D×H)	210×340×120 mm
Dimensions completely mounted (W×D×H)	210×340×120 mm
Dimensions weighing surface (Ø)	160 mm
Dimensions weighing surface	160 mm
Material housing	plastic
Material weighing plate	stainless steel
Material platform	stainless steel
Level indicator	✓
Levelling feet adjustable	✓
Transport safety lock - bolt torque	0,1 Nm

Functions

PreTare function	✓
Recipe/summing level	Rez B (Net-total, memory with plain text designations + setpoint, also for printout)
Recipe weighing - number of database entries	99
Recipe weighing - number of ingredients per database entry	20
Percentage determination	✓
Density determination	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Underfloor weighing	Eye (included in delivery)
Function for averaging under unstable weighing conditions	✓
Time display	✓
Capacity - Display	✓

KERN PLJ 6200-2A



Range of precision balances with enormous weighing capacities – ideal for heavy tare containers or large samples

Standby function	✓
Counting function	✓
Counting resolution (laboratory conditions)	620.000
Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	10 mg
Smallest piece weight when piece counting - normal conditions	100 mg
Reference quantity	10, 25, 50, 100, n (any number of pieces)
Auto-off interval(s) in mains power mode	off 5 min 2 min 15 min
Tare function	manual (multi)
Number of keys for operation	6

Interface

Interfaces	RS-232 standard
------------	-----------------

Power Supply

Supplied power supply	Power supply unit
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO AUS UK US CH
Plug-in power supply / adapter for countries - optional	EURO UK US CH
Input voltage power supply / power [Max]	100 V - 240 V, 50 / 60 Hz
Power supply cable removable	removable
Input voltage device / power [Max]	24 V 1 A
Power socket for mains adapter	Hollow plug, inside plus, Ø outside 5,5 mm, Ø inside 2,1 mm, long 10,5 mm

Environmental conditions

Ambient temperature [Min]	15 °C
Ambient temperature [Max]	35 °C
Humidity of environment [Max]	80 %
Storage temperature [Max]	40 °C

Approval

CE mark	✓
---------	---

Services (optional)

Article number for DAkkS calibration	963-104
Article number for certificate of conformity	969-517

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	520×360×415 mm
Shipping method	Parcel service
Net weight approx.	5,0 kg
Gross weight approx.	8 kg
Shipping weight	15,5 kg

Product information

GTIN/EAN number	4045761243279
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION

