



Equerre de montage en métal, avec presse-étoupe M20

Référence SL7/4-FW-T
N° de catalogue 171455
Alternate Catalog No. SL7/4-FW-T

Gamme de livraison

Gamme			Equipements complémentaires
Fonction de base équipements complémentaires			Equerre de montage avec presse-étoupe M20
Matériaux			Acier inoxydable (angle) Aluminium (Gewindeadapter)
Mode de montage			pour montage vertical
			Joint d'étanchéité compris dans la livraison
Utilisation pour			SL4-PIB-T... SL7-CB-T...
Connexion à SmartWire-DT			non

Vérification de la conception selon IEC/EN 61439

Caractéristiques techniques pour la vérification de la conception			
Température d'emploi min.		°C	-30
Température d'emploi max.		°C	60

Caractéristiques techniques ETIM 7.0

Commutateurs basse tension (EG000017) / Colonne de signalisation, équerre de fixation (EC001153)			
Electricité, Electronique, Automatisation et Commande / Technique de commutation basse tension / Appareillage de commande et de signalisation / Élément de colonne de signalisation, équerre de fixation (ecl@ss10.0.1-27-37-12-33 [AKF051014])			
mode de pose			montage mural
couleur			autre

Homologations

Product Standards			IEC/EN 60947-5-1; UL 508; CSA-C22.2 No. 14-10; CSA-C22.2 No. 94-91; CE marking
UL File No.			E29184
UL Category Control No.			NKCR
CSA File No.			UL report applies to both US and Canada
CSA Class No.			NKCR7
North America Certification			UL listed, certified by UL for use in Canada
Degree of Protection			UL Type 4, 4X, 13

