




Type Designation	4114
Designation IEC	LR14
System	Zn-MnO ₂ (Alkaline)
Shelf Life (Coding)*	10 years
Nominal Voltage [V]	1.5
Typical Capacity C [mAh]	7600 (discharge with high-resistance)
Permissible Temperature Range	- 10 °C ... 50 °C
Weight, approx. [g]	65,8
Volume [ccm]	26

Dimensions [mm]

	min:	max:
Ø	24.9	26.2
A	-	50.0
B	48.6	-
C	13.0	-
E	-	0.9
F	-	7.5
G	1.5	-


Typical Capacities (at 20°C):

Discharge Type	Load	End Voltage[V]	0.9
4M/15M,8H/D,7D/W	3.9 Ω	Time [h]	21,7
Portable Lighting		Capacity [Ah]	6,32
		Energy [Wh]	7,25
Discharge Type	Load	End Voltage[V]	0.8
1H/D,7D/W	3.9 Ω	Time [h]	24,25
Toy		Capacity [Ah]	6,68
		Energy [Wh]	7,27
Discharge Type	Load	End Voltage[V]	0.9
2H/D,7D/W	400 mA	Time [h]	11,3
Portable stereo		Capacity [Ah]	4,52
		Energy [Wh]	4,94

No publication or circulation of data to third parties without consent of VARTA Consumer Batteries

* In consideration of typical loss of capacity at storage and application.