



Safety Data Sheet according to Regulation (EC) No 1907/2006

Page 1 of 10

LOCTITE LB 8012 known as Loctite 8012 Moly EDFN_SFDN

SDS No. : 153750
V004.0

Revision: 02.10.2019
printing date: 07.10.2019

Replaces version from: 19.02.2015

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

LOCTITE LB 8012 known as Loctite 8012 Moly EDFN_SFDN

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:

Lubricant

1.3. Details of the supplier of the safety data sheet

Henkel Ltd
Wood Lane End
HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 1442 278000

Fax-no.: +44 1442 278071

ua-productsafety.uk@henkel.com

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

2.2. Label elements

Label elements (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

Supplemental information

Safety data sheet available on request.

2.3. Other hazards

None if used properly.

Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

General chemical description:

Lubricant

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Quartz (SiO ₂), <1% respirable 14808-60-7	238-878-4	1 - < 5 %	

For full text of the H - statements and other abbreviations see section 16 "Other information".

Substances without classification may have community workplace exposure limits available.

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation:

Move to fresh air. If symptoms persist, seek medical advice.

Skin contact:

Rinse with running water and soap.

Obtain medical attention if irritation persists.

Eye contact:

Rinse immediately with plenty of running water (for 10 minutes), seek medical attention from a specialist.

Ingestion:

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Prolonged or repeated contact may cause skin irritation.

Prolonged or repeated contact may cause eye irritation.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media:

Carbon dioxide, foam, powder

Extinguishing media which must not be used for safety reasons:

High pressure waterjet

5.2. Special hazards arising from the substance or mixture

In the event of a fire, carbon monoxide (CO) and carbon dioxide (CO₂) can be released.

Oxides of carbon, oxides of nitrogen, irritating organic vapors.

5.3. Advice for firefighters

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

Additional information:

In case of fire, keep containers cool with water spray.

SECTION 6: Accidental release measures**6.1. Personal precautions, protective equipment and emergency procedures**

Avoid skin and eye contact.
Ensure adequate ventilation.

6.2. Environmental precautions

Do not empty into drains / surface water / ground water.

6.3. Methods and material for containment and cleaning up

For small spills wipe up with paper towel and place in container for disposal.
For large spills absorb onto inert absorbent material and place in sealed container for disposal.
Dispose of contaminated material as waste according to Section 13.

6.4. Reference to other sections

See advice in section 8

SECTION 7: Handling and storage**7.1. Precautions for safe handling**

Use only in well-ventilated areas.
Vapours should be extracted to avoid inhalation.
Prolonged or repeated skin contact should be avoided
Avoid skin and eye contact.
See advice in section 8

Hygiene measures:

Wash hands before work breaks and after finishing work.
Do not eat, drink or smoke while working.

7.2. Conditions for safe storage, including any incompatibilities

Store in a cool, well-ventilated place.
Keep away from heat and direct sunlight.
Refer to Technical Data Sheet

7.3. Specific end use(s)

Lubricant

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational Exposure Limits

Valid for
Great Britain

Ingredient [Regulated substance]	ppm	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
Molybdenum disulphide 1317-33-5 [MOLYBDENUM COMPOUNDS (AS MO), INSOLUBLE COMPOUNDS]		10	Time Weighted Average (TWA):		EH40 WEL
Molybdenum disulphide 1317-33-5 [MOLYBDENUM COMPOUNDS (AS MO), INSOLUBLE COMPOUNDS]		20	Short Term Exposure Limit (STEL):		EH40 WEL
Quartz (SiO ₂) 14808-60-7 [SILICA, RESPIRABLE CRYSTALLINE]		0,1	Time Weighted Average (TWA):		EH40 WEL
Quartz (SiO ₂) 14808-60-7 [RESPIRABLE CRYSTALLINE SILICA DUST, RESPIRABLE FRACTION]		0,1	Time Weighted Average (TWA):		EU OELIII

Occupational Exposure Limits

Valid for
Ireland

Ingredient [Regulated substance]	ppm	mg/m ³	Value type	Short term exposure limit category / Remarks	Regulatory list
Molybdenum disulphide 1317-33-5 [MOLYBDENUM AND INSOLUBLE COMPOUNDS (AS MO), INHALABLE FRACTION]		10	Time Weighted Average (TWA):		IR_OEL
Molybdenum disulphide 1317-33-5 [MOLYBDENUM AND INSOLUBLE COMPOUNDS (AS MO), RESPIRABLE FRACTION]		3	Time Weighted Average (TWA):		IR_OEL
Quartz (SiO ₂) 14808-60-7 [QUARTZ, RESPIRABLE DUST (SEE CRYSTALLINE SILICA)]		0,1	Time Weighted Average (TWA):		IR_OEL
Quartz (SiO ₂) 14808-60-7 [RESPIRABLE CRYSTALLINE SILICA DUST, RESPIRABLE FRACTION]		0,1	Time Weighted Average (TWA):		EU OELIII
Distillates (petroleum), hydrotreated heavy naphthenic 64742-52-5 [MINERAL OIL, PURE, HIGHLY & SEVERELY REFINED, INHALABLE FRACTION]		5	Time Weighted Average (TWA):		IR_OEL
Distillates (petroleum), hydrotreated light naphthenic < 3% DMSO 64742-53-6 [MINERAL OIL, PURE, HIGHLY & SEVERELY REFINED, INHALABLE FRACTION]		5	Time Weighted Average (TWA):		IR_OEL

Biological Exposure Indices:

None

8.2. Exposure controls:

Engineering controls:
Ensure good ventilation/extraction.

Respiratory protection:
Ensure adequate ventilation.
An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area
Filter type: A (EN 14387)

Hand protection:
Chemical-resistant protective gloves (EN 374).
Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374):
nitrile rubber (NBR; \geq 0.4 mm thickness)
Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):
nitrile rubber (NBR; \geq 0.4 mm thickness)
This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:
Wear protective glasses.
Protective eye equipment should conform to EN166.

Skin protection:
Wear suitable protective clothing.
Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

Advices to personal protection equipment:

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions. Personal protective equipment should conform to the relevant EN standard.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Appearance	paste
Odor	grey
Odour threshold	mild
	No data available / Not applicable
pH	Not applicable
Melting point	No data available / Not applicable
Solidification temperature	No data available / Not applicable
Initial boiling point	No data available / Not applicable
Flash point	160 °C (320 °F)
Evaporation rate	No data available / Not applicable
Flammability	No data available / Not applicable
Explosive limits	No data available / Not applicable
Vapour pressure	No data available / Not applicable
Relative vapour density:	No data available / Not applicable
Density	1,9614 g/cm ³
()	
Bulk density	No data available / Not applicable

Solubility	No data available / Not applicable
Solubility (qualitative) (Solvent: Water)	Slight
Partition coefficient: n-octanol/water	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Decomposition temperature	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Oxidising properties	No data available / Not applicable

9.2. Other information

No data available / Not applicable

SECTION 10: Stability and reactivity

10.1. Reactivity

Reacts with strong oxidants.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

No decomposition if used according to specifications.

10.5. Incompatible materials

See section reactivity.

10.6. Hazardous decomposition products

Irritating organic vapours.

SECTION 11: Toxicological information

General toxicological information:

Prolonged or repeated contact may cause skin irritation.

Prolonged or repeated contact may cause eye irritation.

11.1. Information on toxicological effects**Acute oral toxicity:**

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
Quartz (SiO ₂), <1% respirable 14808-60-7	LD50	> 5.050 mg/kg	rat	not specified

Acute dermal toxicity:

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
Quartz (SiO ₂), <1% respirable 14808-60-7	LD50	> 2.000 mg/kg	not specified	not specified

Acute inhalative toxicity:

No data available.

Skin corrosion/irritation:

No data available.

Serious eye damage/irritation:

No data available.

Respiratory or skin sensitization:

No data available.

Germ cell mutagenicity:

No data available.

Carcinogenicity

No data available.

Reproductive toxicity:

No data available.

STOT-single exposure:

No data available.

STOT-repeated exposure::

No data available.

Aspiration hazard:

No data available.

SECTION 12: Ecological information

General ecological information:

Do not empty into drains / surface water / ground water.

12.1. Toxicity

Toxicity (Fish):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Quartz (SiO ₂), <1% respirable 14808-60-7	LC50	> 1.000 mg/l			OECD Guideline 203 (Fish, Acute Toxicity Test)

Toxicity (Daphnia):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Quartz (SiO ₂), <1% respirable 14808-60-7	EC50	> 1.000 mg/l		Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)

Chronic toxicity to aquatic invertebrates

No data available.

Toxicity (Algae):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Quartz (SiO ₂), <1% respirable 14808-60-7	EC50	> 1.000 mg/l			OECD Guideline 201 (Alga, Growth Inhibition Test)

Toxicity to microorganisms

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Quartz (SiO ₂), <1% respirable 14808-60-7	EC0	> 1.000 mg/l		not specified	not specified

12.2. Persistence and degradability

The product is not biodegradable.

No substance data available.

12.3. Bioaccumulative potential

No data available.

No substance data available.

12.4. Mobility in soil

Cured adhesives are immobile.

No substance data available.

12.5. Results of PBT and vPvB assessment

Hazardous substances CAS-No.	PBT / vPvB
Quartz (SiO ₂), <1% respirable 14808-60-7	According to Annex XIII of regulation (EC) 1907/2006 a PBT and vPvB assessment shall not be conducted for inorganic substances.

12.6. Other adverse effects

No data available.

SECTION 13: Disposal considerations**13.1. Waste treatment methods**

Product disposal:

Dispose of in accordance with local and national regulations.

Disposal of uncleaned packages:

Disposal must be made according to official regulations.

Waste code

08 04 09 waste adhesives and sealants containing organic solvents and other dangerous substances

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

SECTION 14: Transport information**14.1. UN number**

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.2. UN proper shipping name

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.3. Transport hazard class(es)

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.4. Packing group

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.5. Environmental hazards

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.6. Special precautions for user

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

not applicable

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

VOC content < 3 %
(2010/75/EC)

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

SECTION 16: Other information**Further information:**

This Safety Data Sheet has been produced for sales from Henkel to parties purchasing from Henkel, is based on Regulation (EC) No 1907/2006 and provides information in accordance with applicable regulations of the European Union only. In that respect, no statement, warranty or representation of any kind is given as to compliance with any statutory laws or regulations of any other jurisdiction or territory other than the European Union. When exporting to territories other than the European Union, please consult with the respective Safety Data Sheet of the concerned territory to ensure compliance or liaise with Henkel's Product Safety and Regulatory Affairs Department (ua-productsafety.de@henkel.com) prior to export to other territories than the European Union.

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

Dear Customer,

Henkel is committed to creating a sustainable future by promoting opportunities along the entire value chain. If you would like to contribute by switching from a paper to the electronic version of SDS, please contact the local Customer Service representative. We recommend to use a non-personal email address (e.g. SDS@your_company.com).

Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.