




Type Designation	4706
Designation IEC	LR6
System	Zn-MnO ₂ (Alkaline)
Shelf Life (Coding)*	10 years
Nominal Voltage [V]	1.5
Typical Capacity C [mAh]	2980 (discharge with high-resistance)
Permissible Temperature Range	- 20 °C ... 50 °C
Weight, approx. [g]	23,8
Volume [ccm]	7.5

Dimensions [mm]

min: max:

Ø	13.7	14.5
A	-	50.5
B	49.5	-
C	7.0	-
E	-	0.5
F	-	5.5
G	1.0	-

Typical Capacities (at 20°C):



Discharge Type	Load	End Voltage[V]	0.9
1H/D, 7D/W	250 mA	Time [h]	9,4
Toy, non motorized		Capacity [Ah]	2,36
		Energy [Wh]	2,84
Discharge Type	Load	End Voltage[V]	1.05
2S/28S, 5M/H	1500 mW/650mW	Pulse [n]	125
Digital Still Camera		Capacity [mAh]	570
		Energy [mWh]	735
Discharge Type	Load	End Voltage[V]	0.9
4M/H, 8H/D, 7D/W	3,9 Ω	Time [min]	491
Portable Lighting		Capacity [Ah]	2,51
		Energy [Wh]	3,01

No publication or circulation of data to third parties without consent of VARTA Consumer Batteries

* In consideration of typical loss of capacity at storage and application.