

Flachsteckhülsen und Stecker

DIN 46247, Teil 2

Clips femelles plats et fiches

DIN 46247, partie 2

Flat receptacles and tabs

DIN 46247, part 2

4,8 mm

BZ = Bronze
MS = Messing

BZ = bronze
MS = laiton

BZ = bronze
MS = brass

Strombelastbarkeit:
0.5 - 1.0 mm² / 10 A max.
1.5 - 2.5 mm² / 15 A max.

Intensité admissible:
0.5 - 1.0 mm² / 10 A max.
1.5 - 2.5 mm² / 15 A max.

Current carrying capacity:
0.5 - 1.0 mm² / 10 A max.
1.5 - 2.5 mm² / 15 A max.


Oberflächenbehandlung: Code
bl = blank (0)
ag = versilbert (1)
au = vergoldet (2)
ni = vernickelt (5)
sn = reinverzinkt (7)

Traitements de surface: Code
bl = brut (0)
ag = argenté (1)
au = doré (2)
ni = nickelé (5)
sn = étamage pur (7)

Surface-plating: Code
bl = clean (0)
ag = silver-plated (1)
au = gold-plated (2)
ni = nickel plated (5)
sn = pure tin-plated (7)

Bestellbeispiel:
Exemple de commande:
Example of order:

3800.67
(3800 MS sn)



| mm ² (AWG) | für Steckzungen pour languettes for tabs | Artikel-Nr. Numéro d'article Part-No. | DIN | L1 mm | L2 mm | L3 mm | A1 mm | A2 mm | S mm | Stand- Packg | Werkzeuge Outils Tools |
|--------------------------|--|---|----------|----------|----------|----------|----------|----------|---------|-----------------|------------------------------|
| 0.5-1 (22-18) | 4.8 x 0.5 | 3800.6() MS | 46247/T2 | 15.6 | 6 | 3.8 | 6 | 3.4 | 0.35 | 1000 | 3975B |
| | 4.8 x 0.8 | 3801.6() MS | | 15.6 | 6 | 3.8 | 6 | 3.4 | 0.35 | 1000 | 3988N 3984A |
| 1.5-2.5 (16-14) | 4.8 x 0.5 | 3803.6() MS | 46247/T2 | 15.6 | 6 | 3.8 | 6 | 3.4 | 0.35 | 1000 | 3975C |
| | 4.8 x 0.8 | 3805.6() MS | | 15.6 | 6 | 3.8 | 6 | 3.4 | 0.35 | 1000 | 3988N 3984A |
| 0.5-1 (22-18) | 4.8 x 0.8 | 380208.6() MS | | 11.3 | 6 | 3.8 | 8.3 | 3 | 0.35 | 1000 | 3983D |
| 1.5-2.5 (16-14) | 4.8 x 0.8 | 3808.6() MS | | 26.5 | 14.5 | - | 6.5 | 3.5 | 0.38 | 1000 | 3975C 3988N 3984A |

