

Flachsteckhülsen und Stecker

DIN 46247, Teil 2

Clips femelles plats et fiches

DIN 46247, partie 2

Flat receptacles and tabs

DIN 46247, part 2

4,8 mm

BZ = Bronze
MS = Messing

BZ = bronze
MS = laiton

BZ = bronze
MS = brass

Strombelastbarkeit:
0.5 - 1.0 mm² / 10 A max.
1.5 - 2.5 mm² / 15 A max.

Intensité admissible:
0.5 - 1.0 mm² / 10 A max.
1.5 - 2.5 mm² / 15 A max.

Current carrying capacity:
0.5 - 1.0 mm² / 10 A max.
1.5 - 2.5 mm² / 15 A max.


Oberflächenbehandlung: Code
bl = blank (0)
ag = versilbert (1)
au = vergoldet (2)
ni = vernickelt (5)
sn = reinverzinkt (7)

Traitements de surface: Code
bl = brut (0)
ag = argenté (1)
au = doré (2)
ni = nickelé (5)
sn = étamage pur (7)

Surface-plating: Code
bl = clean (0)
ag = silver-plated (1)
au = gold-plated (2)
ni = nickel plated (5)
sn = pure tin-plated (7)

Bestellbeispiel:
Exemple de commande:
Example of order:

3800.67
(3800 MS sn)



mm ² (AWG)	für Steckzungen pour languettes for tabs	Artikel-Nr. Numéro d'article Part-No.	DIN	L1 mm	L2 mm	L3 mm	A1 mm	A2 mm	S mm	Stand- Packg	Werkzeuge Outils Tools
0.5-1 (22-18)	4.8 x 0.5	3800.6() MS	46247/T2	15.6	6	3.8	6	3.4	0.35	1000	3975B 3988N 3984A
	4.8 x 0.8	3801.6() MS		15.6	6	3.8	6	3.4	0.35	1000	
1.5-2.5 (16-14)	4.8 x 0.5	3803.6() MS	46247/T2	15.6	6	3.8	6	3.4	0.35	1000	3975C 3988N 3984A
	4.8 x 0.8	3805.6() MS		15.6	6	3.8	6	3.4	0.35	1000	
0.5-1 (22-18)	4.8 x 0.8	380208.6() MS		11.3	6	3.8	8.3	3	0.35	1000	3983D
1.5-2.5 (16-14)	4.8 x 0.8	3808.6() MS		26.5	14.5	-	6.5	3.5	0.38	1000	3975C 3988N 3984A

