

KERN IFS 10K-3M



Industrial counting scale with convenient decimal keypad for easy data entry, counting resolution 75.000 points, verification optional



Display digit height - smallest digit	13,5 mm
Display digit height	16,5 mm

Construction

Dimensions completely mounted (W×D×H)	695×420×230 mm
Dimension display device (W×D×H)	260×150×65 mm
Dimensions weighing surface (W×D)	300×240 mm
Dimensions weighing surface	300×240 mm
Dimensions weighing platform (W×D×H)	300×240×110 mm
Material weighing plate	stainless steel
Material platform	mild steel
Material display housing	plastic
Material load cell(s)	aluminium
Level indicator	✓
Levelling feet adjustable	✓
Stand height	330 mm
Stand inclinable	✓
Wall mount	✓
Transport safety lock - bolt torque	0,1 Nm
Cable length	2,5 m
Display device cable length	3 m
Load cells - number	1

Functions

PreTare function	✓
Sum memory function	✓
Recipe/summing level	Sum A
PLU - total	100
Tolerance weighing	✓
Tolerance weighing - type of signal	acoustically visual
Counting function	✓
Counting resolution (laboratory conditions)	75.000
Counting reference weight can be entered	✓
Smallest piece weight when piece counting - laboratory conditions	200 mg
Smallest piece weight when piece counting - normal conditions	2 g
Reference quantity	n (any number of pieces)
IP protection - complete device	-
IP protection - display	no IP protection
IP protection - platform	no IP protection
IP protection - load cell	IP65

Category

Brand	KERN
Product category	Industrial scale
Product group	Counting scale
Product family	IFS

Measuring System

Weighing system	Strain gauge
Weighing capacity [Max]	6 kg; 15 kg
Readability [d]	0,002 kg; 0,005 kg
Reproducibility	0,002 kg; 0,005 kg
Linearity	± 0,002 kg; 0,005 kg
Minimum weight [Min]	0,04 kg; 0,1 kg
Resolution	3.000, 3.000
Tare range	15 kg
Adjustment options	Adjusting with external weight
Recommended adjusting weight	15 kg (M1)
Stabilization time	2 s
Warm-up time	10 min; 10 min
Eccentric loading at 1/3 [Max]	0,002 kg; 0,005 kg
Load cell connection	4-wire
Units (if device is conformity assessed)	kg
Construction type of the scale	Multi-range balance
Units	kg
Default unit	kg
Loadcell type	ZEMIC L6D

Display

Display type	LCD
Display backlight	✓

KERN IFS 10K-3M



Industrial counting scale with convenient decimal keypad for easy data entry, counting resolution 75.000 points, verification optional

Peak function	✓
Memory function	✓
Auto-off interval(s) in battery mode/rechargeable battery mode	3 min off
Auto-off interval(s) in mains power mode	off
Tare function	manual (multi)
Number of keys for operation	21

Interface

Interfaces	RS-232 standard
------------	-----------------

Power Supply

Supplied power supply	Power supply unit
Power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH
Power supply - Cable length	180 cm
Input voltage power supply / power [Max]	100 - 240 V~ 50/60 Hz 190 mA
Power supply cable removable	removable
Input voltage device / power [Max]	12 V, 500 mA
Power socket for mains adapter	Hollow plug, inside plus, Ø outside 5,5 mm, Ø inside 2,1 mm, long 9,5 mm
Battery / accumulator type	Pb
Rechargeable battery	6 V, 1.2 Ah
Rechargeable battery operating time - backlight on	8 h
Rechargeable battery operating time - backlight off	18 h
Rechargeable battery charging time	12 h
Rechargeable battery optional	Rchrg. battery optional (factory)

Environmental conditions

Ambient temperature [Min]	-10 °C
Ambient temperature [Max]	40 °C
Humidity of environment [Max]	80 %
Storage temperature [Min]	-20 °C
Storage temperature [Max]	60 °C

Approval

CE mark	✓
Conformity assessment possible ex works	✓
Accuracy classe	III
Verification scale interval [e]	0,002 kg; 0,005 kg

Services (optional)

Article number for adjustment at the location of installation	961-248
Article number for conformity assessment	965-228
Article number for DAkkS calibration	963-128
Article number for certificate of conformity	969-517

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	695×405×220 mm
Shipping method	Parcel service
Net weight approx.	4,8 kg
Gross weight approx.	7 kg
Shipping weight	12,4 kg

Product information

GTIN/EAN number	4045761150997
REACH classification	no prohibited substances

Pictograms

STANDARD



OPTION



FACTORY

