# Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

**Supplier's name or trade mark:** LIGHTME

**Supplier's address:** IDV GmbH LIGHTME-Confirmation-Management, Birkenweiherstraße 2, 63505 Langenselbold, DE

**Model identifier:** LM85166-2

**Type of light source:**

| | | | |
|---|---|---|---|
| Lighting technology used: | LED | Non-directional or directional: | NDLS |
| Light source cap-type (or other electric interface) | E27 | | |
| Mains or non-mains: | MLS | Connected light source (CLS): | Nein |
| Colour-tuneable light source: | Nein | Envelope: | - |
| High luminance light source: | Nein | | |
| Anti-glare shield: | Nein | Dimmable: | No |


**Product parameters**

| Parameter | Value | Parameter | Value |
|---|---|---|---|
| **General product parameters:** | | | |
| Energy consumption in on-mode (kWh/1000 h), rounded up to the nearest integer | 9 | Energy efficiency class | F |
| Useful luminous flux (ϕuse), indicating if it refers to the flux in a sphere (360º), in a wide cone (120º) or in a narrow cone (90º) | 810 in Sphere (360°) | Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set | 2 700 |
| On-mode power ($P_{on}$), expressed in W | 8,5 | Standby power ($P_{sb}$), expressed in W and rounded to the second decimal | - |
| Networked standby power ($P_{net}$) for CLS, expressed in W and rounded to the second decimal | - | Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set | 80 |
| Outer dimensions — Height | 115 | Spectral power distribution in the | See image in last page |
| Outer dimensions — Width | 60 | | |

| | | | | |
|---|---|---|---|---|
| without separate control gear, lighting control parts and non-lighting control parts, if any (millimetre) | Depth | 60 | range 250 nm to 800 nm, at full-load | |
| Claim of equivalent power[(a)] | | Ja | If yes, equivalent power (W) | 60 |
| | | | Chromaticity coordinates (x and y) | 0,463<br>0,420 |
| **Parameters for LED and OLED light sources:** | | | | |
| R9 colour rendering index value | | - | Survival factor | 0,50 |
| the lumen maintenance factor | | 0,70 | | |
| **Parameters for LED and OLED mains light sources:** | | | | |
| displacement factor (cos ϕ1) | | 0,50 | Colour consistency in McAdam ellipses | 6 |
| Claims that an LED light source replaces a fluorescent light source without integrated ballast of a particular wattage. | | -[(b)] | If yes then replacement claim (W) | - |
| Flicker metric (Pst LM) | | 1,0 | Stroboscopic effect metric (SVM) | 0,9 |

[(a)] '-' : not applicable;

[(b)] '-' : not applicable;


380
480
580
680
780