

**DEUTSCH**

**Sehr geehrte Kundin, sehr geehrter Kunde,**

wir freuen uns, dass Sie sich für ein Produkt unseres Sortimentes entschieden haben. Unser Name steht für hochwertige und eingehend geprüfte Qualitätsprodukte aus den Bereichen Wärme, Gewicht, Blutdruck, Körpertemperatur, Puls, Sanfte Therapie, Massage, Beauty, Baby und Luft. Bitte lesen Sie diese Gebrauchsanweisung aufmerksam durch, bewahren Sie sie für späteren Gebrauch auf, machen Sie sie anderen Benutzern zugänglich und beachten Sie die Hinweise. Mit freundlicher Empfehlung Ihr Beurer-Team

- 1. Lieferumfang**  
1x PO 40 Pulsoximeter, 2x 1,5 V AAA Batterien , 1x Umhängeband, 1x Gürteltasche, 1x Diese Gebrauchsanweisung

**2. Bestimmungsgemäße Verwendung**

Verwenden Sie das Beurer Pulsoximeter PO 40 ausschließlich am Menschen zur Messung der arteriellen Sauerstoffsättigung (SpO<sub>2</sub>) des Hämoglobins, der Herzfrequenz (PRbpm) und des Pulsmodulationsindex (PMI). Das Pulsoximeter eignet sich sowohl zur Verwendung im privaten Umfeld (zu Hause) als auch im medizinischen Bereich (Krankenhäusern, medizinischen Einrichtungen).

**3. Zum Kennenlernen**

Das Beurer Pulsoximeter PO 40 dient der nichtinvasiven Messung der arteriellen Sauerstoffsättigung (SpO<sub>2</sub>), der Herzfrequenz (PRbpm) und des Pulsmodulationsindex (PMI). Die **Sauerstoffsättigung** gibt an, wie viel Prozent des Hämoglobins im arteriellen Blut mit Sauerstoff beladen sind. Daher ist sie ein wichtiger Parameter für die Beurteilung der Atemfunktion. Das Pulsoximeter verwendet hierfür zur Messung zwei Lichtstrahlen unterschiedlicher Wellenlänge, die im Gehäuseinneren auf den eingelegten Finger auftreffen. Einem niedrigen Sauerstoffsättigungswert liegen überwiegend Erkrankungen (Atemwegserkrankungen, Asthma, Herzinsuffizienz etc.) zu Grunde. Bei Menschen mit einem niedrigen Sauerstoffsättigungswert kommt es vermehrt zu folgenden Symptomen: Atemnot, Herzfrequenzerhöhung, Leistungsabfall, Nervosität und Schweißausbrüche. Eine chronische und bekannte erniedrigte Sauerstoffsättigung benötigt eine Überwachung durch Ihr Pulsoximeter unter ärztlicher Kontrolle. Eine akut erniedrigte Sauerstoffsättigung, mit oder ohne Begleitsymptome, ist sofort ärztlich abzuklären, es kann sich dabei um eine lebensbedrohliche Situation handeln. Das Pulsoximeter eignet sich daher insbesondere für Risikopatienten wie Personen mit Herzerkrankungen, Asthmatiker, aber auch für Sportler und gesunde Personen, die sich in großen Höhen bewegen (z.B. Bergsteiger, Skifahrer oder Sportflieger).

**Merkmale des Pulsoximeters**

- Einfach zu bedienen und leicht zu transportieren (ideal auch für unterwegs)
- Kompakte und leichte Bauweise
- Zweifarbiges OLED-Display, Anzeige der Sauerstoffsättigung (SpO<sub>2</sub>), der Pulsfrequenz (PRbpm) und des Pulsmodulationsindex (PMI)
- Einstellbare Displayhelligkeit (1 bis 10)
- 7 Anzeigeformate / Niedrig-Batterianzeige / Abschaltautomatik nach 8 Sekunden, wenn kein Signal empfangen wird

**4. Zeichenerklärung**

In der Gebrauchsanweisung, auf der Verpackung und auf dem Typschild des Geräts werden folgende Symbole verwendet:

	<b>WARNUNG</b> Warnhinweis auf Verletzungsgefahren oder Gefahren für Ihre Gesundheit		Hersteller
	<b>ACHTUNG</b> Sicherheitshinweis auf mögliche Schäden an Gerät/ Zubehör		Anwendungsteil Typ BF
	<b>Hinweis</b> Hinweis auf wichtige Informationen		Schadstoffhaltige Batterien nicht im Hausmüll entsorgen
	Gebrauchsanweisung beachten		Die CE-Kennzeichnung bescheinigt die Konformität mit den grundlegenden Anforderungen der Richtlinie 93/42/EWG für Medizinprodukte.
<b>%SpO<sub>2</sub></b>	Arterielle Sauerstoffsättigung des Hämoglobins (in Prozent)		Herstellungsdatum
<b>PR bpm</b>	Pulsfrequenz (Pulsschläge pro Minute)		Alarmunterdrückung
<b>Storage</b> -20°C RH <=93%	Zulässige Lagerungstemperatur und- luftfeuchtigkeit		Geschützt gegen Fremdkörper ≥ 12,5 mm und gegen schräges Tropfwasser
<b>Operating</b> 10°C RH 15-93%	Zulässige Betriebstemperatur und- luftfeuchtigkeit		Entsorgung gemäß Elektro- und Elektronik-Altgeräte EG-Richtlinie WEEE (Waste Electrical and Electronic Equipment)
<b>SN</b>	Seriennummer		

**5. Warn- und Sicherheitshinweise**

Ein Nichtbeachten der nachfolgenden Hinweise kann Personen- oder Sachschäden verursachen. Bewahren Sie die Gebrauchsanweisung auf und machen Sie diese auch anderen Anwendern zugänglich. Übergeben Sie diese Gebrauchsanweisung bei Weitergabe des Geräts.

**⚠ WARNUNG**

- Überprüfen Sie, ob alle im Lieferumfang angegebenen Teile enthalten sind.
- Überprüfen Sie das Pulsoximeter regelmäßig, um sicherzustellen, dass das Gerät vor dem Gebrauch keine sichtbaren Schäden aufweist und die Batterien noch ausreichend geladen sind. Benutzen Sie es im Zweifelsfall nicht und wenden Sie sich an den Beurer-Kundendienst oder an einen autorisierten Händler.
- Benutzen Sie keine Zusatzteile, die nicht vom Hersteller empfohlen bzw. als Zubehör angeboten werden.
- Sie dürfen das Gerät keinesfalls öffnen oder reparieren, da sonst eine einwandfreie Funktion nicht gewährleistet werden kann. Bei Nichtbeachten erlischt die Garantie. Wenden Sie sich bei Reparaturen an den Beurer-Kundendienst oder an einen autorisierten Händler.

Verwenden Sie das Pulsoximeter


- NICHT, wenn Sie allergisch auf Gummiprodukte reagieren.
- NICHT, wenn das Gerät oder der Anwendungsfinger feucht ist.
- NICHT an Kleinkindern oder Säuglingen.
- NICHT während einer MRT- oder CT-Untersuchung.
- NICHT während eines Patiententransports außerhalb einer medizinischen Einrichtung.
- NICHT während einer Blutdruckmessung auf der Armseite mit Manschettenanwendung.
- NICHT an Fingern mit Nagellack, Beschmutzungen oder Pflasterverbänden.
- NICHT an Fingern mit großer Fingerdicke, die nicht zwanglos in das Gerät einführbar sind (Fingerspitze: Breite ca. > 20 mm, Dicke ca. > 15 mm)
- NICHT an Fingern mit anatomischen Veränderungen, Ödemen, Narben oder Verbrennungen.
- NICHT an Fingern mit geringer Dicke und Breite, wie sie zum Beispiel bei Kleinkindern vorkommen (Breite ca. < 10 mm, Dicke ca. < 5 mm).
- NICHT an Patienten, die am Anwendungsort unruhig sind (z.B. Zittern).
- NICHT in der Nähe von brennbaren oder explosiven Gasgemischen.

- Bei Personen mit Durchblutungsstörungen kann eine längere Benutzung des Pulsoximeters zu Schmerzen führen. Verwenden Sie daher das Pulsoximeter nicht länger als 30 Minuten an einem Finger. Nur so kann eine korrekte Sensorausrichtung und Unversehrtheit der Haut gewährleistet werden.
- Das Pulsoximeter zeigt jeweils einen momentanen Messwert, kann aber nicht für eine kontinuierliche Überwachung verwendet werden.
- Das Pulsoximeter verfügt über keine Alarmpunktion und eignet sich daher nicht zur Bewertung medizinischer Ergebnisse.
- Führen Sie aufgrund der Messergebnisse keine Selbstdiagnose oder -behandlung ohne Rücksprache mit Ihrem behandelnden Arzt durch. Setzen Sie insbesondere nicht eigenmächtig eine neue Medikation an und führen Sie keine Änderungen in Art und / oder Dosierung einer bestehenden Medikation durch.
- Schauen Sie während des Messvorgangs nicht direkt in das Gehäuseinneres. Das Rotlicht und das unsichtbare Infrarot-Licht des Pulsoximeters sind schädlich für die Augen.
- Dieses Gerät ist nicht dafür bestimmt, durch Personen (einschließlich Kinder) mit eingeschränkten physischen, sensorischen oder geistigen Fähigkeiten oder mangels Erfahrung und/oder mangels Wissen benutzt zu werden, es sei denn, sie werden durch eine für Ihre Sicherheit zuständige Person beaufsichtigt oder erhalten von ihr Anweisungen, wie das Gerät zu benutzen ist. Kinder sollten beaufsichtigt werden, damit sie nicht mit dem Gerät spielen.
- Die Anzeige der Pulsweite sollte der Pulsäule, erlauben keine Abschätzung über die Puls- oder Durchblutungsstärke am Messort, sondern dienen ausschließlich der Darstellung der aktuellen optischen Signalvarianz am Messort, sie ermöglichen jedoch nicht eine sichere Pulsdiagnostik.

**Bei Nichtbeachtung der nachfolgenden Anweisungen kann es zu fehlerhaften Messungen oder Messversagen kommen:**

- Auf dem Messfinger darf sich kein Nagellack, Kunstnagel oder andere Kosmetika befinden.
- Achten Sie beim Messfinger darauf, dass der Fingernagel so kurz ist, dass die Fingerbeere die Sensorelemente im Gehäuse bedeckt.
- Wenn sich Personen während des Messvorgangs bewegen. Halten Sie Hand, Finger und Körper während des Messvorgangs ruhig.
- Bei Personen mit Herzrhythmusstörungen können die Messwerte der Sauerstoffsättigung (SpO<sub>2</sub>) und der Herzfrequenz (PRbpm) verfälscht sein oder die Messung ist gar nicht erst möglich.
- Bei Verwendung von Elektrochirurgiegeräten oder Defibrillatoren kann die Funktionalität des Pulsoximeters beeinträchtigt werden.
- Das Pulsoximeter zeigt im Falle von Kohlenmonoxidvergiftungen zu hohe Messwerte an.
- Um das Messergebnis nicht zu verfälschen, sollte sich in der unmittelbaren Umgebung des Pulsoximeters keine starke Lichtquelle (z.B. Leuchtstofflampe oder direkte Sonneneinstrahlung) befinden.
- Bei Personen, die einen niedrigen Blutdruck haben, unter Gelbsucht leiden, Medikamente zur Gefäßkontraktion einnehmen oder eine niedrige Blut kann es zu fehlerhaften oder verfälschten Messungen kommen.
- Bei Patienten, denen in der Vergangenheit klinische Farbstoffe verabreicht wurden und bei Patienten mit abnormalem Hämoglobinvorkommen ist mit einer Messverfälschung zu rechnen. Dies gilt insbesondere bei Kohlenmonoxidvergiftungen und Methämoglobinvergiftungen, welche z.B. durch die Zugabe von Lokalanästhetika oder bei vorliegendem Methämoglobinreduktase-Mangel entstehen.
- Bei Patienten mit arteriellem Katheter, Hypotonie, starken Gefäßverengungen, Blutarmut oder Unterkühlungen kann es zu Messversagen kommen.
- Schützen Sie das Pulsoximeter vor Staub, Erschütterungen, Nässe, extremen Temperaturen und explosiven Stoffen.

**6. Gerätebeschreibung**




**Display-Anzeigeformate (7 verschiedene)**




**7.1 Inbetriebnahme**

**7.1 Batterien einlegen**




**7.2 Umhängeband befestigen**

Sie können zum einfacheren Transport des Pulsoximeters (z.B. für unterwegs) ein Umhängeband am Gerät befestigen.



**8. Bedienung**



**ⓘ Hinweis**

- Erscheint auf dem Display dieses Symbol , bedeutet dies, dass das Messsignal instabil ist. Die angezeigten Messwerte sind ungültig.
- Wenn Sie Ihren Finger aus dem Pulsoximeter herausziehen, schaltet sich das Gerät nach ca. 8 Sekunden automatisch aus.
- Um Ihr gewünschtes Display-Anzeigeformat einzustellen, drücken Sie während des Betriebs kurz die Funktionstaste.
- Um Ihre gewünschte Display-Helligkeit einzustellen, halten Sie während des Betriebs die Funktionstaste länger gedrückt.

**9. Messergebnisse beurteilen**

	<b>WARNUNG</b> Die nachfolgende Tabelle zur Beurteilung Ihres Messergebnisses gilt NICHT für Personen mit bestimmten Vorerkrankungen (z.B. Asthma, Herzinsuffizienz, Atemwegserkrankungen) und bei Aufenthalt in Höhenlagen über 1500 Metern. Wenn Sie unter Vorerkrankungen leiden, wenden Sie sich zur Beurteilung Ihrer Messwerte immer an Ihren Arzt.
<b>Messergebnis SpO<sub>2</sub> (Sauerstoffsättigung) in %</b>	<b>Einstufung / Zu treffende Maßnahmen</b>
99-94	Normalbereich
94-90	Erniedrigter Bereich: Arztbesuch empfohlen
< 90	Kritischer Bereich: Dringend Arzt aufsuchen

**Pulsmodulationsindex beurteilen**

Der Pulsmodulationsindex (PMI) kann zwischen 0,3% und 20% liegen. Er schwankt je nach Patient, Messort und körperlichem Zustand. Ein sehr geringer PMI-Wert kann die Messung beeinträchtigen.

**Höhenabhängiger Sauerstoffsättigungabfall**

	<b>Hinweis</b> Die nachfolgende Tabelle informiert Sie über die Auswirkungen unterschiedlicher Höhenlagen auf den Sauerstoffsättigungswert sowie deren Folgen für den menschlichen Organismus. Die nachfolgende Tabelle gilt NICHT für Personen mit bestimmten Vorerkrankungen (z.B. Asthma, Herzinsuffizienz, Atemwegserkrankungen etc.). Bei Personen mit Vorerkrankungen können Krankheits Symptome (z.B. Hypoxie) bereits in niedrigeren Höhenlagen auftreten.	
<b>Höhenlage</b>	<b>Zu erwartender SpO<sub>2</sub>-Wert (Sauerstoffsättigung) in %</b>	<b>Folgen für den Menschen</b>
1500-2500 m	> 90	Keine Höhenkrankheit (in der Regel)
2500-3500 m	-90	Höhenkrankheit, Anpassung empfohlen
3500-5800 m	<-90	Sehr häufiges Auftreten einer Höhenkrankheit, Anpassung zwingend erforderlich
5800-7500 m	<-80	Schwere Hypoxie, nur zeitlich begrenzter Aufenthalt möglich
7500-8850 m	<-70	Sofortige akute Lebensgefahr

Quelle: Hackett PH, Roach RC: High-Altitude Medicine. In: Auerbach PS (ed): Wilderness Medicine, 3rd edition; Mosby, St.Louis, MO 1995; 1-37.

**10. Reinigung / Instandhaltung**

**⚠ ACHTUNG:**

- **Wenden Sie am Pulsoximeter keine Hochdruck- oder Ethylenoxid-Sterilisation an! Das Gerät ist nicht für Sterilisation geeignet. Halten Sie das Pulsoximeter auf keinen Fall unter Wasser, da sonst Flüssigkeit eindringen kann und das Pulsoximeter beschädigt wird.**
- Reinigen Sie nach jeder Anwendung das Gehäuse und die gummierte Innenfläche des Pulsoximeters mit einem weichen, mit medizinischem Alkohol angefeuchteten Tuch.
- Wenn auf dem Display des Pulsoximeters ein niedriger Batteriestand angezeigt wird, tauschen Sie die Batterien aus.
- Wenn Sie das Pulsoximeter länger als einen Monat nicht benutzen, entnehmen Sie beide Batterien aus dem Gerät, um ein eventuelles Auslaufen der Batterien zu verhindern.

**11. Aufbewahrung**

**⚠ ACHTUNG:**

Bewahren Sie das Pulsoximeter in einer trockenen Umgebung auf (relative Luftfeuchtigkeit ≤93%). Zu hohe Luftfeuchtigkeit kann die Lebensdauer des Pulsoximeters verkürzen oder es beschädigen. Bewahren Sie das Pulsoximeter an einem Ort auf, an dem die Umgebungstemperatur zwischen -20°C und 55°C liegt.

**12. Entsorgung**

Bitte entsorgen Sie das Gerät gemäß der Elektro- und Elektronik Altgeräte EG-Richtlinie – WEEE (Waste Electrical and Electronic Equipment). Bei Rückfragen wenden Sie sich bitte an die für die Entsorgung zuständige kommunale Behörde. Die verbrauchten, vollkommen entladenen Batterien sind über die speziell gekennzeichneten Sammelbehälter, die Sondermüllannahmestellen oder über den Elektrohändler zu entsorgen. Sie sind gesetzlich dazu verpflichtet, die Batterien zu entsorgen. Hinweis: Diese Zeichen finden Sie auf schadstoffhaltigen Batterien: Pb = Batterie enthält Blei, Cd = Batterie enthält Cadmium, Hg = Batterie enthält Quecksilber.

**13. Was tun bei Problemen?**

Problem	Mögliche Ursache	Behebung
„Finger out“ wird auf dem Display angezeigt	Der Messfinger ist nicht korrekt in das Pulsoximeter eingelegt	Legen Sie den Messfinger erneut in das Pulsoximeter ein.
Messwerte werden nicht korrekt angezeigt	Der gemessene SpO <sub>2</sub> ist zu niedrig (<70%)  starke Lichtquelle (z.B. Leuchtstofflampe oder direkte Sonneneinstrahlung) befindet sich in der Nähe	Messung erneut durchführen. Sollte Problem mehrmals auftauchen und das Gerät in einwandfreiem Zustand sein, unbedingt einen Arzt aufsuchen.  Pulsoximeter von starken Lichtquellen fernhalten.
Pulsoximeter zeigt Messunterbrechungen oder hohe Messwertsprünge	Unzureichende Durchblutung des Messfingers	Warn- und Sicherheitshinweise in Kapitel 5 beachten
	Messfinger ist zu groß oder zu klein.	Fingerspitze muss folgende Maße haben: Breite zwischen 10 - 20 mm Dicke zwischen 5 - 15 mm
	Finger, Hand oder Körper befindet sich in Bewegung	Finger, Hand und Körper während der Messung ruhig halten.
Pulsoximeter lässt sich nicht einschalten	Batterien sind leer	Tauschen Sie die Batterien aus
	Batterien sind nicht korrekt eingelegt	Legen Sie die Batterien erneut ein
Anzeigelampen sind plötzlich aus	Das Pulsoximeter ist defekt	Kontaktieren Sie Ihren Händler oder den Kundendienst
	Batterien sind leer	Tauschen Sie die Batterien aus
„Error 3“ wird auf dem Display angezeigt	Die Rotlicht-Empfangs-LED ist defekt	Kontaktieren Sie Ihren Händler oder den Kundendienst
„Error 4“ wird auf dem Display angezeigt	Die Infrarotlicht-Empfangs-LED ist defekt	Kontaktieren Sie Ihren Händler oder den Kundendienst
„Error 6“ wird auf dem Display angezeigt	Das Display ist defekt	Kontaktieren Sie Ihren Händler oder den Kundendienst
„Error 7“ wird auf dem Display angezeigt	Die Empfangs-LEDs sind defekt	Kontaktieren Sie Ihren Händler oder den Kundendienst

**14. Technische Daten**

Modell-Nr.	PO 40
Messmethode	Nicht invasive Messung der arteriellen Sauerstoffsättigung des Hämoglobins, der Pulsfrequenz und des Pulsmodulationsindex am Finger.
Messbereich	SpO <sub>2</sub> (Sauerstoffsättigung): 70 - 100%, Puls: 30 - 250 Schläge/Minute, PMI: 0,3 - 20 %
Genauigkeit	SpO <sub>2</sub> (Sauerstoffsättigung): 70 - 100%, ±2%, Puls: 30 - 250 bpm, ±2 Schläge/Minute PMI: 0,3% - 1%; ±0,2 digits; >1,1% ± 20%
Abmessungen	L 58,4 mm x B 33,5 mm x H 37 mm
Gewicht	Ca. 57 g (einschließlich Batterien)
Sensork zur Messung von SpO <sub>2</sub>	Rotlicht (Wellenlänge 660 nm); Infrarot (Wellenlänge 905 nm); Silizium-Empfangsdiode
Zulässige Betriebsbedingungen	+5 °C bis +40 °C, 15 - 93 % relative Luftfeuchte, 86 - 106 kPa Umgebungsdruck
Zulässige Aufbewahrungsbedingungen	-20 °C bis +55 °C, ≤93 % relative Luftfeuchte, 86 - 106 kPa Umgebungsdruck
Stromversorgung	2x 1,5 V AAA Batterien
Batterie-Lebensdauer	2 AAA Alkaline Batterien ermöglichen ca. 2 Jahre Betrieb bei 1 Messungen pro Tag (je 60 Sekunden).
Klassifikation	IP22, Anwendungsteil Typ BF

Änderungen der technischen Angaben ohne Benachrichtigung sind aus Aktualisierungsgründen vorbehalten.

- Dieses Gerät entspricht der europäischen Norm EN60601-1-2 und unterliegt besonderen Vorsichtsmaßnahmen hinsichtlich der elektromagnetischen Verträglichkeit. Bitte beachten Sie dabei, dass tragbare und mobile HF-Kommunikationseinrichtungen dieses Gerät beeinflussen können. Genauere Angaben können Sie unter der angegebenen Kundenservice-Adresse anfordern oder am Ende der Gebrauchsanweisung nachlesen.
- Das Gerät entspricht der EU-Richtlinie für Medizinprodukte 93/42/EC, dem Medizinproduktegesetz und der Norm DIN EN ISO 80601-2-61 (Medizinisch elektrische Geräte – Besondere Festlegungen für die grundlegende Sicherheit und die wesentlichen Leistungsmerkmale von Pulsoximetern für den medizinischen Gebrauch).

**15. Garantie und Service**

Wir leisten 3 Jahre Garantie für Material- und Fabrikationsfehler des Produktes. Die Garantie gilt nicht:  
 • im Falle von Schäden, die auf unsachgemäßer Bedienung beruhen,  
 • für Verschleißteile,  
 • für Mängel, die dem Kunden bereits beim Kauf bekannt waren,  
 • bei Eigenverschulden des Kunden.  
 Die gesetzlichen Gewährleistungen des Kunden bleiben durch die Garantie unberührt. Für die Geltendmachung eines Garantiefalles innerhalb der Garantiezeit ist durch den Kunden der Nachweis des Kaufes zu führen.  
 Die Garantie ist innerhalb eines Zeitraumes von 3 Jahren ab Kaufdatum gegenüber der Beurer GmbH, Söflinger Straße 218, 89077 Ulm, Germany geltend zu machen. Der Kunde hat im Garantiefall das Recht zur Reparatur der Ware bei unserem eigenen oder bei von uns autorisierten Werkstätten. Weitergehende Rechte werden dem Kunden (aufgrund der Garantie) nicht eingeräumt.

**ENGLISH**

**Dear customer,**

Thank you for choosing one of our products. Our name stands for high-quality, thoroughly tested products for applications in the areas of heat, weight, blood pressure, body temperature, pulse, gentle therapy, massage, beauty, baby and air. Please read these instructions for use carefully and keep them for later use, be sure to make them accessible to other users and observe the information they contain. With kind regards, Your Beurer team

**1. Included in delivery**

- 1x PO 40 pulse oximeter, 2x 1,5 V AAA batteries, 1x lanyard, 1x belt bag, 1x these instructions for use

**2. Intended use**

Only use the Beurer PO 40 pulse oximeter on humans to measure the arterial oxygen saturation (SpO<sub>2</sub>) of haemoglobin, the heart rate (PRbpm) and the pulse modulation index (PMI). The pulse oximeter is suitable for private use (at home) as well as for use in the medical sector (hospitals, medical establishments).

**3. Getting to know your instrument**

The Beurer PO 40 pulse oximeter provides a non-invasive measurement of the arterial oxygen saturation (SpO<sub>2</sub>), the heart rate (pulse rate) (PRbpm) and the pulse modulation index (PMI). **Oxygen saturation** indicates the percentage of haemoglobin in arterial blood that is loaded with oxygen. Therefore it is an important parameter for assessing the respiratory function. To take a measurement, the pulse oximeter uses two rays of light with differing wavelengths, which strike the finger inserted inside the housing. A low oxygen saturation value generally indicates underlying illnesses (respiratory diseases, asthma, heart failure etc.).

People with a low oxygen saturation value are more likely to experience the following symptoms: shortness of breath, increased heart rate, weakness, nervousness and outbursts of sweating. If oxygen saturation is known to be chronically diminished, it requires monitoring using the pulse oximeter under medical supervision. If you have acutely diminished oxygen saturation, with or without the accompanying symptoms, you must consult a doctor immediately as it could lead to a life-threatening situation. The pulse oximeter is particularly suitable for patients at risk such as people with heart disease or asthma, but also for athletes and healthy people who exercise at high altitude (e.g. mountaineers, skiers or amateur pilots).

**Features of the pulse oximeter**

- Easy to use and to take with you (ideal for on the go)
- Compact, lightweight design
- Two-colour OLED display, readings for oxygen saturation (SpO<sub>2</sub>), pulse rate (PRbpm) and pulse modulation index (PMI) are shown
- Adjustable display brightness (1 to 10)
- 7 display formats/low battery indicator/automatic switch-off after 8 seconds if no signal is received

**4. Signs and symbols**

The following symbols are used in these instructions for use, on the packaging and on the type plate for the device:

	<b>WARNING</b> Warning instruction indicating a risk of injury or damage to health		Manufacturer
	<b>IMPORTANT</b> Safety note regarding potential for damage to the device/ accessories		Application part, type BF
	<b>Note</b> Note on important information		Do not dispose of batteries containing hazardous substances with household waste.
	Observe the instructions for use		The CE labelling certifies that the product complies with the essential requirements of Directive 93/42/EEC on medical products.
<b>%SpO<sub>2</sub></b>	Arterial oxygen saturation of haemoglobin (in percent)		Date of manufacture
<b>PR bpm</b>	Pulse rate (beats per minute)		Alarm suppression

	Permissible storage temperature and humidity	<b>IP22</b>	Device protected against foreign objects ≥ 12.5 mm and against falling drops of water
	Permissible operating temperature and humidity		Disposal in accordance with the Waste Electrical and Electronic Equipment EC Directive – WEEE
SN	Serial number		

## 5. Warnings and safety notes

Non-observance of the following information may result in personal injury or material damage. Store these instructions for use and make them accessible to other users. Make sure you include these instructions for use when handing over the device to third parties.

### WARNING

- Check to ensure that the package contains all the parts that should be included in the delivery.
- Check the pulse oximeter regularly before use to ensure that there is no visible damage to the device and the batteries are still sufficiently charged. In case of doubt, do not use the device and contact Beurer customer services or an authorised retailer.
- Do not use any additional parts that are not recommended by the manufacturer or offered as equipment.
- Under no circumstances should you open or repair the device yourself, as faultless functionality could no longer be guaranteed thereafter. Failure to comply will result in voiding of the warranty. For repairs, please contact Beurer customer services or an authorised retailer.

#### Do NOT use the pulse oximeter


- if you are allergic to rubber products.
- if the device or the finger you are using is damp.
- on small children or babies.
- during an MRI or CT scan.
- while transporting a patient other than within a medical establishment.
- whilst taking a blood pressure measurement on the same arm using a cuff.
- on fingers that have nail varnish on, are dirty or have a plaster or other dressing on them.
- on large fingers that do not fit into the device easily (fingertip: width approx. > 20 mm, thickness approx. > 15 mm).
- on fingers with anatomical changes, oedemas, scars or burns.
- on fingers that are too small, as with small children for example (width approx. < 10 mm, thickness < 5 mm).
- on patients who are not steady at the site of application (e.g. trembling).
- near flammable or explosive gas mixtures.

- Using the device for long periods may cause pain for people with circulatory disorders. Therefore do not use the pulse oximeter for longer than 30 minutes on one finger. This is essential to ensure correct sensor orientation and to safeguard the integrity of the skin.
- The pulse oximeter displays an instantaneous measurement but cannot be used for continuous monitoring.
- The pulse oximeter does not have an alarm function and is therefore not suitable for evaluating medical results.
- Do not self-diagnose or self-medicate on the basis of the measurements without consulting your doctor. In particular, do not start taking any new medication or change the type and/or dosage of any existing medication without prior approval.
- Do not look directly inside the housing during the measurement. The red light and the invisible infra-red light in the pulse oximeter are harmful to your eyes.
- This device is not intended for use by people (including children) with restricted physical, sensory or mental skills or a lack of experience and/or a lack of knowledge, unless they are supervised by a person who has responsibility for their safety or they receive instructions from this person on how to use the device. Children should be supervised around the device to ensure they do not play with it.
- The displays for the pulse wave and pulse bar allows the strength of the pulse or circulation to be evaluated at the measurement site. Rather, they are exclusively used to display the current visual signal variation at the measurement site and do not enable reliable diagnostics for the pulse.


#### Non-observance of the following instructions can lead to incorrect or failed measurements:

- There must not be any nail varnish, artificial nails or other cosmetics on the finger to be measured.
- Ensure that the finger nail on the finger to be measured is short enough that the fingertip covers the sensor element in the housing.
- If the person moves while the measurement is being taken. Keep your hand, finger and body steady during the measurement.
- For people with cardiac arrhythmia, the oxygen saturation level (SpO<sub>2</sub>) readings and the heart rate (PRbpm) may be incorrect or the measurement may not be possible at all.
- If an electronic surgical device or defibrillator is used, the functioning of the pulse oximeter may be impaired.
- In cases of carbon monoxide poisoning, the pulse oximeter displays a measurement value that is too high.
- To avoid falsifying the measuring result, there should not be any strong light sources (e.g. fluorescent lamps or direct sunlight) in the immediate vicinity of the pulse oximeter.
- People with low blood pressure, who suffer from jaundice or take medication for vascular contraction may experience incorrect or falsified measurements.
- Incorrect measurements are likely for patients who have been administered medical dye in the past or for those who have abnormal haemoglobin levels. This applies in particular for cases of carbon monoxide poisoning and methaemoglobin poisoning, which can occur for example from the administration of local anaesthetics or from an existing methaemoglobin reductase deficiency.
- The measurement may be falsified in patients with an arterial catheter, hypotension, severe vascular constriction, anaemia or hypothermia.
- Protect the pulse oximeter from dust, shocks, moisture, extreme temperatures and explosive materials.

## 6. Unit description




#### Display formats (7 different formats)




## 7. Initial use

### 7.1 Inserting the batteries




### 7.2 Attaching the lanyard

To transport the pulse oximeter more easily (e.g. whilst on the move) you can attach a lanyard to the device.



## 8. Operation



### Note

- If the symbol appears on the display this indicates that the measurement signal is unstable, and the readings shown are invalid.
- When you remove your finger from the pulse oximeter, the device will automatically switch off after approx. 8 seconds.
- To select your desired display format, hold down the function button briefly during operation.
- To select your desired display brightness, hold down the function button for slightly longer during operation.

## 9. Evaluating measurement results

SpO <sub>2</sub> (oxygen saturation) measurement in %	Classification/measures to be taken
99-94	Normal range
94-90	Decreased range: Visit to the doctor recommended
< 90	Critical range: Seek medical attention urgently

### Evaluating pulse modulation index

The pulse modulation index (PMI) may lie between 0.3% and 20%, and varies depending on the patient, measurement location and state of health. A very low PMI value can impair the measurement.

### Decline in oxygen saturation depending on altitude

#### Note

The following table informs you of the effects of various altitudes on oxygen saturation value and its impact on the human body. The following table does NOT apply to people with certain pre-existing conditions (e.g. asthma, heart failure, respiratory diseases etc.). People with pre-existing conditions can show signs of illness (e.g. hypoxia) at lower altitudes.

Altitude	Expected SpO <sub>2</sub> value (oxygen saturation) in %	Impact on human body
1500-2500 m	> 90	No altitude sickness (normally)
2500-3500 m	~90	Altitude sickness, acclimatisation recommended
3500-5800 m	<90	Very frequent altitude sickness, acclimatisation absolutely essential
5800-7500 m	<80	Severe hypoxia, only limited length of stay possible
7500-8850 m	<70	Immediate, acute danger to life

Source: Hackett PH, Roach RC: High-Altitude Medicine. In: Auerbach PS (ed): Wilderness Medicine, 3rd edition; Mosby, St.Louis, MO 1995; 1-37.

## 10. Maintenance/cleaning

### IMPORTANT:

Do not use high pressure or ethylene oxide sterilisation on the pulse oximeter! The device is not suitable for sterilisation. Under no circumstances should you hold the pulse oximeter under water, as this can cause liquid to enter and damage the pulse oximeter.

- Clean the housing and the interior rubber surface with a soft cloth dampened with medical alcohol after each use.
- If a low battery status appears on the display of the pulse oximeter, change the batteries.
- If you are not going to use the pulse oximeter for more than one month, remove both batteries from the device to avoid possible leaking.

### 11. Storage

#### IMPORTANT:

Store the pulse oximeter in a dry place (relative humidity ≤93%). If the humidity is too high it may shorten the service life of the pulse oximeter or damage it. Store the pulse oximeter in a place where the ambient temperature is between -20°C and 55°C.

### 12. Disposal

Please dispose of the device in accordance with EC Directive – WEEE (Waste Electrical and Electronic Equipment). If you have any questions, please contact the local authorities responsible for waste disposal.

The empty, completely flat batteries should be disposed of through specially designated collection boxes, recycling points or electronics retailers. You are legally required to dispose of the batteries.

Note: The codes below are printed on batteries containing harmful substances: Pb = Battery contains lead, Cd = Battery contains cadmium, Hg = Battery contains mercury.

### 13. What if there are problems?

Problem	Possible cause	Solution
"Finger out" appears on the display	The finger on which the measurement is being taken has not been inserted properly in the pulse oximeter	Insert the finger in the pulse oximeter again
Measurement values are not correctly displayed	The measured SpO <sub>2</sub> is too low (<70%)	Do the measurement again. If the problem occurs repeatedly and the device is functioning properly, seek medical advice as a matter of urgency
	There is a strong light source (e.g. fluorescent lamp or direct sunlight) in the vicinity	Remove pulse oximeter from the vicinity of these light sources
The pulse oximeter is displaying measurement interruptions or high measurement value jumps	Insufficient circulation in the measurement finger	Observe the warnings and safety notes in section 5
	Measurement finger is too large or too small	Fingertip must have the following measurements: Width between 10 and 20 mm Thickness between 5 and 15 mm
	Finger, hand or body is moving	Keep your finger, hand and body still during the measurement.
	Cardiac arrhythmia	Seek medical attention

Problem	Possible cause	Solution
Pulse oximeter will not switch on.	Batteries are flat	Replace the batteries
	The batteries have not been inserted correctly	Reinsert the batteries
	The pulse oximeter is faulty.	Contact the retailer or Customer Services
Indicator light goes out suddenly	The pulse oximeter switches off automatically after 8 seconds if it is not receiving a signal	Switch the pulse oximeter on again using the ON/OFF button.
	Batteries are flat	Replace the batteries
"Error 3" appears on the display	The red light receiving LED is faulty	Contact the retailer or Customer Services
"Error 4" appears on the display	The infrared light receiving LED is faulty	Contact the retailer or Customer Services
"Error 6" appears on the display	The display is faulty.	Contact the retailer or Customer Services
"Error 7" appears on the display	The receiving LEDs are faulty	Contact the retailer or Customer Services

## 14. Technical data

Model no.	PO 40
Measurement method	Non-invasive measurement of arterial oxygen saturation of haemoglobin, pulse rate and pulse modulation index in finger.
Measurement range	SpO <sub>2</sub> (oxygen saturation): 70 - 100%, pulse: 30 - 250 beats/minute PMI: 0.3 - 20 %
Accuracy	SpO <sub>2</sub> (oxygen saturation): 70 - 100%, ± 2%, pulse: 30 - 250 bpm, ± 2 beats/minute PMI: 0.3% - 1%; ±0.2 digits; >1.1% ± 20%
Dimensions	L 58.4 mm x W 33.5 mm x H 37 mm
Weight	Approx. 57 g (including batteries)
Sensor to measure SpO <sub>2</sub>	Red light (wave length 660 nm); infra-red (wave length 905 nm); silicon receiver diode
Permissible operating conditions	+5°C to +40°C, ≤15 - 93% relative humidity, 86 - 106 kPa ambient pressure
Permissible storage conditions	-20°C to +55°C, ≤93% relative humidity, 86 - 106 kPa ambient pressure
Power supply	2 x 1.5V — AAA batteries
Battery life	2 AAA alkaline batteries last for approx. 2 years of operation at 1 measurements per day (each of 60 seconds).
Classification	IP22, application part, type BF

Technical information is subject to change without notification to allow for updates.

- This device complies with European Standard EN60601-1-2 and is subject to particular precautions with regard to electromagnetic compatibility. Please note that portable and mobile HF communication systems may interfere with this unit. More details can be requested from the stated Customer Services address or found at the end of the instructions for use.
- This device complies with EU Directive 93/42/EC concerning medical devices, the Medizinproduktegesetz (German Medical Devices Act) and the DIN EN ISO 80601-2-61 standard (Medical electrical equipment – Particular requirements for the basic safety and essential performance of pulse oximeter equipment for medical use).

## Guidance and manufacture's declaration-electromagnetic emission for all EQUIPMENT and SYSTEMS

Guidance and manufacture's declaration –electromagnetic emission		
The PO40 Pulse Oximeter is intended for use in the electromagnetic environment specified below. The customer of the user of the PO40 Pulse Oximeter should assure that it is used in such an environment.		
Emission test	compliance	Electromagnetic environment-guidance
RF emissions CISPR 11	Group 1	The PO40 Pulse Oximeter uses RF energy only for their internal function. Therefore, its RF emissions are very low and are not likely to cause any interference in nearby electronic equipment.
RF emissions CISPR 11	Class B	The PO40 Pulse Oximeter is suitable for use in all establishments, including domestic establishments and those directly connected to the public low-voltage power supply network that supplies buildings used for domestic purposes.
Harmonic emissions IEC 61000-3-2	Not applicable	
Voltage fluctuations/ flicker emission IEC 61000-3-3	Not applicable	

## Guidance and manufacture's declaration-electromagnetic immunity for all EQUIPMENT and SYSTEMS

Guidance and manufacture's declaration-electromagnetic immunity			
The PO40 Pulse Oximeter is intended for use in the electromagnetic environment specified below. The user of PO40 Pulse Oximeter should assure that it is used in such an environment.			
Immunity test	IEC60601 test level	Compliance level	Electromagnetic environment-guidance
Electrostatic discharge (ESD) IEC 61000-4-2	±6kV contact ±8kV air	±6kV contact ±8kV air	Floors should be wood, concrete or ceramic tile. If floor are covered with synthetic material, the relative humidity should be at least 30%.
Power frequency (50Hz) magnetic field IEC 61000-4-8	3 A/m	3 A/m	Power frequency magnetic fields should be at levels characteristic of a typical location in a typical commercial or hospital environment

## Guidance and manufacture's declaration-electromagnetic immunity for EQUIPMENT and SYSTEMS that are not LIFE-SUPPORTING

Guidance and manufacture's declaration-electromagnetic immunity			
The PO40 Pulse Oximeter is intended for use in the electromagnetic environment specified below. The customer or the user of PO40 Pulse Oximeter should assure that it is used in such an environment.			
Immunity test	IEC60601 test level	Compliance level	Electromagnetic environment -guidance
Radiated RF ICE 61000-4-3	3V/m 80MHz to 2.5GHz	3V/m	Portable and mobile RF communication equipment should be used no closer to any part of the PO40 Pulse Oximeter, including cables, than the recommended separation distance calculated from the equation applicable to the frequency of the transmitter.  <b>recommended separation distance</b> $d = \left[ \frac{3.5}{E_1} \right] \sqrt{P} \quad 80\text{MHz to } 800\text{MHz}$ $d = \left[ \frac{7}{E_1} \right] \sqrt{P} \quad 800\text{MHz to } 2.5\text{GHz}$  Where P is the maximum output power rating of the transmitter in watts (W) according to the transmitter manufacturer and d is the recommended separation distance in meters (m). Field strengths from fixed RF transmitters, as determined by an electromagnetic site survey, <sup>a</sup> should be less than the compliance level in each frequency range. Interference may occur in the vicinity of equipment marked with the following symbol: 

NOTE 1 At 80MHz and 800MHz, the higher frequency range applies.

NOTE 2 These guidelines may not apply in all situations. Electromagnetic propagation is affected by absorption and reflection from structures, objects and people.

<sup>a</sup> Field strengths from fixed transmitters, such as base stations for radio (cellular/cordless) telephones and land mobile radios, amateur radio, AM and FM radio broadcast and TV broadcast cannot be predicted theoretically with accuracy. To assess the electromagnetic environment due to fixed RF transmitters, an electromagnetic site survey should be considered. If the measured field strength in the location in which the PO40 Pulse Oximeter is used exceeds the applicable RF compliance level above, the PO40 Pulse Oximeter should be observed to verify normal operation. If abnormal performance is observed, additional measures may be necessary, such as reorienting or relocating the PO40 Pulse Oximeter.

<sup>b</sup> Over the frequency range 150 KHz to 80 MHz, field strengths should be less than 3V/m.

## Recommended separation distances between portable and mobile RF communications equipment and the EQUIPMENT or SYSTEM for EQUIPMENT or SYSTEM that not LIFE-SUPPORTING

Recommended separation distances between portable and mobile RF communications equipment and the PO40 Pulse Oximeter			
The PO40 Pulse Oximeter is intended for use in the electromagnetic environment in which radiated RF disturbances are controlled. The customer or the user of the PO40 Pulse Oximeter can help prevent electromagnetic interference by maintaining a minimum distance between portable and mobile RF communications equipment (transmitters) and the PO40 Pulse Oximeter as recommended below, according to the maximum output power of the communications equipment.			
Rated maximum output power of transmitter (W)	Separation distance according to frequency of transmitter (m)		
	150KHz to 80MHz	80MHz to 800MHz	800MHz to 2.5GHz
	$d = \left[ \frac{3.5}{E_1} \right] \sqrt{P}$	$d = \left[ \frac{3.5}{E_1} \right] \sqrt{P}$	$d = \left[ \frac{7}{E_1} \right] \sqrt{P}$
0.01	0.12	0.12	0.23
0.1	0.37	0.37	0.74
1	1.17	1.17	2.33
10	3.69	3.69	7.38
100	11.67	11.67	23.33
For transmitters rated at a maximum output power not listed above, the recommended separation distance in meters (m) can be estimated using the equation applicable to the frequency of the transmitter, where P is the maximum output power rating of the transmitter in watts (W) according to the transmitter manufacturer.			
NOTE 1 At 80MHz and 800MHz, the separation distance for the higher frequency range applies.			
NOTE 2 These guidelines may not apply in all situations. Electromagnetic propagation is affected by absorption and reflection from structures, objects and people.			