


CONN1: DisplayPort20P M

2017.11.22
图纸确认



FILE NO.	Bestell No.	UNO ITEM NO.	LENGTH	Renkforce giftbox
29212c58	1404070	791300.81	1800+100/-0	10.5*24cm(depth:3.5cm)
29212c59	1404071	791300.05	5000+100/-0	10.5*29cm(depth:3.5cm)
		791300.05	500+20/-0	10.5*14cm(depth:2.0cm)
		791300.11	1000+20/-0	10.5*14cm(depth:3.0cm)
		791300.03	3000+50/-0	10.5*24cm(depth:3.5cm)

MATERIAL LIST:

①	FERRITE	OUTER MOLD BLACK PVC	1PC	
⑩	DUST CAP	DP DUST CAP TRANSPARENT PE	1PC	
⑨	DUST CAP	DVI DUST CAP TRANSPARENT PE	1PC	
⑧	SCREW	PLATED NICKEL MOLD BLACK PVC #4-40(B-L30.5)	2PC	
⑦	ASSEMBLED MOLDING	ABS BLACK ASSEMBLY (SR) TYPE	1SET	
⑥	PVC	PVC 45P BLACK	2PC	
⑤	INNER MOLDING	PE TRANSPARENT	2PC	
④	PCB	PCB WITH IC (8121e)	1PC	
③	CONNECTOR2	DVI24+1 PIN MALE: SOLDER TYPE, BLACK PBT INSULATION, THE PIN GOLD PLATED , THE SHELL FOR GOLD PLATED	1PC	
②	CONNECTOR1	DP 20P/M LATCHING SOLDER, BLACK INSULATION , THE PIN GOLD PLATED , THE SHELL FOR GOLD PLATED	1PC	
①	CABLE	(28AWGBC*1P+D+AL+MYLAR)*4+28AWG BC*1P+28AWG BC*3C+ADB 80 braiding PVC/BLACK OD7.3±0.2MM	1PC	

NOTE:


1. Electrical test:
 - A: DP connector test:
 - (1). Insulation resistance: DC 300V 10M ohm;
 - (2). Contact resistance: 3 ohm;
 - (3). Dielectric strength: 150V AC/Sec, 1mA.
 - B: Finished testing text condition:
 - (1) 100% open short & miss wire test
 - (2) Displayport practical application Test
3. MARKING:

E1149932-T 兄 AWM STYLE 20276 VW-1 80°C 30V DVI Cable
RoHS & REACH COMPLIANT
4. ROHS2.0 ADN REACH COMPLIANT
5. Test: 1920*1080P @ 60 Hz

NO.	PARTS NAME	SPECIFICATION DESCRIPTION	QT'Y	REMARK
	Alei	Alvan	ADD UNO ITEM NO. 791300.05/791300.11/791300.03	2017-11-22 A2
	Alei	Alvan	CHANGE MARKING	2017-10-20 A1
			NEW	2015-11-03 A
	BY	CHK	REVISION RECORD MODIFICATIONS	DATE REV.

CUSTOMER	CN	ITEM NO.	SEE THE CAHRT
PRODUCT NAME	DISPLAYPORT MALE TO DVI24+1 MALE	UNO ITEM NO.	UNIT MM
DRAWNBY	CHECKBY	APPOBY	DATE
Alei	Alvan		2017-11-22

Labeling sample:





Label



three layer corrugated carton(inner carton):





Five layer corrugated carton(outer carton):



1PCS/PE BAG




inner carton+Waterproof bag




Outer carton

“工” Sealing



Outer carton

“井” Packaging



Outer carton



					CUSTOMER		CN		ITEM NO.		see the chart		
Alei	Alvan	ADD UNO ITEM NO. 791300.05/791300.11/791300.03		2017-11-22	A2	PRODUCT NAME		PACKING		UNO ITEM NO.		UNIT	MM
		NEW		2014.09.26	A	DRAWNBY		CHECKBY		APPOBY		DATE	
BY	CHK	REVISION RECORD MODIFICATIONS		DATE	REV.	Alei		Alvan				2017-11-22	