

# FIVENORM

**HAR-UL-CSA-AWM-MTW, PVC single core, UL Style 10269/UL Standard 1063, 600 V, 105°C**



## Technical data

- PVC-single cores acc. to DIN VDE 0285-525-2-31 / DIN EN 50525-2-31, UL Std.1063, UL Style 10269 and CSA-TEW and CSA-AWM I A/B
- **Temperature range**  
H05V2-K / H07V2-K  
flexing +5°C to +90°C  
fixed installation -40°C to +90°C  
UL (AWM) -40°C to +105°C  
UL (MTW) -40°C to +90°C  
CSA (TEW) -40°C to +105°C
- **Nominal voltage**  
up to 1 mm<sup>2</sup> H05V2-K: U<sub>0</sub>/U 300/500 V  
from 1,5 mm<sup>2</sup> H07V2-K: U<sub>0</sub>/U 450/750 V  
UL (AWM) 1000 V (AC)  
UL (AWM) 1250 V (DC)  
UL (MTW) 600 V  
CSA (TEW) 600 V
- **Test voltage**  
H05V2-K = 2000 V  
H07V2-K = 2500 V
- **Test voltage** (Spark Test)  
0,5 mm<sup>2</sup> = 5 kV  
≥ 0,75 mm<sup>2</sup> = 6 kV
- **Insulation resistance**  
min. 20 MOhm x km
- **Minimum bending radius**  
fixed installation for core Ø:  
≤ 8 mm: 4x core Ø  
> 8-12 mm: 5x core Ø  
> 12 mm: 6x core Ø

## Cable structure

- Bare copper fine wire stranded to DIN VDE 0295 cl.5, BS 6360 cl.5 and IEC 60228 cl.5, acc. to UL Std.758
- Core insulation of PVC compound type T13 to DIN VDE 0207-363-3/DIN EN 50363-3 CSA-C 22.2 No. 210 tab.12 class H and class 43 acc. to UL Std.1581
- Core identification to DIN VDE 0293

## Properties

- The materials used during manufacturing are cadmium-free, contain no silicone and are free from substances harmful to the wetting properties of lacquers

## Tests

- PCV self-extinguishing and flame retardant acc. to DIN VDE 0482-332-1-2, DIN EN 60332-1-2, IEC 60332-1-2 (equivalent DIN VDE 0472 part 804 test method B), UL VW-1, CSA FT 1

## Note

- Tinned conductor on request.
- up to = 1,0 mm<sup>2</sup> = H05V2-K, from 1,5 mm<sup>2</sup> up to 35 mm<sup>2</sup> = H07V2-K. Cross-sections up to 35 mm<sup>2</sup> is acc. to DIN VDE 0285-525-2-31. Due to this cross section >35 mm<sup>2</sup> is the type H07V-K but with an increased heat-resistant PVC-compound T13.
- **Type H05V:**  
approved one-colour mark: black, blue, brown, grey, orange, pink, red, turquoise, violet, white, green and yellow. Two-coloured mark in any combination of the above individual colours.
- **Type H07V:**  
approved mark: black, blue, brown, grey, orange, pink, red, turquoise, violet, white and green-yellow. Other marks are available as (H).

## Application

Five norms approved connecting jumper wire primarily designed for exportes, used in machine tools. The approbation of HAR, UL-AWM, UL-MTW, CSA-AWM, CSA-Equipment-wire make possible an economical storekeeping and simplification of parts list.

CE = Product conforms with Low-Voltage Directive 2014/35/EU.

Cross-sec. mm <sup>2</sup> / AWG-no.	Outer Ø app. mm	Cop. weight kg / km	BK	GN-YE	BU	BN	RD	WH	GY	VT	YE	PK	GN	TRANS	D-BU	OG	o.col.	2-col.
<b>app. RAL</b>			9005	-	5015	8003	3000	1013	7000	4005	1021	3015	6018	-	5010	2003	-	-
Part no. 0,5 / 22	2,5	5,2	64075	64076	64077	64078	64079	64080	64081	64082	64083	64084	64085	64086	64087	64088	64089	64090
Part no. 0,75 / 20	2,65	7,2	64091	64092	64093	64094	64095	64096	64097	64098	64099	64100	64101	64102	64103	64104	64105	64106
Part no. 1 / 18	2,8	9,6	64107	64108	64109	64110	64111	64112	64113	64114	64115	64116	64117	64118	64119	64120	64121	64122

Continuation ►

# FIVENORM

**HAR-UL-CSA-AWM-MTW, PVC single core, UL Style 10269/UL Standard 1063, 600 V, 105°C**



Cross-sec. mm <sup>2</sup> / AWG-no.	Outer Ø app. mm	Cop. weight kg / km	BK	GN-YE	BU	BN	RD	WH	GY	VT	YE	PK	GN	TRANS	D-BU	OG	o.col.	2-col.
<b>app. RAL</b>			9005	-	5015	8003	3000	1013	7000	4005	1021	3015	6018	-	5010	2003	-	-
Part no. 1,5 / 16	3,05	14,4	64123	64124	64125	64126	64127	64128	64129	64130	64131	64132	64133	64134	64135	64136	64137	64138
Part no. 2,5 / 14	3,6	24,0	64139	64140	64141	64142	64143	64144	64145	64146	64147	64148	64149	64150	64151	64152	64153	64154
Part no. 4 / 12	4,1	38,0	64155	64156	64157	64158	64159	64160	64161	64162	64163	64164	64165	64166	64167	64168	64169	64170
Part no. 6 / 10	4,8	58,0	64171	64172	64173	64174	64175	64176	64177	64178	64179	64180	64181	64182	64183	64184	64185	64186
Part no. 10 / 8	6,4	96,0	64187	64188	64189	64190	64191	64192	64193	64194	64195	64196	64197	64198	64199	64200	64201	64202
Part no. 16 / 6	8,1	154,0	64203	64204	64205	64206	64207	64208	64209	64210	64211	64212	64213	64214	64215	64216	64217	64218
Part no. 25 / 4	9,6	240,0	64219	64220	64221	64222	64223	64224	64225	64226	64227	64228	64229	64230	64231	64232	64233	64234
Part no. 35 / 2	10,8	336,0	64235	64236	64237	64238	64239	64240	64241	64242	64243	64244	64245	64246	64247	64248	64249	64250
Part no. 50 / 1	13,6	480,0	64251	64252	64253	64254	64255	64256	64257	64258	64259	64260	64261	64262	64263	64264	64265	64266
Part no. 70 / 2/0	15,2	672,0	64267	64268	64269	64270	64271	64272	64273	64274	64275	64276	64277	64278	64279	64280	64281	64282
Part no. 95 / 3/0	16,8	912,0	64283	64284	64285	64286	64287	64288	64289	64290	64291	64292	64293	64294	64295	64296	64297	64298
Part no. 120 / 4/0	19,5	1152,0	64299	64300	64301	64302	64303	64304	64305	64306	64307	64308	64309	64310	64311	64312	64313	64314
Part no. 150 / 300 kcmil	22,2	1440,0	64315	64316	64317	64318	64319	64320	64321	64322	64323	64324	64325	64326	64327	64328	64329	64330

## Barrel (with various capacity)

Cross-sec. mm <sup>2</sup> / AWG-no.	Outer Ø app. mm	Cop. weight kg / km	BK	GN-YE	BU	BN	RD	WH	GY	VT	YE	PK	GN	TRANS	D-BU	OG	o.col.	2-col.
<b>app. RAL</b>			9005	-	5015	8003	3000	1013	7000	4005	1021	3015	6018	-	5010	2003	-	-
Part no. 0,5 / 22	2,5	5,2	65402	65403	65404	65405	65406	65407	65408	65409	65413	65410	65412		65414	65411		
Part no. 0,75 / 20	2,65	7,2	65415	65416	65417	65418	65419	65420	65421	65422	65426	65423	65425		65427	65424		
Part no. 1 / 18	2,8	9,6	65428	65429	65430	65431	65432	65433	65434	65435	65439	65436	65438		65440	65437		

## Barrel (with various capacity)

Cross-sec. mm <sup>2</sup> / AWG-no.	Outer Ø app. mm	Cop. weight kg / km	BK	GN-YE	BU	BN	RD	WH	GY	VT	YE	PK	GN	TRANS	D-BU	OG	o.col.	2-col.
<b>app. RAL</b>			9005	-	5015	8003	3000	1013	7000	4005	1021	3015	6018	-	5010	2003	-	-
Part no. 1,5 / 16	3,05	14,4	65441	65442	65443	65444	65445	65446	65447	65448	65452	65449	65451		65453	65450		
Part no. 2,5 / 14	3,6	24,0	65454	65455	65456	65457	65458	65459	65460	65461	65465	65462	65464		65466	65463		
Part no. 4 / 12	4,1	38,0	65467	65468	65469	65470	65471	65472	65473	65474	65478	65475	65477		65549	65476		
Part no. 6 / 10	4,8	58,0	65550	65551	65552	65553	65554	65555	65556	65557	65558	65559	65560		65561	65562		

## Two colour

Cross-sec. mm <sup>2</sup> / AWG-no.	Outer Ø app. mm	Cop. weight kg / km	BU/WH	WH/BU	D-BU/WH	WH/OG	WH/RD	BK/OG	D-BU/OG	RD/WH	WH/D-BU	YE/BN	OG/BU
<b>app. RAL</b>			-	-	-	-	-	-	-	-	-	-	-
Part no. 0,5 / 22	2,5	5,2	63402	63403	63404	63405	63406	63482	63332	63352	63372	65386	69625
Part no. 0,75 / 20	2,65	7,2	63407	63408	63409	63410	63411	63483	63333	63353	63373	65387	69626
Part no. 1 / 18	2,8	9,6	63412	63413	63414	63415	63416	63484	63334	63354	63374	65388	69627

## Two colour

Cross-sec. mm <sup>2</sup> / AWG-no.	Outer Ø app. mm	Cop. weight kg / km	WH/YE	OG/D-BU	YE/BU	BU/OG	OG/RD	OG/BK	OG/WH	YE/RD	BK/YE
<b>app. RAL</b>			-	-	-	-	-	-	-	-	-
Part no. 0,5 / 22	2,5	5,2	69827	69828	69829	69830	69831	69832	69833	69834	69835
Part no. 0,75 / 20	2,65	7,2	69836	69837	69838	69839	69840	69841	69842	69843	69844
Part no. 1 / 18	2,8	9,6	69845	69846	69847	69848	69849	69850	69851	69852	69853

Continuation ►

# FIVENORM

**HAR-UL-CSA-AWM-MTW, PVC single core, UL Style 10269/UL Standard 1063, 600 V, 105°C**



## Two colour

Cross-sec. mm <sup>2</sup> / AWG-no.	Outer Ø app. mm	Cop. weight kg / km	BU/WH	WH/BU	D-BU/WH	WH/OG	WH/RD	BK/OG	D-BU/OG	RD/WH	WH/D-BU	YE/BN	OG/BU
<b>app. RAL</b>													
Part no. 1,5 / 16	3,05	14,4	63417	63418	63419	63420	63421	63485	63335	63355	63375	65389	69628
Part no. 2,5 / 14	3,6	24,0	63422	63423	63424	63425	63426	63486	63336	63356	63376	65390	69629
Part no. 4 / 12	4,1	38,0	63427	63428	63429	63430	63431	63487	63337	63357	63377	65391	69630
Part no. 6 / 10	4,8	58,0	63432	63433	63434	63435	63436	63488	63338	63358	63378	65392	69655
Part no. 10 / 8	6,4	96,0	63437	63438	63439	63440	63441	63489	63339	63359	63379	65393	69656
Part no. 16 / 6	8,1	154,0	63442	63443	63444	63445	63446	63490	63340	63360	63380	65394	69657
Part no. 25 / 4	9,6	240,0	63447	63448	63449	63450	63451	63491	63342	63362	63382	65395	69658
Part no. 35 / 2	10,8	336,0	63452	63453	63454	63455	63456	63492	63343	63363	63383	65396	69659
Part no. 50 / 1	13,6	480,0	63457	63458	63459	63460	63461	63493	63344	63364	63384	65397	69660
Part no. 70 / 2/0	15,2	627,0	63462	63463	63464	63465	63466	63494	63345	63365	63385	65398	69738
Part no. 95 / 3/0	16,8	912,0	63467	63468	63469	63470	63471	63495	63346	63366	63386	65499	69739
Part no. 120 / 4/0	19,5	1152,0	63472	63473	63474	63475	63476	63496	63347	63367	63387	65400	69740
Part no. 150 / 300 kcmil	22,2	1440,0	63477	63478	63479	63480	63481	63497	63348	63368	63388	65401	69741

## Two colour

Cross-sec. mm <sup>2</sup> / AWG-no.	Outer Ø app. mm	Cop. weight kg / km	WH/YE	OG/D-BU	YE/BU	BU/OG	OG/RD	OG/BK	OG/WH	YE/RD	BK/YE
<b>app. RAL</b>											
Part no. 1,5 / 16	3,05	14,4	69854	69855	69856	69857	69858	69859	69860	69861	69862
Part no. 2,5 / 14	3,6	24,0	69863	69864	69865	69866	69867	69868	69869	69870	69871
Part no. 4 / 12	4,1	38,0	69872	69873	69874	69875	69876	69877	69878	69879	69880
Part no. 6 / 10	4,8	58,0	69881	69882	69883	69884	69885	69886	69887	69888	69889
Part no. 10 / 8	6,4	96,0	69890	69891	69892	69893	69894	69895	69896	69897	69898
Part no. 16 / 6	8,1	154,0	69899	69900	69901	69902	69903	69904	69905	69906	69907

## Two colour, barrel (with various capacity)

Cross-sec. mm <sup>2</sup> / AWG-no.	Outer Ø app. mm	Cop. weight kg / km	BU/WH	WH/BU	D-BU/WH	WH/OG	WH/RD	BK/OG	D-BU/OG	RD/WH	WH/D-BU	YE/BN	OG/BU
<b>app. RAL</b>													
Part no. 0,5 / 22	2,5	5,2	65479	65480	65481	65482	65483	65484	65485	65486	65487	65488	65489
Part no. 0,75 / 20	2,65	7,2	65490	65491	65492	65493	65494	65495	65496	65497	65498	65502	65503
Part no. 1 / 18	2,8	9,6	65504	65505	65506	65507	65508	65509	65510	65511	65512	65514	65515

## Two colour, barrel (with various capacity)

Cross-sec. mm <sup>2</sup> / AWG-no.	Outer Ø app. mm	Cop. weight kg / km	BU/WH	WH/BU	D-BU/WH	WH/OG	WH/RD	BK/OG	D-BU/OG	RD/WH	WH/D-BU	YE/BN	OG/BU
<b>app. RAL</b>													
Part no. 1,5 / 16	3,05	14,4	65516	65517	65518	65519	65520	65521	65522	65523	65524	65525	65526
Part no. 2,5 / 14	3,6	24,0	65527	65528	65529	65530	65531	65532	65533	65534	65535	65536	65537
Part no. 4 / 12	4,1	38,0	65538	65539	65540	65541	65542	65543	65544	65545	65546	65547	65548

Dimensions and specifications may be changed without prior notice. (RN06)