


Data Sheet - TRU Components Automotive wire FLRY-A

Last updated: 8 February 2024

Technical Data

Cable type	: FLRY-A
Length	: 50 m
Halogen-free	: No
Insulation material	: PVC
Conductor material	: Copper
Cable features	: Flexible
Max. temperature range	: +105 °C
Min. temperature range	: -40 °C
Electrical resistance at 20°C	: Min 200 M ohm x km
Rated voltage	: 60 V DC

Drawing



Technical Table FLRY-A Cable

Article number	Cross section	No. of conductors	Outside dimension	Insulation thickness	Color
1564274	0.75 mm ²	19 x 0.23 mm	1.90 mm	0.45 mm	white
1564279	2.50 mm ²	19 x 0.41 mm	3.00 mm	0.55 mm	brown
1565599	0.50 mm ²	19 x 0.19 mm	1.60 mm	0.37 mm	orange
1565602	0.50 mm ²	19 x 0.19 mm	1.60 mm	0.37 mm	grey
1565606	0.75 mm ²	19 x 0.23 mm	1.90 mm	0.45 mm	green
1565609	1.00 mm ²	19 x 0.26 mm	2.10 mm	0.45 mm	brown
1565613	1.50 mm ²	19 x 0.32 mm	2.40 mm	0.50 mm	red
1568641	0.50 mm ²	19 x 0.19 mm	1.60 mm	0.37 mm	white
1568642	0.50 mm ²	19 x 0.19 mm	1.60 mm	0.37 mm	violet
1568647	1.00 mm ²	19 x 0.26 mm	2.10 mm	0.45 mm	blue
1568648	1.00 mm ²	19 x 0.26 mm	2.10 mm	0.45 mm	black
1568649	1.00 mm ²	19 x 0.26 mm	2.10 mm	0.45 mm	red
1568650	1.00 mm ²	19 x 0.26 mm	2.10 mm	0.45 mm	white
1568652	1.00 mm ²	19 x 0.26 mm	2.10 mm	0.45 mm	green
1568655	1.50 mm ²	19 x 0.32 mm	2.40 mm	0.50 mm	white
1568656	1.50 mm ²	19 x 0.32 mm	2.40 mm	0.50 mm	green
1568659	2.50 mm ²	19 x 0.41 mm	3.00 mm	0.55 mm	black
1568660	2.50 mm ²	19 x 0.41 mm	3.00 mm	0.55 mm	red