


Datasheet

Item no. TC-MK313

11	Terminal	3	H62 δ 0.8	Ag Plating
10	Moving piece	1	H62 δ 0.6	Ag Plating
9	Spring	1	Spring steel wire	
8	Plasted Slider	1	Plastic	
7	Inner Sleeve	1	Plastic	
6	Housing	1	Plastic	
5	Bracket	1	iron	Ni Plating
4		2	M6X0.70	Ni Plating
3	Bracket	1	iron	Ni Plating
2	Threaded	1	iron	Ni Plating
1	Handle	1	iron	Ni Plating
NO.	NAME	Q' TY	MATERIAL	FINISHING

The Main Technology Performance

Item	Parameter
Circuit	
Rated voltage Rated current	3A 250V AC 6A 125V AC
Insulated resistance	≥100MΩ
Contact resistance	≤100mΩ
Dielectric strength	≥1000V AC/5S
Endurance	≥10000 Cycles

