



5h



2h

Sunlight hours



Indication of charging the device to 100% in optimal sunlight + conditions.

POWER INDICATOR
DISPLAYS OUTPUT IN AMPERE

2X USB OUTPUT

2/5 POWER INDICATOR

SOLAR PANEL
HIGH EFFICIENCYSunPower® SOLAR PANEL
21 WATTS - HIGH EFFICIENCYUSB OUT 1 (5V/2,1A)
USB OUT 2 (5V/2,1)POWER
INDICATOR

CARABINER

1/5 PRODUCT OVERVIEW

SPECIFICATIONS

Solar Panel Output: 21 Watts - SunPower® Panel
Dimensions folded: 320x155x35mm
Dimensions unfolded: 630x320mm
Weight: 425 grams
Including: Micro USB cable, carabiner and manual.

IN THE BOX



SOLARBOOSTER



CARABINER



MICRO USB CABLE



MANUAL

HIGH EFFICIENCY
SOLAR PANEL

All Xtorm SolarBoosters are equipped with extremely efficient solar panels. With an efficiency of 22%, these panels can generate a lot of power with a small surface area. These SunPower® panels are the best solar panels available on the consumer market.

WATER
RESISTANT

Thanks to the use of water-resistant materials and protected USB port openings the SolarBooster is splash proof. Keep in mind water and electricity are never a good combination.

FLEXIBLE
MATERIAL

The SolarBooster is made from canvas coated with a water-resistant synthetic material that's both flexible and strong. The solar panels are integrated in the material, making it an easy to maintain smooth surface.

FEATHER
LIGHT

The latest generation SunPower® cells make the SolarBooster very lightweight. The compact and practical design make it easy to take with you anywhere you go.

2
YEAR
WARRANTY

All Xtorm products have a 2 year warranty in case something goes wrong. We ensure that you will receive a replacement if the product fails within 2 years.

EN: Warnings

Don't drop, disassemble or attempt to repair the charger by yourself.
Don't expose to any heat source.
Keep out of reach of children.
Don't use in the presence of flammable gas.

NL: Waarschuwing

Probeer de lader niet zelf te repareren of te demonteren.
Niet blootstellen aan een warmtebron.
Buiten bereik van kinderen houden.
Niet gebruiken in de aanwezigheid van brandbaar gas.

DE: Achtung

Versuchen Sie nicht, den Solar Lader selbst zu reparieren.
(Garantieverlust)
Verwenden Sie das Gerät nicht in der Nähe von brennbaren Gasen
Halten Sie das Gerät fern von Hitzequellen,
Ausser Reichweite von Kindern halten.

FR: Attention

Ne pas faire tomber ou démonter ou tenter de réparer le produit soi-même.
Ne pas poser le chargeur solaire près d'une source de chaleur.
Tenir hors de portée des enfants.
Ne pas utiliser en présence de gaz inflammables.

IT: ATTENZIONE

Non usare vicino ad una fiamma.
Non esporre vicino a fonti di calore elevato
Non modificare la struttura o disassemblare
Smettere di utilizzare immediatamente nel caso si sentano odori strani, calore, o strani rumori provenienti dallo stesso.
Non lasciar giocare i bambini.
Usare solo in luoghi asciutti.
Riciclare l'apparato secondo le norme vigenti nella nazione di utilizzo.

CZ: UPOZORNĚNÍ

Neupusťte, nerozobírejte, ani se nepokoušejte spraviť nabíjačku sami.
Nevystavujte tepelným zdrojom.
Uchovávejte mimo dosahu dětí.
Nepoužívejte v blízkosti hořlavých plynů.

SK: Upozornenia

Neupusťte, nerozoberajte, ani sa nepokoušajte opraviť nabíjačku sami.
Nevystavujte tepelným zdrojom.
Uchovávejte mimo dosahu detí.
Nepoužívejte v blízkosti hořlavých plynov

SE: varning

Tappa inte, ta inte isär eller försök reparera laddaren själv.
Utsätt inte för värme.
Förvaras utom räckhåll för barn.
Använd ej i närheten av lättantändlig gas.

ES: Atención

No dejar caer el producto.
No desmontarlo ni intentar repararlo, por sus propios medios.
No exponer la alimentación a una fuente de calor.
Mantenga fuera del alcance de los niños.
No utilizar en presencia de fuentes o gas inflamables.

* THIS MANUAL IS AVAILABLE IN DIFFERENT LANGUAGES ON OUR WEBSITE


Hoofdveste 19
3992 DH Houten
The Netherlands
T: + 31 (0) 30 635 4800
F: + 31 (0) 30 635 4801
www.xtorm.eu

User
Manual
AP275

More energy.

3/5 CHARGE YOUR MOBILE DEVICE | BY SUNLIGHT

Use the SolarBooster outside, ideally in direct sunlight.



Connect with your mobile device using the micro USB cable or your own USB cable

For iPhone/iPad use own USB charging cable.

Connect the USB cable with charger and press the button to start charging.


Expect 2 hours* charging time

Your smartphone will indicate charging status.

* In ideal conditions

4/5 CHARGE 2 DEVICES AT THE SAME TIME

To store your captured energy you can connect a Power Bank to the SolarBooster.




⚠ Important

When charging 2 devices at the same time, the total output of the Solar Booster is divided between the two devices.


E.g. when charging a tablet and smartphone; connect the smartphone to port 1 and the Power Bank to port 2.

5/5 FREE TIPS AND TRICKS!



Best illumination angle




Best place to charge is outside




Best time of the day



Do not leave out in the rain



Best degree of cloudiness



The solar panel doesn't work behind a window

COMPATIBLE WITH



Smartphone



Tablet



Digital camera



USB devices



E-reader

iPhone, iPod, MP3 player, MP4 player, portable speaker, drone, GPS, car navigation, wireless headphone, portable (micro USB), portable controller game console, USB (flash) light, USB fan, power bank, GoPro and much more...