


NOTE:

1. 100% OPEN SHORT, MISS WIRE TEST
2. FLUKE TEST:
TEST LIMIT:ISO11801 Channel Class D
3. PRINT WORD:
CAT5E U/UTP 4x2x26AWG/7 PVC ISO11801 & EN50173 & ANSI/TIA568C.2
4. ROHS2.0 AND REACH COMPLIANT
5. Operating temperature:-20°C~+75°C

MATERIAL LIST

③	OVER MOLD	80A PVC/Grey RAL7035	2	
②	CONNECTOR	RJ45 8P8C UNSHIELDED, THE PIN GOLD PLATED 3u", COLOUR:TRANSPARENT	2	
①	CABLE	U/UTP CAT. 5E (26AWG CCA)*4PAIRS JACKET:PVC OD:4.8±0.2mm, Grey RAL7035	1	

WIRING DIAGRAM



NO.	PARTS NAME	SPECIFICATION STANDARD	QT'Y	REMARK
		NEW		2020-10-16
BY	CHK	REVISION RECORD MODIFICATION		DATE

Basetech					
CUSTOMER		ITEM NO.			
PRODUCT NAME	CAT. 5E U/UTP PATCH CORD	UNO ITEM NO.	215011	UNIT	MM
DRAWN BY	CHECK BY	APPO BY			
Basetech	Basetech	Basetech		2020-10-16	

Color:GREY (RAL 7035)

FN No.	Length (mm)	Packing
FN 29212c196	150±5	Polybag with sticker
FN 29212c196a	250±10	Polybag with sticker
FN 29212c196b	500±10	Polybag with sticker
FN 29212c196c	1000±20	Polybag with sticker
FN 29212c196d	2000±30	Polybag with sticker
FN 29212c196e	3000±50	Polybag with sticker
FN 29212c196f	5000±100	Polybag with sticker
FN 29212c196g	10000±300	Polybag with sticker
FN 29212c196h	15000±300	Polybag with sticker
FN 29212c196PF	150±5	Banderole
FN 29212c196aPF	250±10	Banderole
FN 29212c196bPF	500±10	Banderole
FN 29212c196cPF	1000±20	Banderole
FN 29212c196dPF	2000±30	Banderole
FN 29212c196ePF	3000±50	Banderole
FN 29212c196fPF	5000±100	Banderole
FN 29212c196gPF	10000±300	Banderole
FN 29212c196hPF	15000±300	Banderole

Basetech

Basetech					
CUSTOMER		ITEM NO.			
PRODUCT NAME	CAT. 5E U/UTP PATCH CORD	UNO ITEM NO.	215011	UNIT	MM
DRAWN BY	CHECK BY	APPO BY			
Basetech	Basetech	Basetech	2020-10-16		

NEW

2020-10-16

A

BY

CHK

REVISION RECORD MODIFICATION

DATE

REV.

Basetech

Basetech

Basetech

2020-10-16