



Yuasa Technisches Datenblatt

Yuasa YBX3335 - YBX3000 SMF Batterien

Leistung

Spannung	12V
Kapazität 20 Std (vorgegeben)	90Ah
Kaltstartstrom (A) EN1	700A

Abmessungen

Länge	303mm
Breite	174mm
Höhe	222mm

Maße und Gewichte

Durchschnittliches Gewicht inkl. Säure	20.8kg
Gewicht (trocken)	-
Säure Volumen	-



Gehäuseeigenschaften

Gehäusotyp	JIS D31 + BH
Batteriehälter	B1
Ladezustandsanzeige	✓
Tragegriffe	✓
Entgasung	✓
Semi Traktionseigenschaften	-
Deckel Typ	SMF doppelwandige Deckelkonstruktion

Technologie

Flammschutz	✓
Technologie	Ca/Ca
Separator	PE
VDA Überroll Test	✓
Ladestrom	4A

Anschlusspol Typ

T1


Standard DIN Post



Positive Terminal

Negative Terminal


Zellenanordnung



0

Batteriehälter

B1



Ausstellungsdatum: 10/08/2018 - E&EO



Yuasa Technical Data Sheet

Yuasa YBX3335 - YBX3000 SMF Batteries

Performance

Voltage	12V
Capacity (20-hour)	90Ah
Cold Cranking Amps (EN1)	700A

Dimensions

Length	303mm
Width	174mm
Height	222mm

Weights & Measures

Mean Weight with Acid	20.8kg
Dry Weight	-
Acid Volume	-



Container Features

Case Type	JIS D31 + BH
Hold Down	B1
State of Charge Indicator	✓
Handles	✓
End Venting	✓
Semi-Traction Features	-
Lid Type	SMF Double Lid


Technology

Flame Arrestor	✓
Technology	Ca/Ca
Separator	PE
VDA Roll Over Test	✓
Recommended Charge Rate	4A

Terminal Type

T1


Standard DIN Post



Positive Terminal


Negative Terminal

Cell Assembly Layout



Battery Hold-down

B1



Data Sheet generated on 10/08/2018 - E&OE