

SINEAX TV804


Isolating Amplifier

DC current isolator



Features / Benefits

- Input: Current (active or passive)
- Output: Current (active or passive)
- Response time: 40 ms
- Power for 2-wire transducers, 20 V DC
- 3-way galvanic isolation
- Power supply: 9 ... 40 V DC, 19 ... 28 V AC



General Data

Power supply	9 ... 40 V DC, 19 ... 28 V AC
Accuracy	0.2%
Response time	40 ms
Galvanic isolation	Power supply / input / output at 1500 V AC, digital
Power consumption	2.5 W
Protection for inputs	Except current: 60 V continuous, current 200 mA continuous
Humidity	Up to 90% at + 40 °C (not condensing)
Housing	Terminal housing for mounting on 35 mm DIN 46277. "V0" self-extinguishing glass filled nylon case
Dimensions	17.5 x 100 x 112 mm (w x h x d)
Weight	140 g
Operating temperature	- 20 ... + 60 °C
Connections	Plug-in screw clamp terminal blocks, wires up to 2.5 mm ²
IP Protection	IP 20
Conformity	CE


Order Code

Description	Code
DC current isolator	162 868




SINEAX TV804

Isolating Amplifier


Application



Electrical connections



Dimensional drawing



CAMILLE BAUER

Rely on us.

Camille Bauer Ltd
Aargauerstrasse 7
CH-5610 Wohlen / Switzerland

Phone: +41 56 618 21 11

Fax: +41 56 618 35 35

e-mail: info@camillebauer.com

www.camillebauer.com