







EN 60947-5-1

**Mini**

© DE

WERMA®

WERMA Signaltechnik GmbH + Co. KG
D-78604 Rietheim-Weilheim
Telefon +49 (0)7424 / 9557-0
Telefax +49 (0)7424 / 9557-44
info@werma.com
www.werma.com

	DANGER
	
	
(DE) Anschluss ausschließlich durch ausgebildete Elektro-Fachkräfte.	(GB) Electrical connection is to be made by trained electrical specialists only.
(FR) Le branchement doit uniquement être effectué par des professionnels.	(IT) Il collegamento deve essere eseguito solo da elettricisti specializzati.
(ES) La conexión sólo debe ser realizada por electricistas debidamente formados.	(PT) A ligação deve ser feita exclusivamente por profissional elétrico especializado.
(NL) De aansluiting mag enkel gebeuren door erkende vakmensen.	(CZ) Pripojení smí provádět pouze kvalifikovaný personál.
(PL) Podłączenie wyłącznie przez specjalistów-elektryków.	(FI) Liittäminen kuuluu ainoastaan koulutettujen sähköalan ammattilaisten tehtäviin.
(RU) Подключение проводится только специа- листом-электриком.	(TR) Bağlantı sadece eğitimli elektrik teknisyenleri tarafından yapılmalıdır.
(CN) 布线需由专业电工执行	
	
	



**DANGER
EVS**

TwinFLASH

(DE) Bei Epilepsie ungeeignet!
 (GB) Unsuitable for epilepsy sufferers.
 (FR) Ne convient pas aux personnes souffrant d'épilepsie.
 (IT) Inadatto per epilettici.
 (ES) Inadecuado para epilépticos.
 (PT) Não aconselhavel a pessoas que sofram de Epilepsia.
 (NL) Niet geschikt voor epileptici.
 (CZ) Nevhodné pro epileptiky.
 (PL) Nie stosować przy zchorzeniu padaczki.
 (FI) Ei sovellu epileptikoille.
 (RU) Не подходит для страдающих эпилепсией.
 (TR) Epilepsi hastalığı olanların kullanmaması önerilir.
 (CN) 不适用于癫痫病患者



260




460





160
















	260 x10 74	12V ≈	≤90 mA
	260 x10 75	24V ≈	≤75 mA
	260 x10 60	115V/60Hz- 230V/50Hz	≤45 mA
	260 x20 74	12V ≈	≤70 mA
	260 x20 75	24V ≈	≤70 mA
	260 x20 60	115V/60Hz- 230V/50Hz	≤45 mA
	260 430 75	24V ≈	≤90 mA
	460 x10 74	12V ≈	≤100 mA
	460 x10 75	24V ≈	≤100 mA
	460 x10 60	115V/60Hz- 230V/50Hz	≤70 mA
	460 x20 74	12V ≈	≤85 mA
	460 x20 75	24V ≈	≤100 mA
	460 x20 60	115V/60Hz- 230V/50Hz	≤65 mA
	160 700 74	12V ≈	≤30 mA
	160 700 75	24V ≈	≤40 mA
	160 700 60	115V/60Hz- 230V/50Hz	≤30 mA

1	1a - 260 700 01
	1b - 260 700 06
	1c - 260 700 07
	1d - 260 700 03
	1e - 260 700 04
	1f - 260 700 05






- 3
- 3a - 260 700 01
 - 3b - 260 700 06
 - 3c - 260 700 07
 - 3d - 260 700 03
 - 3e - 260 700 04
 - 3f - 260 700 05




	X2	X1	X0 (COM)	Function
LED				12/24 V
	•	•	•	flashing
	•	•	•	EVS
	•	•	•	115-230 V
TONE	•	•	•	flashing
	•	•	•	EVS
	•	•	•	115-230 V
	•	•	•	flashing

	X3	X4	X0 (COM)	Function
LED				12/24 V
	•	•	•	permanent
	•	•	•	blinking
	•	•	•	115-230 V
TONE	•	•	•	permanent
	•	•	•	blinking
	•	•	•	115-230 V
	•	•	•	permanent




	X2	X1	X0 (COM)	Function
LED				12/24 V
	•	•	•	flashing
	•	•	•	EVS
	•	•	•	115-230 V
TONE	•	•	•	flashing
	•	•	•	EVS
	•	•	•	115-230 V
	•	•	•	flashing

	X3	X4	X0 (COM)	Function
LED				12/24 V
	•	•	•	pulse 95 dB
	•	•	•	perm. 89 dB
	•	•	•	115-230 V
TONE	•	•	•	pulse 95 dB
	•	•	•	perm. 89 dB
	•	•	•	115-230 V
	•	•	•	pulse 95 dB




	X3	X4	X0 (COM)	Function
LED				12/24 V
	•	•	•	pulse 95 dB
	•	•	•	perm. 89 dB
	•	•	•	115-230 V
TONE	•	•	•	pulse 95 dB
	•	•	•	perm. 89 dB
	•	•	•	115-230 V
	•	•	•	pulse 95 dB

	X3	X4	X0 (COM)	Function
LED				12/24 V
	•	•	•	pulse 95 dB
	•	•	•	perm. 89 dB
	•	•	•	115-230 V
TONE	•	•	•	pulse 95 dB
	•	•	•	perm. 89 dB
	•	•	•	115-230 V
	•	•	•	pulse 95 dB



	X2	X1	X0 (COM)	Function
LED				12/24 V
	•	•	•	flashing
	•	•	•	EVS
	•	•	•	115-230 V
TONE	•	•	•	flashing
	•	•	•	EVS
	•	•	•	115-230 V
	•	•	•	flashing



150000000128_AH
310.260.001



© DE