

YN SERIES

The Y series clamps are designed to be both rugged and versatile whilst remaining easy to use. The jaws are designed so that the clamps can be hooked onto cables or clamped onto busbars for current measurement up to 600 A AC.


There are two types of Y series clamps available:

The first acts as a current transformer (ratios of 100:1 or 1000:1), giving an output current that may be read by a multimeter, logger or other suitable devices with appropriate current calibres.

The other kind of Y series clamp has a DC voltage output proportional to the AC current measured, allowing instruments without current calibres to measure, display and record currents on a DC voltage calibre.

There is also a model available specifically for direct use with oscilloscopes.





Model Y1N

Current 500 A AC		
Ratio 1000/1		
Output	1 mA/A	

ELECTRICAL SPECIFICATIONS

Current range: 4 A AC .. 600 A AC

Current transformation ratio:

1000:1

Output signal: 1 mA AC/A AC

Accuracy (1):

Primary current	4 A	25 A	100 A	250 A	500 A	600 A (2)
Accuracy in % of output signal	4.5 % + 0.5 mA	4.5 %	3.5 %	3 %	3 %	3 %
Phase shift	not specified	4°	2°	2°	2°	2°

class 3 at 1.25 VA

Bandwidth:

48 Hz .. 1,000 Hz Load impedance:

 $5~\Omega$ max

Overload:

700 A for 10 minutes

 Maximum output voltage (secondary open): Electronic protection circuit limiting voltage to 10 V peak max

Operating voltage:

600 VRMS

Common mode voltage:

 Influence of adjacent and parallel conductors: < 30 mA/A at 50 Hz

 Influence of conductor position in jaws: ±1.5%

MECHANICAL SPECIFICATIONS

- Operating temperature:
 - -15 °C .. +50 °C
- Storage temperature:

-40°C .. +85°C

- Influence of temperature:
 - < 0.1 % per 10 °K
- Operating altitude:

0 to 2,000 m

Max. jaw opening:

33 mm

Clamping capacity:

Cable: Ø max 30 mm Busbar: 63 x 5 mm

Casing protection rating:

IP20 in accordance with IEC 529

Drop test:

1.5 m (IEC 68-2-32)

Shock resistance:

100 g, in accordance with IEC 68-2-27

Vibration resistance:

10/55/10 Hz, 0.15 mm test in accordance with IEC 68-2-6

 Self-extinguishing capability: UL94 V0

Dimensions:

66 x 195 x 34 mm

Weight:

420 g

Colour: Dark grey

Output:

1.5 m two-wire lead with double or reinforced insulation terminated by 2 elbowed male safety plugs (4 mm)

SAFETY SPECIFICATIONS

Electrical safety:

Double or reinforced insulation between the primary and secondary circuits and the outer casing in accordance with IEC 1010-2-032.

- 600 V category III, pollution degree 2
- 300 V category IV, pollution degree 2
- Electromagnetic compatibility (EMC): EN 50081-1: class B
- EN 50082-2: - Electrical discharge: IEC 1000-4-2
- Radiated field: IEC 1000-4-3
- Fast transients: IEC 1000-4-4
- Magnetic field at 50/60 Hz: IEC 1000-4-8

^{(2) 700} A for 10 minutes max

To order	Reference
AC current clamp model Y1N with operating manual	P01120001A



⁽¹⁾ Conditions of reference: 23 °C \pm 5 °K, 20 % to 75 % RH, 48 Hz to 65 Hz, external magnetic field < 40 A/m, no current-carrying conductor nearby, centred test sample, load impedance 5 $\ensuremath{\Omega}$.

Model Y2N

Current 500 A AC		
Ratio	1000/1	
Output	1 mA/A	

ELECTRICAL SPECIFICATIONS

• Current range: 4 A AC .. 600 A AC

Current transformation ratio:

1000:1

Output signal:

1 mA AC/A AC

Accuracy (1):

Primary current	4 A	25 A	100 A	250 A	500 A	600 A (2)
Accuracy in % of output signal	3 % + 0.5 mA	3 %	1.5 %	1%	1%	1%
Phase shift	not specified	3°	1.5°	1°	1°	1°

class 1 at 1.25 VA

Bandwidth:

48 Hz .. 1,000 Hz

Load impedance:

 $5~\Omega$ max

Overload:

700 A for 10 minutes

 Maximum output voltage (secondary open): Electronic protection circuit limiting voltage to 10 V peak max

Operating voltage:

600 VRMS

Common mode voltage:

600 VRMS

Influence of adjacent and parallel conductors:
 < 30 mA/A at 50 Hz

• Influence of conductor position in jaws: < 1 %

MECHANICAL SPECIFICATIONS

• Operating temperature:

-15 °C .. +50 °C

Storage temperature:

-40 °C .. +85 °C

• Influence of temperature: < 0.1 % per 10 °K

Operating altitude:

Operating altitude 0 to 2,000 m

Max. jaw opening:

33 mm

Clamping capacity:

Cable: Ø max 30 mm Busbar: 63 x 5 mm

Casing protection rating:

IP20 in accordance with IEC 529

Drop test:

1.5 m (IEC 68-2-32)

Shock resistance:

100 g, in accordance with IEC 68-2-27

Vibration resistance:

10/55/10 Hz, 0.15 mm test in accordance with IEC 68-2-6

 Self-extinguishing capability: UL94 V0 Dimensions:

66 x 195 x 34 mm

• Weight:

420 g

 Colour: Dark grey

Output:

1.5 m two-wire lead with double or reinforced insulation terminated by 2 elbowed male safety plugs (4 mm)

SAFETY SPECIFICATIONS

Electrical safety:

Double or reinforced insulation between the primary and secondary circuits and the outer casing in accordance with IEC 1010-2-032.

- 600 V category III, pollution degree 2
- 300 V category IV, pollution degree 2
- Electromagnetic compatibility (EMC):

EN 50081-1: class B EN 50082-2:

- Electrical discharge: IEC 1000-4-2

- Radiated field: IEC 1000-4-3

- Fast transients: IEC 1000-4-4

- Magnetic field at 50/60 Hz: IEC 1000-4-8

^{(2) 700} A for 10 minutes max

To order	Reference
AC current clamp model Y2N with operating manual	P01120028A





⁽¹⁾ Conditions of reference: $23\,^{\circ}\text{C} \pm 5\,^{\circ}\text{K}$, $20\,^{\circ}\text{k}$ to $75\,^{\circ}\text{R}$ RH, $48\,^{\circ}\text{Hz}$ to $65\,^{\circ}\text{Hz}$, external magnetic field < $40\,^{\circ}\text{A/m}$, no current-carrying conductor nearby, centred test sample, load impedance $5\,^{\circ}\Omega$.

Current clamp for AC current

Model Y3N

Current	500 A AC
Ratio	100/1
Output	10 mA/A

ELECTRICAL SPECIFICATIONS

• Current range: 4 A AC .. 600 A AC

Current transformation ratio:

• Output signal: 10 mA AC/A AC

Accuracy (1):

Primary current	4 A	25 A	100 A	250 A	500 A	600 A (2)
Accuracy in % of output signal	5% + 5 mA	5 %	3 %	3 %	3 %	3 %
Phase shift	not specified	6°	5°	3°	3°	3°

class 3 at 2.5 VA

Bandwidth:

48 Hz .. 1,000 Hz

Load impedance:

 $0.1~\Omega$ max

Overload:

700 A for 10 minutes

 Maximum output voltage (secondary open):
 Electronic protection circuit limiting voltage to 10 V peak max

 Operating voltage: 600 VRMS

Common mode voltage:

 $30 \; V_{\text{RMS}}$

Influence of adjacent and parallel conductors:
 < 30 mA/A at 50 Hz

• Influence of conductor position in jaws: $\pm 1~\%$

MECHANICAL SPECIFICATIONS

• Operating temperature: 15 °C ... +50 °C

• Storage temperature: -40 °C ... +85 °C

• Influence of temperature: < 0.1 % per 10 °K

• Operating altitude: 0 to 2,000 m

• Max. jaw opening: 33 mm

Clamping capacity:

Cable: Ø max 30 mm Busbar: 63 x 5 mm

• Casing protection rating: IP20 in accordance with IEC 529

• **Drop test:** 1.5 m (IEC 68-2-32)

• Shock resistance: 100 g, in accordance with IEC 68-2-27

Vibration resistance:

10/55/10 Hz, 0.15 mm test in accordance with IEC 68-2-6

 Self-extinguishing capability: UL94 V0 Dimensions:

66 x 195 x 34 mm

• Weight: 420 g

• Colour: Dark grey

Output:

 $1.5~\mbox{m}$ two-wire lead with double or reinforced insulation terminated by 2 elbowed male safety plugs (4 mm)

SAFETY SPECIFICATIONS

Electrical safety:

Double or reinforced insulation between the primary and secondary circuits and the outer casing in accordance with IEC 1010-2-032.

- 600 V category III, pollution degree 2
- 300 V category IV, pollution degree 2
- Electromagnetic compatibility (EMC): EN 50081-1: class B
- EN 50082-2: - Electrical discharge: IEC 1000-4-2
- Radiated field: IEC 1000-4-3
- Fast transients: IEC 1000-4-4
- Magnetic field at 50/60 Hz: IEC 1000-4-8

^{(2) 700} A for 10 minutes max.

To order	Reference
AC current clamp model Y3N with operating manual	P01120029A




⁽¹⁾ Conditions of reference: $23\,^{\circ}\text{C} \pm 5\,^{\circ}\text{K}$, $20\,^{\circ}\text{k}$ to $75\,^{\circ}\text{R}$ RH, 48 Hz to 65 Hz, external magnetic field < 40 A/m, no current-carrying conductor nearby, centred test sample, load impedance $0.1\,\Omega$.

Current clamp for AC current

Model Y4N

Current	500 A AC
Output	1 mV DC/A AC



ELECTRICAL SPECIFICATIONS

- Current range: 4 A AC .. 600 A AC
- Output signal: 1 mV DC/A AC
- Accuracy (1):

Primary current	2 A	25 A	100 A	250 A	500 A	600 A (2)
Accuracy in % of output signal	5 % + 0.5 mV DC	5 %	2 %	1 %	1%	2%

Bandwidth:

48 Hz .. 1,000 Hz (error: add 2 % to reference)

- Load impedance:
 - $> 100 \text{ k}\Omega \text{ max}$
- Overload:

700 A for 10 minutes

- Operating voltage: 600 VRMS
- Common mode voltage:

600 VRMS

- Influence of adjacent and parallel conductors:
 < 30 mA/A at 50 Hz
- Influence of conductor position in jaws: $\pm 1~\%$

MECHANICAL SPECIFICATIONS

- Operating temperature: 15 °C .. +50 °C
- Storage temperature: $-40\,^{\circ}\text{C}$.. $+85\,^{\circ}\text{C}$
- Influence of temperature: < 0.1 % per 10 °K

• Operating altitude: 0 to 2,000 m

Max. jaw opening:33 mm

• Clamping capacity: Cable: Ø max 30 mm Busbar: 63 x 5 mm

- Casing protection rating: IP20 in accordance with IEC 529
- **Drop test:** 1.5 m (IEC 68-2-32)
- Shock resistance:
 - 100 g, in accordance with IEC 68-2-27
- Vibration resistance: 10/55/10 Hz, 0.15 mm test in accordance with IEC 68-2-6
- Self-extinguishing capability: UL94 V0
- **Dimensions:** 66 x 195 x 34 mm
- Weight: 420 g
- Colour: Dark grey

Output

1.5 m two-wire lead with double or reinforced insulation terminated by 2 elbowed male safety plugs (4 mm)

SAFETY SPECIFICATIONS

Electrical safety:

Double or reinforced insulation between the primary and secondary circuits and the outer casing in accordance with IEC 1010-2-032.

- 600 V category III, pollution degree 2
- 300 V category IV, pollution degree 2
- Electromagnetic compatibility (EMC): EN 50081-1: class B EN 50082-2:
- Electrical discharge: IEC 1000-4-2
- Radiated field: IEC 1000-4-3
- Fast transients: IEC 1000-4-4
- Magnetic field at 50/60 Hz: IEC 1000-4-8

^{(2) 600} A for 10 minutes max

To order	Reference
AC current clamp model Y4N with operating manual	P01120005A



⁽¹⁾ Conditions of reference: $23\,^{\circ}\text{C} \pm 5\,^{\circ}\text{K}$, $20\,\%$ to $75\,\%$ RH, $48\,\text{Hz}$ to $65\,\text{Hz}$, external magnetic field < $40\,\text{A/m}$, no current-carrying conductor nearby, centred test sample, load impedance $10\,\text{M}\Omega$.


Oscilloscope clamp for AC current

Model Y7N (insulated AC current probe)

Current	1,200 A peak	
Output	1 mV/A	

DESCRIPTION

This 500 A AC clamp can be used for the display and measurement of 'current' curves. It comes with a coaxial cable terminated by a BNC plug, thus making it the ideal tool for use with oscilloscopes. It supplies a mV output signal that is directly proportional to the measured current.



ELECTRICAL SPECIFICATIONS

• Current range:

1 A AC .. 500 A AC (1,200 A peak)

Output signal:

1 mV AC / A AC (0.5 V for 500 A)

Accuracy and phase shift (1):

Primary current	1 A 20 A	20 A 100 A	100 A 500 A	
% Accuracy of output signal	\leq 5 % + 0.3 mV	≤ 5 %	≤ 2 %	
Phase shift	not specified	≤ 3°	≤ 1°	

Bandwidth:

5 Hz .. 10 kHz (at -3 dB) (depending on current)

Rise/fall time from 10 % to 90 %:

37 µs

• 10 % delay time:

1 µs

Ampere second product:

10 A.s

Insertion impedance (at 400 Hz / 10 kHz):

 $< 0.1 \text{ m}\Omega / < 3.1 \text{ m}\Omega$

dV/dt:

0.24 mV/µs (typical)

Maximum currents:

500 A constant

700 A: 10 minutes operation / 30 minutes shutdown for frequency \leq 2 kHz (limitation proportional to the inverse of one third of the frequency above that)

Internal load impedance:

 $\leq 100 \,\Omega / 4.7 \,\mathrm{nF}$

Influence of temperature:

≤ 0.15 % of output signal per 10 °K

Influence of adjacent conductor:
 ≤ 5 µV / A at 50 Hz

• Influence of conductor position in jaws: $\leq 1.5\% + 0.1 \text{ A AC}$

MECHANICAL SPECIFICATIONS

• Operating temperature: -25 °C to +50 °C

Storage temperature:

-40°C to +80°C

Relative humidity for operation:
 0 to 85 % RH decreasing linearly above 35 °C

• Operating altitude:

0 to 2,000 m

Max. jaw opening:

33 mm

Clamping capacity:

Cable: Ø max 30 mm

Busbar: 1 busbar of 63 x 5 mm

Casing protection rating:

IP20 (IEC 529)

• Drop test:

1.5 m (IEC 68-2-32)

Shock resistance:
 100 g / 6 ms / half-periode (IEC 68-2-27)

Protection against impacts:

IK04 0.5 J (EN 50102)

Vibration resistance:

10/55/10 Hz 0.15 mm (IEC 68-2-6)

Self-extinguishing capability:

UL94 V0

• **Dimensions:** 195 x 66 x 34 mm • **Weight:** 420 g

Colour:

Dark grey

Output:

Via 2 m coaxial cable terminated by insulated BNC plug

SAFETY SPECIFICATIONS

• Electrical safety:

Instrument with double insulation or reinforced insulation between the primary the secondary and the grippable part located under the guard as per IEC 1010-1 & IEC 1010-2-032

- 600 V category III, pollution degree 2
- 300 V category IV, pollution degree 2

Electromagnetic compatibility (EMC):
 EN 50081-1: class R

EN 50081-1: class B EN 50082-2:

Electrostatic discharge: IEC 1000-4-2
 4 kV level 2 performance criterion B
 8 kV in the air level 3 performance criterion B

 Radiated field: IEC 1000-4-3 10 V/m performance criterion A

Fast transients: IEC 1000-4-4
 1 kV level 2 performance criterion B
 2 kV level 3 performance criterion B

 Magnetic field at 50/60 Hz: IEC 1000-4-8 field of 400 A/m at 50 Hz: < 1 A






Oscilloscope clamp for AC current


Model Y7N (insulated AC current probe)

CURVES


Error on measurement at 50 Hz




Phase shift at 50 Hz



Frequency response




Phase shift according to frequency



Influence of frequency and derating

Frequency Hz	5 Hz to 10 Hz	10 Hz to 20 Hz	20 Hz to 45 Hz	65 Hz to 3 kHz	3 kHz to 6 kHz	6 kHz to 10 kHz
1 A to 200 A	15 %					
> 200 A	not spec.					
1 A to 300 A		5 %				
300 A to 400 A		15 %				
400 A to 500 A		25 %				
1 A to 500 A			5 %			
1 A to 50 A				5 % + 0.4 A		
50 A to 500 A				5 %		
> 500 A				not spec.		
1 A to 100 A					15 % + 0.4 A	
> 100 A					not spec.	
1 A to 50 A						-3 dB
> 50 A						not spec.

Influence of DC current




⁻ Error in % of reading; not spec. means not specified - Do not exceed 500 A for measurement with constant operation, and for the derating, use the formula 500 (A) * 2 / F (kHz) to calculate the maximum current in A AC, in constant use, depending on the frequency in kHz.


Model Y7N (insulated AC current probe)

RESPONSE TO A SQUARE SIGNAL


5 A at 10 Hz




5 A at 500 Hz




5 A at 50 Hz



5 A at 4 kHz



RESPONSE TO A STEP



(1) Conditions of reference: $23 ^{\circ}C \pm 3 ^{\circ}K$, $20 ^{\circ}K$ to $75 ^{\circ}K$ RH, sinusoidal signal with frequency of 48 Hz at 1 kHz, external magnetic field < 40 A/m, no DC components, no external conductor with circulating current, conductor centred for measurement, load impedance $> 1 \text{ M}\Omega / < 100 \text{ pF}$.

To order	Reference
AC current clamp model Y7N for oscilloscope with operating manual	P01120075