

Controller - AXC F 1152 - 1151412

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



PLCnext Control for the direct control of Axioline F I/Os. With two Ethernet interfaces. Complete with connector and bus base module.

Product Description

The controllers of the PLCnext Control AXC F 1152 family for the Axioline I/O system are fast, robust, and easy to use. They were consistently designed for maximum performance, easy handling and use in harsh industrial environments.

Your advantages

- ✓ PROFINET support
- ✓ Connection to PROFICLOUD
- ✓ Numerous protocols supported such as: http, https, FTP, SNMP, SMTP, SQL, MySQL, DCP, etc.
- ✓ Up to 63 AXIO I/O modules can be mounted side by side
- ✓ 2 x Ethernet interfaces (integrated switch)
- ✓ Increased resistance to EMI
- ✓ Extended temperature range of -25°C ... +60°C
- ✓ Linux operating system
- ✓ Supports high-level languages



Key Commercial Data

Packing unit	1 pc
GTIN	
GTIN	4063151149420
Weight per Piece (excluding packing)	225.600 g
Weight per piece (including packing)	286.300 g
Custom tariff number	85371091
Country of origin	Germany
Sales Key	O1 - Automation Systems

Controller - AXC F 1152 - 1151412

Technical data

Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

Dimensions

Width	45 mm
Height	126.93 mm
Depth	75 mm

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 60 °C up to 2000 m above mean sea level (observe derating)
	-25 °C ... 55 °C up to 3000 m above mean sea level (observe derating)
	≤ 55 °C (with max. 1 A on U _{Bus})
	> 55 °C ... 60 °C (only in conjunction with an Axioline F power module AXL F PWR 1H (order number 2688297))
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (according to DIN EN 61131-2)
Permissible humidity (storage/transport)	5 % ... 95 % (according to DIN EN 61131-2)
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	58 kPa ... 106 kPa (up to 4500 m above mean sea level)
Shock	30g, 11 ms period, half-sine shock pulse, according to IEC 60068-2-27
Vibration (operation)	5g

Control system

Engineering tool	PLCnext Engineer
	Eclipse
Programming languages supported	Programming in acc. with IEC 61131-3
	C++
	C#
	Java
	Manufacturer-specific
Supports cloud computing	yes
Cloud platform	Proficloud

General data

Processor	Arm® Cortex®-A9 1x 800 MHz
Operating system	Linux
RAM	512 Mbyte DDR3 SDRAM

IEC 61131 runtime system

Engineering tool	PLCnext Engineer
	Eclipse
Program memory	8 Mbyte

Controller - AXC F 1152 - 1151412

Technical data

IEC 61131 runtime system

Mass storage	16 Mbyte
Retentive mass storage	48 kByte (NVRAM)
Realtime clock	Yes

Fieldbus function

Designation	System limits of the controller
Amount of process data	max. 8192 Bit (per station)
	max. 4096 Bit (Input)
	max. 4096 Bit (Output)
Number of supported devices	max. 63 (per station)
Number of local bus devices that can be connected	max. 63 (observe current consumption)
Program memory	8 Mbyte

Data interfaces

Interface	Axioline F local bus
Number	1
Connection method	Bus base module
Transmission speed	100 Mbps
Interface	Ethernet
Number	2
Connection method	RJ45 socket
Transmission speed	10/100 Mbps (full duplex)
Protocols supported	HTTP
	HTTPS
	SFTP
	SNTP
	SNMP
	IPsec
	syslog
	OPC UA

PROFINET

Device function	PROFINET controller, PROFINET device
Specification	Version 2.3
Update rate	min. 1 ms (4 devices)
	min. 4 ms (16 devices)

Mechanical design

Weight	215 g
Diagnostics display	No
Controller redundancy	No
Safety function	No

Controller - AXC F 1152 - 1151412


Technical data

Standards and Regulations

Vibration (storage/transport)	5g
Shock	30g, 11 ms period, half-sine shock pulse, according to IEC 60068-2-27
Vibration (operation)	5g
Shock (operation)	10g (Bump endurance test according to DIN EN 60068-2-27)

Drawings

Dimensional drawing



Classifications

eCl@ss

eCl@ss 4.0	27240602
eCl@ss 4.1	27240602
eCl@ss 5.0	27242700
eCl@ss 5.1	27242700
eCl@ss 6.0	27242200
eCl@ss 7.0	27242207

Controller - AXC F 1152 - 1151412

Classifications

eCl@ss

eCl@ss 8.0	27242207
eCl@ss 9.0	27242207

ETIM

ETIM 3.0	EC001045
ETIM 4.0	EC001435
ETIM 5.0	EC000236
ETIM 6.0	EC000236
ETIM 7.0	EC000236

Approvals

Approvals

Approvals

UL Listed / cUL Listed / cULus Listed

Ex Approvals

Approval details

UL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
Nominal voltage UN		125 V	
Nominal current IN		1 A	

cUL Listed		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	FILE E 238705
Nominal voltage UN		125 V	
Nominal current IN		1 A	

cULus Listed	
--------------	--

Controller - AXC F 1152 - 1151412

Accessories

Accessories

I/O component

Extension module - AXC F IL ADAPT - 1020304



Right-alignable Inline adapter terminal (INTERBUS master) for one PLCnext Control device for setting up a PLCnext Technology Inline station

Power module - AXL F PWR 1H - 2688297



Axioline F, Power module for the logic supply U_{Bus} , max. 4 A, degree of protection: IP20, including bus base module and Axioline F connector

Parameterization memory

Program / configuration memory - SD FLASH 8GB PLCNEXT MEMORY - 1061701



Program and configuration memory for storing the application programs and other files in the file system of the PLC, plug-in, 8 GB.

Program / configuration memory - SD FLASH 2GB PLCNEXT MEMORY - 1043501



Program and configuration memory for storing the application programs and other files in the file system of the PLC, plug-in, 2 GB.

Programming

Software - PLCNEXT ENGINEER - 1046008



Controller - AXC F 1152 - 1151412

Accessories

Programming cable

Connecting cable - CAB-USB C/ USB C/1,8M - 1021809



Connecting cable, for connecting the controller to a PC from USB C to USB C

Connecting cable - CAB-USB A/ USB C/1,8M - 2404677



Connecting cable, for connecting the controller to a PC from USB A to USB C

Spare parts

Bus connector - AXL BS BK - 2701422



Axioline F bus base module for housing type BK
