

LED RECHARGEABLE INSPECTION LIGHT



IS409



PACKING	INNER	MASTER
/	pcs	pcs
Blister F6	6	24



INCLUSI/INCLUDED/INCLUS/INCLUIDOS:



DATI TECNICI / SPECIFICATION / CARACTÉRISTIQUES / CARACTERISTICAS / SPEZIFIKATIONEN

Codice / Item / Code / Codigo / Code	IS409
Nome prodotto / product name / Nom du produit / Designación / Produktname	IS409
Alimentazione / Power supply / Alimentation / Alimentación / Stromversorgung	100-240V 50/60 Hz / 5V 1A
Batteria / Battery / Batterie / Batería / Batterie	3.7V 2200mAh Li-ion (18650)
Tempo di ricarica / Charging Time / Temps de recharge / Tiempo de carga / Ladezeit	3.5 hrs
Autonomia / Runtime / Autonomie / Autonomía / Leuchtdauer	5 hrs (panel), 9 hrs (torch)
Tecnologia della Luce / Light technology / Technologie de la lumière / Tecnología de iluminación / Leuchtentechnologie	SMD (panel), High power LED (torch)
Potenza d'illuminazione (W) / (W) Power / Puissance (W) / Potencia (W) / Leuchtstärke (W)	3W + 2W
Consumo elettrico (W) / (W) Consumption / Consommation (W) / Consumo (W) / Verbrauch (W)	
Lumen / Lumen / Lumen / Lumen / Lumen	170 (torch) / 300 (panel)
Tipo di luce / Kelvin degrees / Degrés Kelvin / Temperatura de luz / Grad Kelvin	
IRC / Colour rendering Index / Indice de rendu des couleurs / IRC / Farbwiedergabeindex	
Fascio di luce / Light beam / Type de faisceau / Tipo de haz / Lichtstrahl	Torch: focus 15°, Panel: diffuse 60°
Portata / Range / Distance d'éclairage / Alcance alumbrado / Leuchtweite	30 mt
Durata di vita del LED / LED Life time / Durée de vie des LED / Durada de vida del LED /	30.000 hrs
Massima intensità del fascio / Peak beam intensity / Intensité maximale du faisceau / Máxima intensidad / Abstrahlintensität	
Dimmerabilità / Dimmable / Dimmable / Dimmer, regulador / Dimmereigenschaften	
Numero di cicli on-off / On off cycles / Nr de cycles on-off / Numero de On-OFF / Ein-Aus Zyklen	
Power factor / Power factor / Power factor / Power factor / Leistungsfaktor	
Cavo / Cable / Câble / Cable / Kabel	
Materiale / Material / Matériau / Material / Material	PC
Grado di protezione / Protection degree / Degré de protection / Estanqueidad / Schutzgrad	IP54
Resistenza Meccanica / Mechanical resistance / Résistance Mécanique / Resistencia mecanica / Mechanische Widerstandsfähigkeit	IK07
Accessori / Accessories / Accessoires / Accesorios / Zubehör	220V Adaptor, 12V Adaptor
Dimensioni prodotto / Product dimensions / Dimensions du produit / Dimensiones producto / Abmessungen Produkt	Width x Height x Length: 35 x 32 x 180 mm
Dimensioni prodotto imballato / Packed dimensions / Dimensions du produit emballé / Dimensiones embalaje / Abmessungen Umverpackung	Width x Height x Length: 102 x 320 x 65 mm
Peso netto / Net Weight / Poids net / Peso neto / Gewicht netto	215 g
Peso prodotto imballato / Weight of packaged product / Poids du produit emballé / Peso producto con embalaje / Gewicht mit Umverpackung	275 g