Features

Regulated Converter

- 300W baseplate-cooled, fan-less operation
- 550W peak power or forced air rating
- Industrial, household and medical 2MOPP ready
- Standby power consumption <0.5W
- Aux Output: 5VSB / 1A
- Signals: remote sensing and ON/OFF control

RECOM AC/DC Converter

RACM550-G

550 Watt 5" x 3"



Open Frame or Enclosed Single Output



















UL62368-1 (TÜV NRTL) certified
CAN/CAS C22.2 No. 62368-1 certified
IEC/EN62368-1 certified
ANSI/AAMI ES60601-1 (ed 3.1) certified
CAN/CSA-C22.2 No. 60601-1:14 certified
IEC/EN60335-1 certified
IEC/EN60950-1 certified
IEC/EN60601-1 (ed. 3.1)
EN60601-1-2 (ed. 4) (pending)
IEC/EN61558-1 (pending)
IEC/EN61558-2-16 (pending)
EN55032 compliant
EN55024 compliant
CB Reports

Description

The RACM550 Series is designed to support up to 300 Watt continuous output power without fan cooling. The compact 5" x 3" baseplate design enables direct heat dissipation through metal housings in the application. Up to 550 watts are available to drive dynamic loads for several seconds of peak power or with forced air for even longer time frames. A fan output is on board as standard as well as a 5V/1A VSB output for applications with housekeeping circuits and on/off control. A wide input range of 80 to 264VAC, up to 5000m operating altitude and international safety agency certifications make the series worldwide suitable for BF-rated applied parts, household and industrial ITE applications.

| Selection Guide | | | | |
|------------------------|---------------------------------|---------------------------------|--|--|
| Part Number | Input Voltage Range [VAC] | Nom. Output Voltage [VDC] | Max. Output Current ⁽¹⁾ [A] | Efficiency typ. ⁽²⁾ [%] |
| RACM550-24SG (3) | 80-264 | 24 | 22.92 | 93 |
| RACM550-36SG (3) | 80-264 | 36 | 15.28 | 93 |
| RACM550-48SG (3) | 80-264 | 48 | 11.46 | 93 |
| RACM550-56SG (3) | 80-264 | 56 | 9.82 | 94 |

Notes:

Note1: With forced air cooling (2.5m/s) + conduction cooling + refer to "Line Derating"

Note2: Efficiency is tested at nominal input and full load at +25°C ambient

Model Numbering



Notes:

Note3: add suffix "/OF" for open frame version add suffix "/ENC" for enclosed version (MOQ 1000pcs)

Ordering Examples:

RACM550-24SG/OF 24Vout Single open frame RACM550-36SG/ENC 24Vout Single enclosed



Series

Specifications (measured @ Ta= 25°C, rated input, rated load unless otherwise stated)


| BASIC CHARACTERISTICS | | | | | |
|---|---|--------------------------------------|-----------------|----------------|------------------|
| Parameter | Condition | | Min. | Тур. | Max. |
| Nom. Input Voltage | | | 100VAC | | 240VAC |
| Input Voltage Range (4) | | | 80VAC 120VDC | | 264VAC 370VDC |
| Input Current | | 5VAC OVAC | | | 6.5A 3.0A |
| Inrush Current | | 5VAC OVAC | | | 40A 60A |
| No load Power Consumption | | | | | 2W |
| Standby Power | main output OFF, V | 'SB Output unloaded | | | 0.5W |
| Input Frequency Range | AC | input | 47Hz | | 63Hz |
| ErP Lot 6 Standby Mode Conformity (VSB Output Load Capability) | Input Power= 1W (main output= standby mode) | | | | 450mW |
| Minimum Load | | | 0% | | |
| Power Factor | | SVAC OVAC | 0.98 0.95 | 0.99 0.97 | |
| Start-up Time | main output VSB Output | 115VAC/230VAC 115VAC/230VAC | | 400ms 140ms | |
| Rise Time | main output VSB Output | 115VAC/230VAC 115VAC/230VAC | | 15ms 5ms | |
| Hold-up Time | main output VSB Output | 115VAC/230VAC, 550W 115VAC/230VAC | | 15ms 130ms | |
| Output Dipple and Naise (5) | 20MHz BW @ 25°C | main output | | 1% of | Vout nom. max |
| Output Ripple and Noise (5) | VSB Output | | | | 120mVp-p |

Notes:

Note4: The products were submitted for safety files at AC-input operation. For DC-input make sure that sufficient fuses are used

Note5: Measurements are made with a 12" twisted pair-wire terminated with a 0.1µF and 10µF parallel capacitor

Efficiency vs. Load



| REGULATIONS | | | | | |
|--|----------------------------------|--------------------------|------------|--|--|
| Parameter | Cond | lition | Value | | |
| Output Acquirecy | main (| output | ±3.0% max. | | |
| Output Accuracy | VSB o | putput | ±4.0% max | | |
| Line Regulation | low line to high line, full load | main output / VSB output | ±1.0% max. | | |
| Load Regulation (6) | 10% to 100% load | main output / VSB output | 1.0% max. | | |
| Notes: | | | | | |
| Note6: Operation below 10% load will not harm the converter, but specifications may not be met | | | | | |

www.recom-power.com REV.: 1/2020 PA-2



Series


Specifications (measured @ Ta= 25°C, rated input, rated load unless otherwise stated)

| ADDITIONAL FEATURES | | | | | |
|----------------------------------|---|--|------|-------|-------------------------------|
| Parameter | Cond | ition | Min. | Тур. | Max. |
| VSB Output Voltage | | | | | 5VDC |
| | CTRL ON | 115VAC/230VAC | | | 5W |
| VSB Output Power | CTRL OFF | 230VAC 115VAC | | | 5W 1W |
| Output Voltage Adjustability (7) | on-board potentiometer | | | | ±2VDC |
| ON/OFF CTRL | CON3, Pin3 (refer to "VSB & CTRL (CON3)" | main and FAN output ON main and FAN output OFF | | | - 5VDC or open shorted to GND |
| Fan Output Voltage | | | | | 12VDC |
| Fan Output Current | @ +50°C (not protected) | continuous peak (1s) | | 250mA | 500mA |
| Remote Sense (8) | | | | | 2VDC |
| Power OK LED | LED = green LED = red | | | | working failure |

Notes:

Note7: By trimming up, decrease output current to avoid exceeding rated output power. By trimming down, do not exceed maximum continuous output current

Note8: The output voltage can be adjusted by both ADJ (potentiometer) and Sense. The maximum combined adjustment range is ±2VDC



| Parameter | Ту | pe | Value |
|---|------------------------|----------|--------------------------|
| Input Fuse (9) | inte | ernal | 2x T6.3A, slow blow type |
| Over Voltage Category (OVC) | | | OVCII |
| Class of Equipment | | | Class I |
| Isolation Voltage (safety certified) (10) | I/P to O/P | 1 minute | 4kVAC |
| Isolation Resistance | | | 10MΩ min. |
| Insulation Grade | | | reinforced |
| Leakage Current | | | 0.25mA max. |
| Means of Protection | 250VAC working voltage | | 2MOPP |

Note9: Refer to local safety regulations if input over-current protection is also required. Recommended fuse: slow blow type Note10: For repeat Hi-Pot testing, reduce the time and/or the test voltage

| PROTECTIONS MAIN OUTPUT | | | |
|-----------------------------------|-------------|---------------------------|---|
| Short Circuit Protection (SCP) | below 100mΩ | P _{in} =10W max. | hiccup mode, auto recovery |
| Over Voltage Protection (OVP) | | | 110% - 120%, hiccup mode |
| Over Current Protection (OCP) | | | 105% - 135%, hiccup mode |
| Over Temperature Protection (OTP) | | | auto recovery, internal temperature sensors |



Series


Specifications (measured @ Ta= 25°C, rated input, rated load unless otherwise stated)


| PROTECTIONS AUX (VSB) | | |
|--------------------------------|-------------|----------------------------|
| Short Circuit Protection (SCP) | below 100mΩ | hiccup mode, auto recovery |
| Over Voltage Protection (OVP) | | 8-9VDC, hiccup mode |
| Over Current Protection (OCP) | | 2.5-3.5A, hiccup mode |


| ENVIRONMENTAL | | | | |
|-----------------------------|--------------------------------|----------------------------|---|--|
| Parameter | Condition | on | Value | |
| Operating Temperature Range | refer to below graphs (vali | d for /OF and /ENC) | -40°C to +70°C | |
| Temperature Coefficient | | | ±0.02%/K | |
| Operating Altitude (11) | | | 5000m | |
| Operating Humidity | non-condensing | | 20% - 90% RH max. | |
| Pollution Degree | | | PD2 | |
| Shock | | | 250m/s², 6ms; 3 times, each along x, y, z axes | |
| Vibration | | | 90-200Hz, 10m/s ² ; 3.5min./1cycle, 5 periods, each along x, y, z axes | |
| MTBF | according to MIL-217F Method 2 | +25°C (forced air cooling) | 200 x 10 ³ hours | |
| INITO | Components Stress Method | +45°C (forced air cooling) | 50 x 10 ³ hours | |

Notes:

Note11: Recognized by safety agency for safe operation up to 5000m. High altitude operation may impact the performance and lifetime. Please contact RECOM tech support for advice.







Conduction Cooling: ground plane ref.: 2mm alloy; size A4

Convection Cooling: <0.1m/s = still air 0.1 - 0.2m/s = natural convection

continued on next page

www.recom-power.com REV.: 1/2020 PA-4



Series

Specifications (measured @ Ta= 25°C, rated input, rated load unless otherwise stated)


Peak Load Capability

Calculation

 $\begin{array}{lll} P_{\text{nom}} &= \text{nom. output power} & [W] \\ P_{\text{p}} &= \text{peak output power} & (\leq 550W) & [W] \\ P_{\text{r}} &= \text{recovery output power} & [W] \\ t_{1} &= \text{peak time set (10s max.)} & [s] \\ t_{2} &= \text{recovery time (min. 4 x t_{1})} & [s] \end{array}$

= safety factor 1.7

 $P_{r} = \frac{P_{nom} x (t_{1set} + t_{2}) - (P_{p} x t_{1set})}{t_{2} x k}$



Practical Example (RACM550-24SG/OF):

Take the RACM550-24SG/OF at 100VAC input voltage and T_{AMB} = 60°C (220W) with conduction cooling.

 $P_{\text{nom.}}$ = refer to derating graphs= 245W with line derating 220W

 $P_P = 550W$

 $t_1 = 10s$

 $t_2 = 40s$

k = 1.7

$P_r = \frac{220 \times (10 + 40) - (550 \times 10)}{40 \times 1.7} = 80.9W$

| Certificate Type (Safety) | Report / File Number | Standard |
|--|------------------------------|--|
| Audio/video, information and communication technology equipment - Safety requirements (CB) | 044 700554 000 | IEC62368-1:2014 2nd Edition |
| Audio/video, information and communication technology equipment - Safety requirements | 211-700554-000 | EN62368-1:2014 + A11:2017 |
| Audio/video, information and communication technology equipment - Safety requirements | 65.250.19.032.02 | UL62368-1:2014 |
| (TÜV NRTL) | | CAN/CSA C22.2 No.62368-1:2014 |
| Information Technology Equipment, General Requirements for Safety (CB) | 211-700555-000 | IEC60950-1:2005, 2nd Edition + A2:2013 |
| Information Technology Equipment, General Requirements for Safety | 211 700303 000 | EN60950-1:2006 + A2:2013 |
| Household and similar electrical appliances - Safety - Part 1: General requirements | | EN60335-1:2012 + A11:2014 |
| Measurement methods for electromagnetic fields of household appliances and similar apparatus with regard to human exposure | SA1904214L 02001 | EN62233:2008 |
| Medical Electric Equipment, General Requirements for Safety and Essential Performance | E314885-D1001-1-A0- C0-UL | ANSI/AAMI ES60601-1:2005 CAN/CSA-C22.2 No. 60601-1:14 |
| Medical Electric Equipment, General Requirements for Safety and Essential Performance (CB Class I) | | IEC60601-1:2005, 3rd Edition + AM1:2012 |
| Medical Electric Equipment, General Requirements for Safety and Essential Performance (CB Class II) | (pending) | IEC60601-1:2005, 3rd Edition + AM1:2012 |
| Medical Electric Equipment, General Requirements for Safety and Essential Performance | | EN60601-1:2006 + A12:2014 |
| Safety of power transformers, power supplies, reactors and similar products - Part 1: General requirements and tests (CB) | | IEC61558-1:2005, 2nd Edition + A1:2009 |
| Safety of transformers, reactors, power supply units and similar products for supply voltages up to 1100 V - Part 2-16: Particular requirements and tests for switch mode power supply units and transformers for switch mode power supply units (CB) | (pending) | IEC61558-2-16:2009, 1st Edition + A1:2013 |
| Safety of power transformers, power supplies, reactors and similar products - Part 1: General requirements and tests (LVD) | | EN61558-1:2005 + A1:2009 |
| Safety of transformers, reactors, power supply units and similar products for supply voltages up to 1100 V - Part 2-16: Particular requirements and tests for switch mode power supply units and transformers for switch mode power supply units (LVD) | (pending) | EN61558-2-16:2009 + A1:2013 |
| RoHS2 | | RoHS 2011/65/EU + AM2015/863 |



Series


Specifications (measured @ Ta= 25°C, rated input, rated load unless otherwise stated)

| EMC Compliance | Condition | Standard / Criterion |
|---|--|--------------------------------------|
| Electromagnetic compatibility of multimedia equipment - Emission requirements | without external filter | EN55032:2015, Class B |
| Electromagnetic compatibility of multimedia equipment - Immunity requirements | | EN55035:2017 |
| Information technology equipment - Immunity characteristics - Limits and methods of measurement | | EN55024:2010 + A1:2015 |
| ESD Electrostatic discharge immunity test | Air ±8kV, Contact ±4kV | EN61000-4-2:2009, Criteria A |
| Radiated, radio-frequency, electromagnetic field immunity test | 3V/m (80-5000MHz) | EN61000-4-3:2006+A2:2010, Criteria A |
| Fast Transient and Burst Immunity | AC Power Port: ±1kV | EN61000-4-4:2012, Criteria A |
| Surge Immunity | AC Power Port: L-N ±1kV | EN61000-4-5:2014, Criteria B |
| Immunity to conducted disturbances, induced by radio-frequency fields | AC Power Port: 3V (0.15-80MHz) 3V to 1V (10-30MHz) 1V (30-80MHz) | EN61000-4-6:2014, Criteria A |
| Power Magnetic Field Immunity | 50Hz/60Hz, 1A/m | EN61000-4-8:2010, Criteria A |
| Voltage Dips and Interruptions | Voltage Dips 100% at 50/60Hz | EN61000-4-11:2004, Criteria A |
| Voltage Dips and Interruptions | Voltage Dips 30% at 50Hz | EN61000-4-11:2004, Criteria A |
| Voltage Dips and Interruptions | Voltage Dips 30% at 60Hz | EN61000-4-11:2004, Criteria B |
| Voltage Dips and Interruptions | Voltage Interruptions > 95% at 50Hz | EN61000-4-11:2004, Criteria C |
| Voltage Dips and Interruptions | Voltage Interruptions > 95% at 60Hz | EN61000-4-11:2004, Criteria B |
| Limits of Harmonic Current Emissions | Class A | EN61000-3-2:2014 |
| Limits of Voltage Fluctuations & Flicker | Clause 5 | EN61000-3-3:2013 |

| DIRACKIOLONI ANIC | DINOLOAL | OLIADA OTEDIOTICO |
|-------------------|----------|-------------------|
| DIMENSION AND | PHYSICAL | CHARACTERISTICS |

| Parameter | Туре | Value | |
|-------------------|---------------------------|-----------------------|--|
| Material | PCB | FR4, (UL94 V-0) | |
| ivialeriai | baseplate / case ("/ENC") | aluminum | |
| Dimension (LxWxH) | open frame version | 127.0 x 76.0 x 38.0mm | |
| | enclosed version | 150.0 x 87.0 x 45.0mm | |
| Woight | open frame version | 500g typ. | |
| Weight | enclosed version | 590g typ. | |


Dimension Drawing Open Frame (mm)





Series

Specifications (measured @ Ta= 25°C, rated input, rated load unless otherwise stated)



Compatible Connector (valid for open frame and enclosed version)

| PE (CON1) | | | AC Input (CON4) | | FAN (CON2) | | | VSB & CTRL (CON3) | | | Sense (CON6) | | | |
|-----------|----------|---|-----------------|--------------|---------------------------------|-----|--------------|---------------------------------|------------------|------------------------------|---------------------------------|------------------|------------------------------|---------------------------------|
| # | Function | Connector | # | Function | Connector | # | Function | Connector | # | Function | Connector | # | Function | Connector |
| 1 | PE | TE Connectivity PIDG series with positive lock .250EX | 1 3 | AC/N AC/L | Molex 09-50- 1031 or similar | 1 2 | -FAN +FAN | Molex 22-01- 1022 or similar | 1 2 3 4 | +5VSB GND PS ON GND | Molex 51110- 0450 or similar | 1 2 3 4 | -Sense NC +Sense NC | Molex 51110- 0450 or similar |

NC= No connection

| MAIN Out | MAIN Output Screw Terminal (CON7/8) | | | | | | | |
|------------------------------|-------------------------------------|-------|--|--|--|--|--|--|
| # | Function | AWG | | | | | | |
| CON7 | -Vout | 14-26 | | | | | | |
| CON8 | +Vout | 14-26 | | | | | | |
| wire stripping length: 5.0mm | | | | | | | | |

recommended tightening torque: 0.8Nm

Maximum tightening torque for mounting without standoffs: 0.3Nm FC= fixing centers


Tolerance: ISO-2768-M (unless otherwise stated)

continued on next page



Series


Specifications (measured @ Ta= 25°C, rated input, rated load unless otherwise stated)






Series

Specifications (measured @ Ta= 25°C, rated input, rated load unless otherwise stated)







Series

Specifications (measured @ Ta= 25°C, rated input, rated load unless otherwise stated)

| PACKAGING INFORMATION | | | | | | | |
|-----------------------------|---------------|-------------------------------------|--|--|--|--|--|
| Parameter | 1 | - уре | Value | | | | |
| Packaging Dimension (LxWxH) | cardboard box | open frame version enclosed version | 134.0 x 86.0 x 45.0mm 155.0 x 92.0 x 50.0mm | | | | |
| Packaging Quantity | | | 1pcs | | | | |
| Storage Temperature Range | | | -55°C to +85°C | | | | |
| Storage Humidity | non-co | ondensing | 95% RH max. | | | | |

The product information and specifications may be subject to changes even without prior written notice. The product has been designed for various applications; its suitability lies in the responsibility of each customer. The products are not authorized for use in safety-critical applications without RECOM's explicit written consent. A safety-critical application is an application where a failure may reasonably be expected to endanger or cause loss of life, inflict bodily harm or damage property. The applicant shall indemnify and hold harmless RECOM, its affiliated companies and its representatives against any damage claims in connection with the unauthorized use of RECOM products in such safety-critical applications.

www.recom-power.com REV.: 1/2020 PA-10