AZ888

SUBMINIATURE POLARIZED POWER RELAY

FEATURES

- 8 A / 5 A switching capability
- 1 Form A, 2 Form A and combined 1 Form A / 1 Form B contact arrangements
- Monostable non-latching and bistable latching types available
- Single and dual coil latching versions
- Low coil power
- High Dielectric strength 3 kV_{RMS}
- Low height 10.5 mm
- Epoxy sealed versions optional, Gold plating optional
- UL Class F insulation (155°C) standard
- RoHS compliant
- UL, CUR file E44211

CONTACTS

Arrangement SPST-N.O. (1 Form A) DPST-N.O. (2 Form A) SPST-N.O. (1 Form A) / SPST-N.C. (1 Form B) Ratings (max.) 1 Form A (resistive load) switched power 150 W or 2000 VA switched current 8 A 240 VDC* or 380 VAC switched voltage 2 Form A 1 Form A/1 Form B 150 W or 1250 VA switched power switched current 5 A switched voltage 240 VDC* or 380 VAC * Note: If switching voltage is greater than 30 VDC, special precautions must be taken. Please contact the factory. **Contact materials** AgSnO₂ - silver tin oxide gold plating available Initial resistance < 50 mΩ (1 A / 6 VDC, with gold plating: 0.1 A / 6 VDC)

COIL	
Nominal coil DC voltages	see coil voltage specifications tables
Dropout non-latching types	> 10% of nominal coil voltage
Coil power	(typ.)
non-latching, dual coil latching at nominal voltage	300 mW
at pickup voltage	192 mW
single coil latching at nominal voltage at pickup voltage	150 mW 96 mW
Max. temperature	155°C (311°F), Class F



GENERAL DATA

	Life Expectancy mechanical electrical	(minimum operations) 1×10^{7} 1×10^{5} at 8 A 250 VAC resistive (1s on/9s off) 3×10^{4} at 5 A 250 VAC resistive (2s on/2s off)
	Operate Time non-latching types	at nominal coil voltage 10 ms (max.)
	Release Time non-latching types	at nominal coil voltage, w/o coil suppression 5 ms (max.)
	Set Time latching types	at nominal coil voltage 10 ms (max.)
	Reset Time latching types	at nominal coil voltage 10 ms (max.)
,	Dielectric Strength	(at sea level for 1 min.) 3 kV _{RMS} coil to contacts 2 kV _{RMS} between contact sets 1 kV _{RMS} between open contacts
	Surge voltage coil to contact	5 kV (at 1.2 x 50 μs)
	Insulation Resistance	1000 M Ω (min.) at 20°C, 500 VDC, 50% RH
	Temperature Range operating	(at nominal coil voltage) -40°C (-40°F) to 85°C (185°F)
Ľ.	Vibration resistance operating damage	2.0 mm (0.079") DA at 10–55 Hz 3.5 mm (0.138") DA at 10–55 Hz
	Shock operating damage	20 g 100 g
	Terminals	Tinned copper alloy, P. C.
	Soldering max. temperature max. time	260°C (500°F) 5 seconds
	Cleaning max. solvent temp. max. immersion time	80°C (176°F) 30 seconds
	Dimensions length width height Weight	20.2 mm (0.795") 11.3 mm (0.445") 10.5 mm (0,413") 4.5 grams (approx.)

A ZETTLER GROUP Company

ZETTLER electronics GmbH

Junkersstr. 3, D-82178 Puchheim, Germany

phone: +49 89 800 97-0 fax: +49 89 800 97-200 office@ZETTLERelectronics.com www.ZETTLERelectronics.com page 1 of 3 2019-03-06

AZ888


UL/CUR APPROVED CONTACT RATINGS

1 Form A	8 A at 250 VAC, general use, 30k cycles, 85°C 8 A at 250 VAC, resistive, 50k cycles, 85°C * 8 A at 250 VAC, resistive, 100k cycles, 70°C 5 A at 30 VDC, general use, 50k cycles, 85°C * 5 A at 30 VDC, general use, 30k cycles, 85°C * 16 HP at 125/250 VAC, 6k cycles, 85°C 8300 pilot duty, 30k cycles, 85°C R150 pilot duty, 30k cycles, 85°C 8300 pilot duty, 50k cycles, 70°C R300 pilot duty, 50k cycles, 70°C R300 pilot duty, 50k cycles, 70°C
2 Form A	5 A at 250 VAC, general use, 50k cycles, 40°C 5 A at 250 VAC, general use, 30k cycles, 85°C 5 A at 250 VAC, resistive, 100k cycles, 70°C 5 A at 30 VDC, resistive, 100k cycles, 70°C 5 A at 30 VDC, resistive, 30k cycles, 85°C 1/10 HP at 125/250 VAC, 6k cycles, 40°C B300 pilot duty, 50k cycles, 40°C R150 pilot duty, 50k cycles, 40°C
1 Form A/1 Form B	5 A at 250 VAC, general use, 50k cycles, 40°C 5 A at 250 VAC, general use, 30k cycles, 85°C 5 A at 250 VAC, resistive, 100k cycles, 70°C 5 A at 30 VDC, resistive, 100k cycles, 70°C 5 A at 30 VDC, resistive, 30k cycles, 85°C 1/6 HP at 125/250 VAC, 6k cycles, 40°C B300 pilot duty, 50k cycles, 70°C

R150 pilot duty, 50k cycles, 70°C

* For dual coil latching type only

ORDERING DATA



Example ordering data

AZ888-1A-5D	Monostable type, 1 Form A, 5 VDC nominal coil voltage, non sealed, non gold plated, standard coil polarity
AZ888P1-1AB-12DEA	Single coil latching, combined 1 Form A and 1 Form B contact arrangement, 12 VDC nominal coil voltage, sealed, gold plated, standard coil polarity
AZ888P2-2A-9DR	Dual coil latching, 2 Form A, 9 VDC nominal coil voltage, non sealed, non gold plated, reversed coil polarity

COIL VOLTAGE SPECIFICATIONS

Monostable non-latching

Nominal Coil VDC	Must Operate VDC	Max. Continuous VDC	Resistance Ohm ± 10%
3	2.4	3.9	30
5	4.0	6.5	83
6	4.8	7.8	120
9	7.2	11.7	270
12	9.6	15.6	480
18	14.4	23.4	1080
24	19.2	31.2	1920

Single coil latching

Nominal Coil	Must Operate	Max. Continuous	Resistance
VDC	VDC	VDC	Ohm ± 10%
3	2.4	3.9	60
5	4.0	6.5	167
6	4.8	7.8	240
9	7.2	11.7	540
12	9.6	15.6	960
18	14.4	23.4	2160
24	19.2	31.2	3840

Dual coil latching

Nominal Coil VDC	Must Operate VDC	Max. Continuous VDC	Resistance Ohm ± 10%
3	2.4	3.9	30
5	4.0	6.5	83
6	4.8	7.8	120
9	7.2	11.7	270
12	9.6	15.6	480
18	14.4	23.4	1080
24	19.2	31.2	1920

ZETTLER electronics GmbH


A ZETTLER GROUP Company

Z88


MECHANICAL DATA

Dimensions in mm

Monostable non-latching and single coil bistable latching types




Bistable dual coil latching type




PC BOARD LAYOUT


Viewed towards terminals. Dimensions in inches with metric equivalents in parentheses.


Monostable non-latching and single coil bistable latching types





Bistable dual coil latching type






WIRING DIAGRAMS


Viewed towards terminals, shown in deenergized / reset condition.

Note: The diagrams show the standard coil polarity. The polarity is reversed for types with reverse polarity option 'R'


Monostable non-latching type



Bistable single coil latching type



Bistable dual coil latching type



NOTES

- Specifications subject to change without notice. 1
- 2. All values at 20°C (68°F) unless otherwise stated.
- 3. Relay may pull in with less than "Must Operate" value.
- 4. Coil suppression circuits such as diodes, etc. in parallel to the coil will lengthen the release time.
- 5. Relay has fixed coil polarity.
- 6 For complete isolation between the relay's magnetic fields, it is recommended that a .197" (5.0 mm) space be provided between adjacent relays
- case

DISCLAIMER

This product specification is to be used in conjunction with the application notes which can be downloaded from

www.ZETTLERelectronics.com/pdfs/relais/ApplicationNotes.pdf

A ZETTLER GROUP Company

The specification provides an overview of the most significant part features. Any individual applications and operating conditions are not taken into consideration. It is recommended to test the product under application conditions. Responsibility for the application remains with the customer. Proper operation and service life cannot be guaranteed if the part is operated outside the specified limits.

ZETTLER electronics GmbH

Junkersstr. 3, D-82178 Puchheim, Germany

phone: +49 89 800 97-0 fax: +49 89 800 97-200

office@ZETTLERelectronics.com www.ZETTLERelectronics.com page 3 of 3 2019-03-06

7. Relay adjustment may be affected if undue pressure is exerted on relay