



CONNECTCORE® 6UL DEVELOPMENT KIT

Design and build your connected products on an industrial and productization-ready Single Board Computer platform.

The ConnectCore 6UL Development Kit delivers a complete off-the-shelf Single Board Computer (SBC) built on the ConnectCore 6UL System-on-Module (SOM).

The SBC is a proven reference design for ConnectCore 6UL module-based development, suited for rapid prototyping; as a productization-ready product platform, it requires little to no hardware development effort. Its standard form factor is the ideal solution for connected applications demanding professional reliability and flexibility in medical/healthcare, transportation, energy, utility, agriculture, building automation and industrial markets.

FOCUS ON YOUR CORE COMPETENCY.

The SBC is built on the ConnectCore 6UL SOM with a low-power NXP i.MX6UL application processor, 256 MB flash, 256 MB RAM, dual 10/100 Mbit Ethernet, pre-certified dual-band 802.11ac wireless LAN, Bluetooth 4.2 connectivity, NFC tag capabilities, and complete set of available peripherals.

Digi tests, integrates and maintains complete Yocto Project Linux BSP and software support for the ConnectCore 6UL module and SBC platform. This includes software components such as the Digi TrustFence® Device Security Framework, wireless connectivity stacks, and drivers for relevant industry leading cellular modems. We also offer optional services, including antenna design/selection guidance, cellular integration support, certification assistance, or custom design services, to get you to market faster and smarter.

THE KIT INCLUDES:

- ✓ 1 ConnectCore 6UL SBC Pro w/dual-Ethernet, 802.11a/b/g/n/ac, and Bluetooth 4.2
- ✓ 1 Console Port cable
- ✓ 1 Dual-band antenna
- ✓ Power supply and accessories

NUMBER	DESCRIPTION
CC-WMX6UL-KIT	ConnectCore 6UL Development Kit

FEATURES AND BENEFITS

- Compact Pico-ITX form factor (100 mm x 72 mm)
- NXP i.MX6UL with 256K/1GB NAND flash, 256K/1GB DDR3
- Pre-certified dual-band 802.11ac Wi-Fi connectivity
- Bluetooth 4.2, with Bluetooth Low Energy support
- NFC Forum Type 2 Tag compliant capabilities
- Dual-10/100 Mbit Ethernet networking
- Ready for cellular connectivity and XBee RF integration
- Full and customizable set of peripherals and interfaces
- Off-the-shelf and productization-ready SBC platform
- Industrial operating temperature range
- Complete Yocto Project Linux BSP with source code

SPECIFICATIONS

ConnectCore® 6UL SBC PRO

PERFORMANCE*

APPLICATION PROCESSOR NXP i.MX6UL-2, ARM® Cortex®-A7 @ 528 MHz, 128 KB L2 cache, with NEON™ MPE (Media Processor Engine) co-processor

MEMORY 256K/1GB NAND flash, 256K/1GB DDR3

WIRED NETWORK CONNECTIVITY

ETHERNET 2 x 10/100 Mbit Ethernet

WIRELESS NETWORK CONNECTIVITY

WI-FI Dual-band 802.11a/b/g/n/ac 1x1 (MCS 0-9)

BLUETOOTH Bluetooth 4.2, with Bluetooth Low Energy support

ANTENNAS On-module U.FL or on-board MMCX antenna connector for Wi-Fi and Bluetooth, external NFC antenna option

NFC Energy-harvesting NXP NTAG, field detection trigger, ISO 14443A and NFC Forum Type 2 Tag compliant

DIGI XBEE® RF Standard Digi XBee socket

PERIPHERALS/INTERFACES

ETHERNET 2 x RJ-45 (10/100 Mbit)

USB 2 x USB Host (Dual Type-A), 1 x USB Host (6-pin header), 1 x USB OTG (Micro-USB)

DISPLAY 24-bit Parallel RGB (40-pin header), and 18-bit LVDS (20-pin header)

CAMERA 8-bit Parallel CSI (20-pin header)

GPIO 14-pin header (8 x GPIO, 1 x Touch)

UART / CONSOLE 14-pin header (1 x two-wire, 2 x four-wire, one shared with XBee socket), 3-pin header (Console)

OTHER CONNECTIVITY 1 x I2C (6-pin header), 1 x SPI (8-pin header), 2 x CAN (6-pin header)

PCI EXPRESS MINI CARD Half-size and full-size card support, with on-board Micro SIM slot support

RF CONTROL 14-pin header (Wi-Fi Enable/Disable, Bluetooth Enable/Disable, Wakeup, PCM, LTE Control, GPS Co-Existence)

EXTERNAL STORAGE microSD, on-board 4 GB eMMC flash for data storage

AUDIO 3.5 mm headphone jack, 6-pin header (speaker), 8-pin header (line-in, microphone, line-out)

BUTTONS / SWITCHES Power, Reset, User, Boot Select (NAND/microSD), RF (Wi-Fi Enable, Bluetooth Enable), Antenna Select (U.FL on-module/MMCX on-board)

DEBUG Tag-Connect for JTAG and SWD

POWER 3.3V Out (2-pin header), 5V Out (2-pin header), Battery (2-pin header)

LEDS Power, 3 x User

CERTIFICATIONS**

RADIO APPROVALS US, Canada, EU, Japan, Australia, New Zealand

EMISSIONS / IMMUNITY / SAFETY FCC Part 15 Class B, EN 55022 Class B, EN 61000-3-2, EN 61000-3-3, ICES-003 Class B, VCCI Class II, AS 3548, FCC Part 15 Subpart C Section 15.247, IC (Industry Canada), RSS-210 Issue 5 Section 6.2.2(o), EN 300 328, EN 301 489-17, EN 55024, EN 301 489-3, Safety (UL/UL equivalent)

POWER REQUIREMENTS

SUPPLY VOLTAGE 5VDC @ 300 mA (typical); See ConnectCore 6UL module product brief for module-only power consumption guidance.

POWER CONNECTORS Locking barrel connector (2 mm), or dedicated power connector (3-pin header)

ENVIRONMENTAL

OPERATING TEMPERATURE -40° C to 85° C

STORAGE TEMPERATURE -50° C to +125° C

RELATIVE HUMIDITY Relative humidity 5% to 90% (non-condensing)

ALTITUDE Altitude 12,000 feet (3,658 meters)

DESIGN VERIFICATION Temperature: IEC 60068-2-1, IEC 60068-2-2, IEC 60068-2-78; Vibration/Shock: IEC 60068-2-6, IEC 60068-2-64, IEC 60068-2-27, HALT

MECHANICAL

DIMENSIONS 100 x 72 mm

* Populates ConnectCore 6UL module P/N CC-WMX-JN58-NE (LGA mounting). **Final certifications pending.



Go to market smarter. Go to market faster.
visit www.digi.com/cc6ul

877-912-3444 | 952-912-3444

© 1996-2018 Digi International Inc. All rights reserved. All other trademarks are the property of their respective owners.



91003409
A10/818