



Type : Mercury and Lead Free Button Cell
Chemical System : Zinc/Manganese Dioxide
Nominal Voltage : 1.5Volts
Nominal Dimensions : $\varnothing 11.6\text{mm} \times 4.2\text{mm}$
Application : Calculator, hearing aid, lighter, electronic, toy, camera, ... etc.
Average Weight : 1.4g
Date Code : Unless otherwise specified, each cell Will carry a numeric year code and an alphabetical month code.
Shelf Life : 12 months shelf life after delivery .
Close Circuit Voltage : 1.30 Volts (min.) (load resistor 300Ω at $20 \pm 2^\circ\text{C}$ for 0.1 to 2 seconds)
Lot Acceptance Test (to 1.0V at $22 \pm 3^\circ\text{C}$) : 70mAh (at 1.6 k Ω load)
Service Output Test (to 1.2V at $22 \pm 3^\circ\text{C}$) : 359Hr (at 10k Ω load)

Model No.: **GP186F**



Typical Discharge characteristics at $20 \pm 2^\circ\text{C}$

The information (subject to change without prior notice) contained in this document is for reference only and should not be used as a basis for product guarantee or warranty. For applications other than those described here, please consult your nearest GP Sales and Marketing Office or Distributors.