

**Artikel Nr.: 180515**

Netzgerät, BASIC, DIM, CV, HALOGEN, Ultra 70












IP20 

**Elektrische Daten**

Betriebsart	spannungskonstant	Eingangsspannung	220-240V AC/50-60Hz
Leistung	0-70,00 W	Leistungsfaktor	
Ausgangsspannung	11,5V AC	Anschlußmöglichkeit	Klemme
Ausgangsstrom	0-6000 mA		


**Produkteigenschaften**

 Schutzklasse II	 Überspannungsschutz
SELV Schutzkleinspannung	 Lampenbetriebsgerät 110
 Kurzschlußfest	 Möbeleinbau geeignet
 Überlastschutz	ErP Standby-Stromverbrauch < 0,5 W
 Übertemperaturschutz	LVD Sicherheit nach EN 61347
 Sicherheitstrafo	EMC Funkentstörung + Störfestigkeit nach EN 55015 + EN 61547
 dimmbar - Phasen-/abschnitt	EMC Netzstromoberwellen + Flicker nach EN 61000-3-2 + EN 61000-3-3

Schwarze Felder sind zutreffend / graue Felder sind nicht zutreffend

**Artikel Nr.: 180515**

Netzgerät, BASIC, DIM, CV, HALOGEN, Ultra 70

**Abmessungen und Gewicht****Grenzwerte**

Länge	115,00 mm	Betriebstemperatur	
Breite	45,00 mm	Gehäusetemperatur	80 °C
Höhe	28,00 mm	max. Menge Sicherungsautomaten	B10A=8, B16A=14, C10A=18, C16A=29
Durchmesser	0,00 mm	max. Einschaltstrom	20A/300µs
Gewicht	109 g	kapazitive Last	97,79nF

**Article No.: 180515**

Power supply unit, BASIC, DIM, CV, HALOGEN, Ultra 70












IP20 CE

**Electrical Characteristics**

Operating mode	constant voltage	Input voltage	220-240V AC/50-60Hz
Power	0-70,00 W	Power factor	
Output voltage	11,5V AC	Connection possibility	clamp
Output current	0-6000 mA		


**Product features**

	Protection class II		Overvoltage protection
SELV	Low voltage protection		Lamp control gear 110
	Short circuit protection		Suitable for furniture installation
	Overload protection	ErP	Standby-power consumption < 0,5 W
	Overheating protection	LVD	Safety according to EN 61347
	Safety transformer	EMC	Interference suppression + immunity according to EN 55015 + EN 61547
	dimnable - leading/trailing edge	EMC	Mains harmonics + flicker according to EN 61000-3-2 + EN 61000-3-3

Black fields are applicable / gray fields are not applicable

**Article No.: 180515**

Power supply unit, BASIC, DIM, CV, HALOGEN, Ultra 70

**Dimensions & Weight****Absolute maximum ratings**

Length	115,00 mm	Operating temperature	
Width	45,00 mm	Case temperature	80 °C
Height	28,00 mm	max. amount of circuit breakers	B10A=8, B16A=14, C10A=18, C16A=29
Diameter	0,00 mm	max. inrush current	20A/300µs
Product weight	109 g	capacitive load	97,79nF