



MOTOR FEATURES

| REFERENCE NUMBER REFERENCIA REFERENZNUMMERN | NOMINAL VOLTAGE TENSION NOMINALE NENNSPANNUNG | NOMINAL TORQUE PAR NOMINAL DREHMOMENT NOMINAL | NOMINAL SPEED VELOCIDAD NOMINAL GESCHWINDIGKEIT NOMINAL | NOMINAL CURRENT CORRIENTE NOMINAL COURANT NOMINAL NOMINALSTROM | STARTING TORQUE PAR DE ARRANQUE COUPLE DE DEMARRAGE ANZUGSDREHMOMENT | STARTING CURRENT CORRIENTE DE ARRANQUE COUPLET DE DEMARRAGE ANZUGSTROM | SHAFT EJE ARBRE WELLE | CONNECTIONS CONEXIONES CONNECTIONS ANSCHLUSSART | WIRING DIAGRAM ESQUEMA ELECTRICO SCHEMA ELECTRIQUE SCHALTPLAN | TRANSMISSION RATIO RELACION DE REDUCCION RAPPORT DE REDUCTEUR UNTERSATZUNG | APPROXIMATE WEIGHT PESO APROXIMADO POIDS APPROXIMATIF GEWICHT (ca.) | WATER TIGHTNESS GRADO DE ESTANQUEIDAD ETANCHÉITÉ FEUCHTIGKEITSSCHUTZKLASSE | WHEEL MATERIAL MATERIAL RUEDA MATERIAU ROUE MATERIAL DES SCHNELLERENDES | DESIGN: A, B, C DISEÑO: A, B, C DRESSIN: A, B, C ABBILDUNG: A, B, C | CURVE CURVA COURBE KURVE |
|---|---|---|---|---|---|---|--------------------------------|--|--|---|--|---|--|--|-----------------------------------|
| | Un (V) | Mn (N.m./lbf.in) | Pn (r.p.m.) | In (A) | Ma (N.m./lbf.in) | Ia (A) | | | | i | P (kg/lb) | IP | | | |
| 11137112000 | 12 | 5 / 44.2 | 40 | 5 | 25 / 221.2 | 25 | E22 | C25 | EE2 | 62:1 | 1.25 / 2.76 | IP53 | PLA | A | 1 |
| 11137113000 | 24 | 5 / 44.2 | 40 | 2.5 | 25 / 221.2 | 13 | E22 | C25 | EE2 | 62:1 | 1.25 / 2.76 | IP53 | PLA | A | 1 |
| 11137612000 | 12 | 5 / 44.2 | 40 | 5 | 25 / 221.2 | 25 | E23 | C25 | EE2 | 62:1 | 1.25 / 2.76 | IP53 | PLA | A | 1 |
| 11137613000 | 24 | 5 / 44.2 | 40 | 2.5 | 25 / 221.2 | 13 | E23 | C25 | EE2 | 62:1 | 1.25 / 2.76 | IP53 | PLA | A | 1 |
| 11137612000E | 12 | 5 / 44.2 | 40 | 5 | 25 / 221.2 | 25 | E23 | C25 | F2 | 62:1 | 1.25 / 2.76 | IP53 | PLA | A | 1 |
| 11137613000E | 24 | 5 / 44.2 | 40 | 2.5 | 25 / 221.2 | 13 | E23 | C25 | F2 | 62:1 | 1.25 / 2.76 | IP53 | PLA | A | 1 |
| 11137632000 | 12 | 6 / 53.1 | 25 | 4 | 25 / 221.2 | 15 | E23 | C25 | EE2 | 62:1 | 1.25 / 2.76 | IP53 | PLA | A | 3 |
| 11137633000 | 24 | 6 / 53.1 | 25 | 2 | 25 / 221.2 | 8 | E23 | C25 | EE2 | 62:1 | 1.25 / 2.76 | IP53 | PLA | A | 3 |
| 11147613000 | 24 | 5 / 44.2 | 40 | 2.5 | 25 / 221.2 | 13 | E23 | C25 | EE2 | 62:1 | 1.25 / 2.76 | IP53 | PLA | B | 1 |
| 11190312000 | 12 | 3 / 26.5 | 70 | 6 | 25 / 221.2 | 34 | E23 | C25 | EE2 | 62:1 | 1.25 / 2.76 | IP53 | PLA | A | 2 |
| 11190313000 | 24 | 3 / 26.5 | 70 | 3 | 25 / 221.2 | 17 | E23 | C25 | EE2 | 62:1 | 1.25 / 2.76 | IP53 | PLA | A | 2 |
| 11190392000 | 12 | 1.5 / 13.2 | 240 | 8 | 10 / 88.5 | 46 | E23 | C26 | EE1 | 49:4 | 1.25 / 2.76 | IP53 | PLA | A | 4 |
| 11190393000 | 24 | 1.5 / 13.2 | 240 | 4 | 10 / 88.5 | 23 | E23 | C26 | EE1 | 49:4 | 1.25 / 2.76 | IP53 | PLA | A | 4 |
| 11190413000 | 24 | 5 / 44.2 | 40 | 2.5 | 25 / 221.2 | 13 | E24 | C25 | EE2 | 62:1 | 1.30 / 2.87 | IP53 | BRO | A | 1 |
| 11190942000 | 12 | 5 / 44.2 | 40 | 5 | 25 / 221.2 | 25 | E52 | C2 | EE2 | 62:1 | 1.25 / 2.76 | IP53 | PLA | A | 1 |
| 11191073000 | 24 | 1.5 / 13.2 | 240 | 4 | 14 / 123.9 | 23 | E24/E53 | C26 | EE1 | 49:4 | 1.25 / 2.76 | IP40 | CEL | C | 4 |
| 11191992000 | 12 | 3 / 26.5 | 100 | 6 | 20 / 177.01 | 48 | E67 | C26 | F3 | 59:2 | 1.25 / 2.76 | IP53 | PLA | A | 59 |
| 11191993000 | 24 | 3 / 26.5 | 100 | 3 | 20 / 177.01 | 24 | E67 | C26 | F3 | 59:2 | 1.25 / 2.76 | IP53 | PLA | A | 59 |




mm / inch


SHAFT EJE ARBRE WELLE




E22




E23




E24



E52




E53




E67


CONNECTIONS CONEXIONES CONNEXIONS ANSCHLUSSART



C2




C25




C26


WIRING DIAGRAM ESQUEMA ELÉCTRICO SCHEMA ÉLECTRIQUE SCHALTBILD




EE1



EE2




F2




F3


CURVES CURVAS COURBES KURVEN




1




2



3



4



59