

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0348260161](#)
Status: **Active**
Overview:
Description: Mini50 Unsealed Right-Angle Header, Dual Row, 16 Circuit, Polarization Option B, 2.80mm Pin Length, Gray, Tray

General

Product Family	PCB Headers
Series	34826
Application	Automotive, Power, Signal, Wire-to-Board
Overview	mini50_unsealed_connection_systems
Product Name	Mini50
UPC	887191338941

Physical

Breakaway	No
Circuits (Loaded)	16
Circuits (maximum)	16
Color - Resin	Gray
Durability (mating cycles max)	10
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	2.840/g
Number of Rows	2
Orientation	Right Angle
PC Tail Length	2.80mm
PCB Locator	Yes
Packaging Type	Tray
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	4.0A (for reference only)
Voltage - Maximum	14V (typical operating)

Material Info

Reference - Drawing Numbers

Application Specification	AS-34791-020-001, AS-34791-020-CH-001, AS-34791-020-FR-001
Packaging Specification	PK-31301-440-001
Product Specification	PS-34791-020-001
Sales Drawing	SD-34826-001-001
Test Summary	347910020-TS-000

EU ELV
Compliant

EU RoHS **China RoHS**
Compliant

REACH SVHC
Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[34826](#) Series

Mates With

Mini50 Unsealed Dual Row Receptacle
[34824](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION