

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0099990988

Status:

Active

Overview:

Mini-SPOX Wire-to-Board Connector System

Description:

2.50mm Pitch, Mini-SPOX PCB Header, Single Row, Vertical, Through Hole, Tin Plating, 4 Circuits, Bag, with Swaged PC Tails

Documents:

- 2D Drawing (DXF)

2D Drawing DXF (PDF)

Drawing (PDF)

3D Model

3D Model (PDF)
- Product Specification 52641001-PS-000 (PDF)

Product Specification PS-5264-001-001 (PDF)

Packaging Specification SPK-5267-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	PCB Headers
Series	5267
Application	Signal, Wire-to-Board
Overview	Mini-SPOX Wire-to-Board Connector System
Product Name	Mini-SPOX
UPC	800753629776

Physical

Breakaway	No
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	373.000/mg
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.50mm
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Bag
Pitch - Mating Interface	2.50mm
Plating min - Mating	4.064µm
Plating min - Termination	4.064µm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

5267 Series

Mates With

Mini-SPOX Receptacle Housing 5264

Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	3.0A
Voltage - Maximum	250V
Material Info	
Engineering Number	5267-04A-X
Reference - Drawing Numbers	
Packaging Specification	SPK-5267-001-001
Product Specification	52641001-PS-000, PS-5264-001-001
Sales Drawing	52670002-SD-000

This document was generated on 12/22/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION