



| Art.-No. | Bemessungswerte/Ratings/Valeurs assignées | | | Spannungsfall Voltage drop Chute de tension max [mV] | Schmelzintegral Melting integral Intégral de fusion [A ² s] | |
|-----------------------|---|--------------------------------|--|---|---|--------|
| | Strom Current Courant | Spannung Voltage Tension | Ausschaltvermögen Breaking capacity Pouvoir de coupure | | | |
| 521.002 | 32 mA | 250 V | 80 A/250 V | 640 | 0,006431 | |
| 521.003 | 40 mA | | | 630 | 0,008896 | |
| 521.004 | 50 mA | | | 600 | 0,000600 | |
| 521.005 | 63 mA | | | 560 | 0,001032 | |
| 521.006 | 80 mA | | | 520 | 0,038528 | |
| 521.007 | 100 mA | | | 470 | 0,008600 | |
| 521.008 | 125 mA | | | 420 | 0,018438 | |
| 521.009 | 160 mA | | | 370 | 0,034304 | |
| 521.010 | 200 mA | | | 320 | 0,016000 | |
| 521.011 | 250 mA | | | 280 | 0,025000 | |
| 521.012 | 315 mA | | | 250 | 0,049613 | |
| 521.013 | 400 mA | | | 230 | 0,13 | |
| 521.014 | 500 mA | | | 210 | 0,20 | |
| 521.015 | 630 mA | | | 190 | 0,44 | |
| 521.016 | 800 mA | | | 170 | 0,86 | |
| 521.017 | 1 A | | | 160 | 6,28 | |
| 521.018 | 1,25 A | | | 160 | 2,50 | |
| 521.019 | 1,6 A | | | 1000 A/250 V | 160 | 1,54 |
| 521.020 | 2 A | | | | 160 | 5,52 |
| 521.021 | 2,5 A | | | | 160 | 8,25 |
| 521.022 | 3,15 A | | | | 160 | 16,47 |
| 521.023 | 4 A | | | | 160 | 25,92 |
| 521.024 | 5 A | | | | 150 | 49,00 |
| 521.025 | 6,3 A | | | | 140 | 78,59 |
| 521.026 | 8 A | | | 300 A/250 V | 140 | 162,56 |
| 521.027 | 10 A | 120 | 238,60 | | | |
| 521.028 ¹⁾ | 12,5 A | 120 | 437,50 | | | |
| 521.030 ¹⁾ | 16 A | 120 | 737,28 | | | |
| 521.031 | 20 A | 120 | | | | |

Aufbau: 32 mA-1,25 A: Glasrohr, durchsichtig
1,6 - 16 A: Glasrohr, mit Löschmittel
Kontaktkappen: Messing, vernickelt
Verpackung: 100 St. = 10 x 10 Faltschachteln
1000 St. = Industrieverpackung

Construction: 32 mA - 1,25 A: Glasstube, transparent
1,6 - 16 A: Glasstube, with extinguishing agent
Contact caps: Brass, nickel plated
Packing: 100 pcs. = 10 boxes of 10 pieces
1000 pcs. = Industrial boxes

Construction: 32 mA - 1,25 A: Tube verre, transparent
1,6 - 16 A: Tube verre, avec moyen d'extinction
Cabocons de contact: Laiton, nickelé
Emballage: 100 pcs. = en 10 boîtes de 10 pièces
1000 pcs. = en emballage industriel

Strom-Zeit-Kennlinien
Current Time Characteristics
Caractéristique courant/temps



Schmelzzeit-Grenzwerte / Pre-arcing time limits / Temps de fusion limité

| Bemessungsstrom Rated current Courant assigné | 1,5 I _{rat} | 2,1 I _{rat} | 4 I _{rat} | | 10 I _{rat} | |
|---|----------------------|----------------------|--------------------|----------|---------------------|-------|
| | min. | max. | min. | max. | min. | max. |
| 32 mA - 1,25 A | 1 h | 10 min. | 40 ms | 2.000 ms | 5 ms | 90 ms |
| 1,6 A - 10 A | 1 h | 30 min. | 40 ms | 2.000 ms | 5 ms | 90 ms |